



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A																									
Supplier Information																																		
Company Name	TE Connectivity	Request Document ID		Contact Name	John R. Penica	Contact Title	Mgr. Global Product Compliance																											
Company Unique ID	TE Connectivity	Response Date	2016-06-15	Contact Email	jrpenica@te.com																													
Contact Phone Number		717-592-3266																																
Legal Statement																																		
Supplier Acceptance	true																																	
Legal Statement																																		
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.																																		
Product																																		
Manufacturer Item number	1676363-3	Amount	4.70724	Version	-	Identity																												
Manufacturer Item Name	RN 0805 4K99 0.1% 10PPM 5KRL	Weight Uom	mg	Mfr Site		Authority																												
Date		UOM	Each																															
EUROHS-0508	Product(s) meets EU RoHS requirement without any exemptions																																	
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products																																	
EUREACH-0615	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH																																	
Product Disclosure																																		
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption																									
Material	1	Nickel Plating				1.0	0.01270013	mg																										
Substance	2	Nickel	Nickel	7440-02-0	100.0	1.0	0.01270013	mg																										
Material	1	Upside Electrode				1.0	0.05379905	mg																										
Substance	2	Ethanol, 2-(2-butoxyethoxy)-	Supplier	112-34-5	20.0	1.0	0.01075981	mg																										
Substance	2	Copper oxide (CuO)	Supplier	1317-38-0	10.0	1.0	0.0053799	mg																										
Substance	2	Terpineol	Supplier	8000-41-7	15.0	1.0	0.00806986	mg																										
Substance	2	Silver	Supplier	7440-22-4	55.0	1.0	0.02958948	mg																										
Material	1	Backside Electrode				1.0	0.05379905	mg																										
Substance	2	Ethanol, 2-(2-butoxyethoxy)-	Supplier	112-34-5	20.0	1.0	0.01075981	mg																										
Substance	2	Copper oxide (CuO)	Supplier	1317-38-0	10.0	1.0	0.0053799	mg																										
Substance	2	Terpineol	Supplier	8000-41-7	15.0	1.0	0.00806986	mg																										
Substance	2	Silver	Supplier	7440-22-4	55.0	1.0	0.02958948	mg																										
Material	1	Overcoat				1.0	0.0433019	mg																										
Substance	2	Ethanol, 2-(2-butoxyethoxy)-	Supplier	112-34-5	12.0	1.0	0.00519623	mg																										
Substance	2	Carbon black	Supplier	1333-86-4	3.0	1.0	0.00129906	mg																										
Substance	2	Resin acids and Rosin acids	Supplier	73138-82-6	35.0	1.0	0.01515567	mg																										
Substance	2	Acetamide	Supplier	60-35-5	20.0	1.0	0.00866038	mg																										
Substance	2	Talc (Mg3H2(SiO3)4)	Supplier	14807-96-6	10.0	1.0	0.00433019	mg																										
Substance	2	Silica, vitreous	Supplier	60676-86-0	20.0	1.0	0.00866038	mg																										
Material	1	Tin Plating				1.0	0.02980154	mg																										
Substance	2	Tin	Supplier	7440-31-5	100.0	1.0	0.02980154	mg																										
Material	1	Edge Electrode				1.0	2.35362E-5	mg																										
Substance	2	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	100.0	1.0	2.35362E-5	mg																										
Material	1	Resistor Layer				1.0	1.882896E-5	mg																										
Substance	2	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	100.0	1.0	1.882896E-5	mg																										
Material	1	Marking				1.0	0.02379981	mg																										

Substance	2	Titanium oxide (TiO2)	Supplier	13463-67-7	20.0	1.0	0.00475996	mg	
Substance	2	Cellulose, ethyl ether	Supplier	9004-57-3	80.0	1.0	0.01903984	mg	
Material	1	Substrate				1.0	4.48999617	mg	
Substance	2	Aluminum oxide (Al2O3)	Supplier	1344-28-1	96.0	1.0	4.3104	mg	
Substance	2	Quartz (SiO2)	Supplier	14808-60-7	3.0	1.0	0.1347	mg	
Substance	2	Magnesium oxide (MgO)	Supplier	1309-48-4	1.0	1.0	0.04489996	mg	