



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Manufacturing Info/ Material Info	Sectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Penica, John R	Contact Title	Sr Mgr Environmental Engineering, IND Central Eng		
Company Unique ID	TE Connectivity	Response Date	2015-12-22	Contact Email	jrpenica@te.com				
Contact Phone Number	1-717-592-3266								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	36964	Amount	566.890178	Version	-	Identity			
Manufacturer Item Name	SPLICE,CE 22-14	Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EURoHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-1214	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
Manufacturing Information									
J-STD-020 MSL Rating		Max Total a Wave Time		Ramp Rate		Wave Additional Info			
Classification Temp		Max Wave Solder Time	0.0	Ramp Down Rate		Psi Rating Reflow			
Max Time Within 5		Psi Rating Wave		Package Designator		Size	0.0		
Time Above 217		Reflow Additional Info		Preheat Max Temp		Terminal Base Alloy	NAC		
Preheat Duration		bulk Solder Termination	NAC	Nbr or Reflow Cycles		Terminal Plating	NAC		
Preheat Min Temp		Nbr of Instances	0	Component Temp Spike		Shape	NAC		
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	SPLICE SOLIS PARA SPEC 22-14				1.0	337.925378	mg	
Material	2	Tin Plate				1.0	4.037378	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	1.0	4.02648	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.00807476	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	1.0	0.00282616	mg	
Material	2	Brazing Filler				1.0	5.088	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	6.7	1.0	0.3409	mg	
Substance	3	Copper	Supplier	7440-50-8	87.05	1.0	4.4291	mg	
Substance	3	Silver	Supplier	7440-22-4	6.25	1.0	0.318	mg	
Material	2	Copper				1.0	328.8	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.05	1.0	0.1644	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	0.003288	mg	
Substance	3	Copper	Supplier	7440-50-8	99.7575	1.0	328.00266	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.003288	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	1.0	0.01644	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.03288	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	0.06576	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.3288	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.1644	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.001644	mg	

Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	0.01644	mg	
Sub-Item	1	TUBING EXTRUDED				1.0	228.9648	mg	
Material	2	PVC				1.0	227.82	mg	
Substance	3	Ethene, chloro-	Supplier	75-01-4	4.0E-4	1.0	9.1128E-4	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	7.5	1.0	17.0865	mg	
Substance	3	Ethene, chloro-, homopolymer	Supplier	9002-86-2	87.9961	1.0	200.47272	mg	
Substance	3	8-Oxa-3,5-dithia-4-stannatetradecanoic acid, 10-ethyl-4,4-dimethyl-7-oxo-, 2-ethylhexyl ester	Supplier	57583-35-4	1.5	1.0	3.4173	mg	
Substance	3	Octadecanoic acid, calcium salt (2:1)	Supplier	1592-23-0	0.5	1.0	1.1391	mg	
Substance	3	Calcium hydroxide (Ca(OH)2)	Supplier	1305-62-0	0.0035	1.0	0.0079737	mg	
Substance	3	8-Oxa-3,5-dithia-4-stannatetradecanoic acid, 10-ethyl-4-[[2-[(2-ethylhexyl)oxy]-2-oxoethyl]thio]-4-methyl-7-oxo-, 2-ethylhexyl ester	Supplier	57583-34-3	0.5	1.0	1.1391	mg	
Substance	3	Limestone	Supplier	1317-65-3	2.0	1.0	4.5564	mg	
Material	2	COLORANT				1.0	1.1448	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	8.5	1.0	0.097308	mg	
Substance	3	Ethene, chloro-, homopolymer	Supplier	9002-86-2	81.2896	1.0	0.9306	mg	
Substance	3	Octadecanoic acid, zinc salt (2:1)	Supplier	557-05-1	0.19	1.0	0.00217512	mg	
Substance	3	Aluminate (Al(OH)63-), (OC-6-11)-, magnesium carbonate hydroxide (2:6:1:4)	Supplier	11097-59-9	0.7	1.0	0.0080136	mg	
Substance	3	Octadecanoic acid, calcium salt (2:1)	Supplier	1592-23-0	1.0	1.0	0.011448	mg	
Substance	3	Rosin	Supplier	8050-09-7	0.15	1.0	0.0017172	mg	
Substance	3	8-Oxa-3,5-dithia-4-stannatetradecanoic acid, 10-ethyl-4,4-dimethyl-7-oxo-, 2-ethylhexyl ester	Supplier	57583-35-4	1.0	1.0	0.011448	mg	
Substance	3	Ethene, chloro-	Supplier	75-01-4	4.0E-4	1.0	1.0E-5	mg	
Substance	3	2-Naphthalenecarboxylic acid, 4-[2-(5-chloro-4-methyl-2-sulphophenyl)diazenyl]-3-hydroxy-, calcium salt (1:1)	Supplier	7023-61-2	5.0	1.0	0.05724	mg	
Substance	3	Silica	Supplier	7631-86-9	0.3	1.0	0.0034344	mg	
Substance	3	8-Oxa-3,5-dithia-4-stannatetradecanoic acid, 10-ethyl-4-[[2-[(2-ethylhexyl)oxy]-2-oxoethyl]thio]-4-methyl-7-oxo-, 2-ethylhexyl ester	Supplier	57583-34-3	0.2	1.0	0.0022896	mg	
Substance	3	Zeolites	Supplier	1318-02-1	0.18	1.0	0.00206064	mg	

Substance	3	Copper, [29H,31H- phthalocyanina to(2-)- .kappa.N29,.ka ppa.N30,.kapp a.N31,.kappa. N32]-, (SP-4- 1)-	Supplier	147-14-8	1.35	1.0	0.0154548	mg	
Substance	3	Glycerol	Supplier	56-81-5	0.14	1.0	0.00160272	mg	