



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	John R. Penica	Contact Title	Mgr. Global Product Compliance		
Company Unique ID	TE Connectivity	Response Date	2016-06-22	Contact Email	jrpenica@te.com				
Contact Phone Number	717-592-3266								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	5-534206-9	Amount	1315.267461	Version	-	Identity			
Manufacturer Item Name	18 MODII VRT DR CE 100/115	Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-0615	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	MOD IV DUAL ENTRY CONTACT,30AU				18.0	29.2718	mg	
Material	2	Nickel Plate				18.0	2.713	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	18.0	0.005426	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	18.0	0.002713	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	18.0	2.70486	mg	
Material	2	Gold Plate				18.0	0.0258	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	18.0	0.0257226	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	18.0	7.74E-5	mg	
Material	2	Tin Plate				18.0	0.575	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	18.0	0.00115	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	18.0	0.57345	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	18.0	4.025E-4	mg	
Material	2	Phos Bronze				18.0	25.958	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6985	18.0	24.58184	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	18.0	0.0051916	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	18.0	0.0025958	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	18.0	1.16811	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	18.0	0.0012979	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	18.0	0.025958	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	18.0	0.0025958	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	18.0	2.5958E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	18.0	0.077874	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	18.0	0.025958	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	18.0	0.025958	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	18.0	0.0012979	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	18.0	0.012979	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	18.0	0.025958	mg	

Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	18.0	1.2979E-4	mg	
Sub-Item	1	Polyester Compound				1.0	788.375061	mg	
Material	2	PCT-GF30				1.0	788.375061	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	31.0	1.0	244.39627	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	6.0	1.0	47.3025	mg	
Substance	3	Antimonate (SbO3 ¹⁻), sodium (1:1)	Supplier	15432-85-6	3.5	1.0	27.59313	mg	
Substance	3	Benzene, ethenyl-, homopolymer, brominated	Supplier	88497-56-7	14.0	1.0	110.37251	mg	
Substance	3	Carbon black	Supplier	1333-86-4	0.7	1.0	5.51863	mg	
Substance	3	Talc (Mg3H2(SiO3)4)	Supplier	14807-96-6	2.0	1.0	15.7675	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-cyclohexanedi methanol	Supplier	25135-20-0	42.8	1.0	337.42453	mg	