



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	John R. Penica	Contact Title	Mgr. Global Product Compliance		
Company Unique ID	TE Connectivity	Response Date	2016-06-22	Contact Email	jrpenica@te.com				
Contact Phone Number	717-592-3266								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	87220-4	Amount	278.924	Version	-	Identity			
Manufacturer Item Name	04 MODII HDR SRST UNSHRD .100	Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-0615	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	MOD II POST PLTD 5/30 AU				4.0	55.276	mg	
Material	2	Gold Plate				4.0	0.271	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	4.0	0.27019	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	4.0	8.13E-4	mg	
Material	2	Nickel Plate				4.0	0.596	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	4.0	0.001192	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	4.0	5.96E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	4.0	0.59421	mg	
Material	2	Phos Bronze				4.0	54.392	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6985	4.0	51.50841	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	4.0	0.0108784	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	4.0	0.0054392	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	4.0	2.44764	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	4.0	0.0027196	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	4.0	0.054392	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	4.0	0.0054392	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	4.0	5.4392E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	4.0	0.16318	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	4.0	0.054392	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	4.0	0.054392	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	4.0	0.0027196	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	4.0	0.027196	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	4.0	0.054392	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	4.0	2.7196E-4	mg	
Material	2	Gold Plate				4.0	0.017	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.1	4.0	1.7E-5	mg	
Substance	3	Gold	Supplier	7440-57-5	99.9	4.0	0.016983	mg	
Sub-Item	1	Nylon Compound				1.0	57.82	mg	

Material	2	PA66-GF25				1.0	57.82	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	23.95	1.0	13.84789	mg	
Substance	3	Poly[imino(1-oxo-1,6-hexanediy)]	Supplier	25038-54-4	0.945	1.0	0.5464	mg	
Substance	3	Siloxanes and Silicones, di-Me	Supplier	63148-62-9	0.0020	1.0	0.0011564	mg	
Substance	3	1,4:7,10-Dimethanodibenzo[a,e]cyclooctene, 1,2,3,4,7,8,9,10,13,13,14,14-dodecachloro-1,4,4a,5,6,6a,7,10,10a,11,12,12a-dodecahydro-	Supplier	13560-89-9	14.17	1.0	8.19309	mg	
Substance	3	Hexanedioic acid, polymer with hexahydro-2H-azepin-2-one and 1,6-hexanediamine	Supplier	24993-04-2	51.993	1.0	30.06235	mg	
Substance	3	1,2-Benzenedicarboxylic acid, 1,2-diundecyl ester, branched and linear	Supplier	85507-79-5	1.43	1.0	0.82683	mg	
Substance	3	Carbon black	Supplier	1333-86-4	0.49	1.0	0.28332	mg	
Substance	3	Boric acid, zinc salt	Supplier	1332-07-6	2.1	1.0	1.21422	mg	
Substance	3	Antimony oxide (Sb ₂ O ₃)	Supplier	1309-64-4	4.81	1.0	2.78114	mg	
Substance	3	Aluminum, hydroxybis(octadecanoato- κ O)-	Supplier	300-92-5	0.1	1.0	0.05782	mg	
Substance	3	Copper iodide (CuI)	Supplier	7681-65-4	0.01	1.0	0.005782	mg	