



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Benfer David W	Contact Title	Product Compliance Engineer for DND		
Company Unique ID	TE Connectivity	Response Date	2016-04-11	Contact Email	dave.benfer@te.com				
Contact Phone Number	717-986-3725								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	5554349-1	Amount	33894.174804	Version	-	Identity			
Manufacturer Item Name	EMI RCPT ASSY, 24 POS, SHLD	Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-0615	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	SUPPORT/TE RM,RCPT,LPF ,C/LATCH				1.0	644.714798	mg	
Material	2	PPE+PS				1.0	644.714798	mg	
Substance	3	1-Butene, polymer with ethene	Supplier	25087-34-7	2.0	1.0	12.8943	mg	
Substance	3	Phenol, 2,6-dimethyl-, homopolymer	Supplier	25134-01-4	41.225	1.0	265.78368	mg	
Substance	3	Zinc sulfide (ZnS)	Supplier	1314-98-3	0.15	1.0	0.96707	mg	
Substance	3	Phosphoric acid, P,P-1,3-phenylene P,P,P,P-tetraphenyl ester	Supplier	57583-54-7	12.0	1.0	77.36578	mg	
Substance	3	Phosphorous acid, triisodecyl ester	Supplier	25448-25-3	1.0	1.0	6.44715	mg	
Substance	3	Ethene, 1,1,2,2-tetrafluoro-, homopolymer	Supplier	9002-84-0	0.15	1.0	0.96707	mg	
Substance	3	Zinc oxide (ZnO)	Supplier	1314-13-2	0.15	1.0	0.96707	mg	
Substance	3	Benzene, methyl-	Supplier	108-88-3	0.1	1.0	0.64471	mg	
Substance	3	Carbon black	Supplier	1333-86-4	1.0	1.0	6.44715	mg	
Substance	3	Benzene, ethenyl-, polymer with 1,3-butadiene	Supplier	9003-55-8	41.225	1.0	265.78368	mg	
Substance	3	Phosphoric acid, triphenyl ester	Supplier	115-86-6	1.0	1.0	6.44715	mg	
Sub-Item	1	CAP, TERM HSG, .050/.085				1.0	594.9	mg	
Material	2	PPE+PS				1.0	594.9	mg	
Substance	3	1-Butene, polymer with ethene	Supplier	25087-34-7	2.0	1.0	11.898	mg	
Substance	3	Phenol, 2,6-dimethyl-, homopolymer	Supplier	25134-01-4	41.225	1.0	245.24753	mg	
Substance	3	Zinc sulfide (ZnS)	Supplier	1314-98-3	0.15	1.0	0.89235	mg	

Substance	3	Phosphoric acid, P,P-1,3-phenylene P,P,P,P-tetraphenyl ester	Supplier	57583-54-7	12.0	1.0	71.388	mg	
Substance	3	Phosphorous acid, trisodecyl ester	Supplier	25448-25-3	1.0	1.0	5.949	mg	
Substance	3	Ethene, 1,1,2,2-tetrafluoro-, homopolymer	Supplier	9002-84-0	0.15	1.0	0.89235	mg	
Substance	3	Zinc oxide (ZnO)	Supplier	1314-13-2	0.15	1.0	0.89235	mg	
Substance	3	Benzene, methyl-	Supplier	108-88-3	0.1	1.0	0.5949	mg	
Substance	3	Carbon black	Supplier	1333-86-4	1.0	1.0	5.949	mg	
Substance	3	Benzene, ethenyl-, polymer with 1,3-butadiene	Supplier	9003-55-8	41.225	1.0	245.24753	mg	
Substance	3	Phosphoric acid, triphenyl ester	Supplier	115-86-6	1.0	1.0	5.949	mg	
Sub-Item	1	SHIELD,EMI,R ECEPT,24 POSN,CHAMP				1.0	25732.684	mg	
Material	2	Tin-Nickel Plate				1.0	268.016	mg	
Substance	3	Tin	Supplier	7440-31-5	70.0	1.0	187.6112	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.5	1.0	1.34008	mg	
Substance	3	Nickel	Nickel	7440-02-0	29.5	1.0	79.06472	mg	
Material	2	Zinc Alloy				1.0	25340.22	mg	
Substance	3	Silicon	Supplier	7440-21-3	0.035	1.0	8.86908	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.02	1.0	5.06804	mg	
Substance	3	Tin	Supplier	7440-31-5	0.0030	1.0	0.76021	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.06	1.0	15.20413	mg	
Substance	3	Copper	Supplier	7440-50-8	0.25	1.0	63.35055	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	2.53402	mg	
Substance	3	Zinc	Supplier	7440-66-6	95.0315	1.0	24081.19117	mg	
Substance	3	Aluminum	Supplier	7429-90-5	4.3	1.0	1089.62946	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	2.53402	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.2534	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	1.0	25.34022	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	25.34022	mg	
Substance	3	Magnesium	Supplier	7439-95-4	0.05	1.0	12.67011	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.02	1.0	5.06804	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0050	1.0	1.26701	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.1267	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0040	1.0	1.01361	mg	
Material	2	Nickel Plate				1.0	124.448	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.12445	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	124.07466	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.2489	mg	
Sub-Item	1	COVER, .050/.085, CHAMP				1.0	1616.9	mg	
Material	2	PBT-GF15				1.0	1616.9	mg	
Substance	3	Carbon black	Supplier	1333-86-4	1.5	1.0	24.2535	mg	
Substance	3	Ethene, 1,1,2,2-tetrafluoro-, homopolymer	Supplier	9002-84-0	0.5	1.0	8.0845	mg	
Substance	3	2-Propenenitrile, polymer with ethenylbenzene	Supplier	9003-54-7	0.4	1.0	6.4676	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	55.9	1.0	903.8471	mg	

Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	5.0	1.0	80.845	mg	
Substance	3	Acetic acid ethenyl ester, polymer with ethene	Supplier	24937-78-8	3.0	1.0	48.507	mg	
Substance	3	Phosphoric acid, zinc salt (2:3)	Supplier	7779-90-0	0.9	1.0	14.5521	mg	
Substance	3	Octadecanoic acid, 1,1-[2,2-bis[[1-(1-oxooctadecyl)oxy]methyl]-1,3-propanediyl] ester	Supplier	115-83-3	0.5	1.0	8.0845	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	17.0	1.0	274.873	mg	
Substance	3	Furan, tetrahydro-	Supplier	109-99-9	0.3	1.0	4.8507	mg	
Substance	3	Carbonic dichloride, polymer with 4,4-(1-methylethylidene)bis[2,6-dibromophenol] and phenol	Brominated Flame Retardants (other than PBBs or PBDEs)	94334-64-2	15.0	1.0	242.535	mg	
Sub-Item	1	ARRAY, TERM, PLATED, 24 POSN, RCPT				1.0	885.938003	mg	
Material	2	Nickel Plate				1.0	14.33076	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.02866152	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.01433076	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	14.28777	mg	
Material	2	Gold Plate				1.0	0.607243	mg	
Substance	3	Gold	Supplier	7440-57-5	99.0	1.0	0.60117	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	1.0	1.0	0.00607243	mg	
Material	2	Copper Alloy				1.0	871.0	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.871	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.5	1.0	4.355	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.2	1.0	1.742	mg	
Substance	3	Copper	Supplier	7440-50-8	85.2175	1.0	742.24443	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	0.00871	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.00871	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.0871	mg	
Substance	3	Iron	Supplier	7439-89-6	0.6	1.0	5.226	mg	
Substance	3	Tin	Supplier	7440-31-5	2.8	1.0	24.388	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.0871	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.0871	mg	
Substance	3	Nickel	Nickel	7440-02-0	10.5	1.0	91.455	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.004355	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.4355	mg	
Sub-Item	1	HOUSING, EMI RCPT, CHAMP LATCH				1.0	3533.1	mg	
Material	2	PPE+PS				1.0	3533.1	mg	
Substance	3	1-Butene, polymer with ethene	Supplier	25087-34-7	2.0	1.0	70.662	mg	
Substance	3	Phenol, 2,6-dimethyl-, homopolymer	Supplier	25134-01-4	41.225	1.0	1456.52048	mg	
Substance	3	Zinc sulfide (ZnS)	Supplier	1314-98-3	0.15	1.0	5.29965	mg	
Substance	3	Phosphoric acid, P,P-1,3-phenylene P,P,P,P-tetraphenyl ester	Supplier	57583-54-7	12.0	1.0	423.972	mg	
Substance	3	Phosphorous acid, triisodecyl ester	Supplier	25448-25-3	1.0	1.0	35.331	mg	

Substance	3	Ethene, 1,1,2,2-tetrafluoro-, homopolymer	Supplier	9002-84-0	0.15	1.0	5.29965	mg	
Substance	3	Zinc oxide (ZnO)	Supplier	1314-13-2	0.15	1.0	5.29965	mg	
Substance	3	Benzene, methyl-	Supplier	108-88-3	0.1	1.0	3.5331	mg	
Substance	3	Carbon black	Supplier	1333-86-4	1.0	1.0	35.331	mg	
Substance	3	Benzene, ethenyl-, polymer with 1,3-butadiene	Supplier	9003-55-8	41.225	1.0	1456.52048	mg	
Substance	3	Phosphoric acid, triphenyl ester	Supplier	115-86-6	1.0	1.0	35.331	mg	
Sub-Item	1	ARRAY, TERM, PLATED, 24 POSN, RCPT				1.0	885.938003	mg	
Material	2	Nickel Plate				1.0	14.33076	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.02866152	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.01433076	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	14.28777	mg	
Material	2	Gold Plate				1.0	0.607243	mg	
Substance	3	Gold	Supplier	7440-57-5	99.0	1.0	0.60117	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	1.0	1.0	0.00607243	mg	
Material	2	Copper Alloy				1.0	871.0	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.871	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.5	1.0	4.355	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.2	1.0	1.742	mg	
Substance	3	Copper	Supplier	7440-50-8	85.2175	1.0	742.24443	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	0.00871	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.00871	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.0871	mg	
Substance	3	Iron	Supplier	7439-89-6	0.6	1.0	5.226	mg	
Substance	3	Tin	Supplier	7440-31-5	2.8	1.0	24.388	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.0871	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.0871	mg	
Substance	3	Nickel	Nickel	7440-02-0	10.5	1.0	91.455	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.004355	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.4355	mg	