



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Benfer David W	Contact Title	Product Compliance Engineer for DND		
Company Unique ID	TE Connectivity	Response Date	2016-06-25	Contact Email	dave.benfer@te.com				
Contact Phone Number	717-986-3725								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	1-1871058-3	Amount	6333.7	Version	-	Identity			
Manufacturer Item Name	PCI EXPRESS CONN. EON TYPE, 98	Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUROHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-0615	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	PCI EXPRESS, EON TYPE, 98P,L=3.25,AS SY				1.0	6333.7	mg	
Material	2	Nickel Plate				1.0	49.098	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.049098	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.098196	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	48.95071	mg	
Material	2	Gold Plate				1.0	3.43	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	1.0	3.41971	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	1.0	0.01029	mg	
Material	2	Tin Plate				1.0	11.172	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.022344	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	1.0	11.14184	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	1.0	0.0078204	mg	
Material	2	PPA-GF30				1.0	4800.0	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	1440.0	mg	
Substance	3	Benzene, ethenyl-, homopolymer, brominated	Supplier	88497-56-7	20.0	1.0	960.0	mg	
Substance	3	Antimonate (SbO31-), sodium (1:1)	Supplier	15432-85-6	3.8	1.0	182.4	mg	
Substance	3	1,4-Benzenedicarb oxylic acid, polymer with 1,6-hexanediamine and hexanedioic acid	Supplier	25776-72-1	46.0	1.0	2208.0	mg	
Substance	3	Carbon black	Supplier	1333-86-4	0.2	1.0	9.6	mg	
Material	2	Phos Bronze				1.0	1470.0	mg	

Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	1.47	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.147	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.2	1.0	2.94	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	1.0	0.0735	mg	
Substance	3	Copper	Supplier	7440-50-8	90.0485	1.0	1323.71295	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	0.294	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.35	1.0	5.145	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.0147	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	1.0	1.47	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	1.0	0.147	mg	
Substance	3	Tin	Supplier	7440-31-5	9.0	1.0	132.3	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	1.0	1.47	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.00735	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	0.0735	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.735	mg	