



<b>Form Type</b>	Distribute	<b>Version</b>	2.0	<b>Ref</b>	IPC 1752A	<b>Sectionals</b>	Material Info	<b>Subsectionals</b>	D, A
<b>Supplier Information</b>									
<b>Company Name</b>	TE Connectivity	<b>Request Document ID</b>		<b>Contact Name</b>	Wu, Cc	<b>Contact Title</b>	Engineer Product Compliance china		
<b>Company Unique ID</b>	TE Connectivity	<b>Response Date</b>	2016-07-02	<b>Contact Email</b>	cc.wu@te.com				
<b>Contact Phone Number</b>	86-2124071672								
<b>Legal Statement</b>									
<b>Supplier Acceptance</b>	true								
<b>Legal Statement</b>									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
<b>Product</b>									
<b>Manufacturer Item number</b>	3-794627-6	<b>Amount</b>	952.003	<b>Version</b>	-	<b>Identity</b>			
<b>Manufacturer Item Name</b>	06P MICRO MNL ASSY,RA ,SMT, LF	<b>Weight Uom</b>	mg	<b>Mfr Site</b>		<b>Authority</b>			
<b>Date</b>		<b>UOM</b>	Each						
<b>EUroHS-0508</b>	Product(s) meets EU RoHS requirement without any exemptions								
<b>ChinaRoHS-0508</b>	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
<b>EUREACH-0615</b>	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
<b>Product Disclosure</b>									
<b>Sub-Item/Material/Substance</b>	<b>Level</b>	<b>Name</b>	<b>Substance Category</b>	<b>Substance CAS</b>	<b>Substance Concentration</b>	<b>Quantity</b>	<b>Mass per Unit</b>	<b>UOM</b>	<b>Exemption</b>
Sub-Item	1	Post Contact right angle SMT I				3.0	35.986	mg	
Material	2	Brass				3.0	34.3395	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	3.0	3.4339E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	28.0225	3.0	9.62279	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.05	3.0	0.01716975	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	3.0	0.00343395	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	3.0	0.01716975	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	3.0	0.0343395	mg	
Substance	3	Copper	Supplier	7440-50-8	71.5	3.0	24.55274	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	3.0	3.4339E-4	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	3.0	0.00343395	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	3.0	1.717E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.2	3.0	0.068679	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	3.0	0.00171697	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	3.0	0.01716975	mg	
Material	2	Tin Plate				3.0	1.1295	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	3.0	1.12645	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	3.0	0.002259	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	3.0	7.9065E-4	mg	
Material	2	Nickel Plate				3.0	0.517	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	3.0	0.001034	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	3.0	5.17E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	3.0	0.51545	mg	
Sub-Item	1	6POS MICRO MNL HSG.BLACK				1.0	456.98	mg	
Material	2	PA4T-GF30-FR(40)				1.0	456.98	mg	
Substance	3	Carbon black	Supplier	1333-86-4	0.9	1.0	4.11282	mg	

Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	137.094	mg	
Substance	3	Polyamide 4T - ISO 1043-1 Term PA4T	Supplier	1043-1-PA4T	47.1	1.0	215.23758	mg	
Substance	3	Halogen-free organic phosphorus flame retardant - ISO 1043-4 code #FR(40)	Supplier	1043-4-FR40	12.0	1.0	54.8376	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	10.0	1.0	45.698	mg	
Sub-Item	1	MICROMNL LP CONT,R/A,PR E-TIN				2.0	106.96	mg	
Material	2	Phos Bronze				2.0	104.0	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	2.0	0.104	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	2.0	0.0104	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.2	2.0	0.208	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	2.0	0.0052	mg	
Substance	3	Copper	Supplier	7440-50-8	90.0485	2.0	93.65044	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	2.0	0.0208	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.35	2.0	0.364	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	2.0	0.00104	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	2.0	0.104	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	2.0	0.0104	mg	
Substance	3	Tin	Supplier	7440-31-5	9.0	2.0	9.36	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	2.0	0.104	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	2.0	5.2E-4	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	2.0	0.0052	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	2.0	0.052	mg	
Material	2	Tin Plate				2.0	1.84	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	2.0	1.83503	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	2.0	0.00368	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	2.0	0.001288	mg	
Material	2	Nickel Plate				2.0	1.12	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	2.0	0.00224	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	2.0	0.00112	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	2.0	1.11664	mg	
Sub-Item	1	MICROMNL LP CONT,R/A,SN				3.0	57.715	mg	
Material	2	Brass				3.0	56.8	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	3.0	5.68E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	28.0225	3.0	15.91678	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.05	3.0	0.0284	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	3.0	0.00568	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	3.0	0.0284	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	3.0	0.0568	mg	
Substance	3	Copper	Supplier	7440-50-8	71.5	3.0	40.612	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	3.0	5.68E-4	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	3.0	0.00568	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	3.0	2.84E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.2	3.0	0.1136	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	3.0	0.00284	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	3.0	0.0284	mg	
Material	2	Tin Plate				3.0	0.157	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	3.0	0.15658	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	3.0	3.14E-4	mg	

Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	3.0	1.099E-4	mg	
Material	2	Nickel Plate				3.0	0.758	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	3.0	0.001516	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	3.0	7.58E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	3.0	0.75573	mg	