



<b>Form Type</b>	Distribute	<b>Version</b>	2.0	<b>Ref</b>	IPC 1752A	<b>Sectionals</b>	Material Info	<b>Subsectionals</b>	D, A																									
<b>Supplier Information</b>																																		
<b>Company Name</b>	TE Connectivity	<b>Request Document ID</b>		<b>Contact Name</b>	John R. Penica	<b>Contact Title</b>	Mgr. Global Product Compliance																											
<b>Company Unique ID</b>	TE Connectivity	<b>Response Date</b>	2016-05-20	<b>Contact Email</b>	jrpenica@te.com																													
<b>Contact Phone Number</b>		717-592-3266																																
<b>Legal Statement</b>																																		
<b>Supplier Acceptance</b>	true																																	
<b>Legal Statement</b>																																		
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.																																		
<b>Product</b>																																		
<b>Manufacturer Item number</b>	1546306-2	<b>Amount</b>	10320.002	<b>Version</b>	-	<b>Identity</b>																												
<b>Manufacturer Item Name</b>	2P .374" DR BARRIER STRIP	<b>Weight Uom</b>	mg	<b>Mfr Site</b>		<b>Authority</b>																												
<b>Date</b>		<b>UOM</b>	Each																															
<b>EUroHS-0508</b>	Product(s) meets EU RoHS requirement without any exemptions																																	
<b>ChinaRoHS-0508</b>	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products																																	
<b>EUREACH-0615</b>	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH																																	
<b>Product Disclosure</b>																																		
<b>Sub-Item/Material/Substance</b>	<b>Level</b>	<b>Name</b>	<b>Substance Category</b>	<b>Substance CAS</b>	<b>Substance Concentration</b>	<b>Quantity</b>	<b>Mass per Unit</b>	<b>UOM</b>	<b>Exemption</b>																									
Material	1	Inulating body				1.0	4599.99999974	mg																										
Substance	2	Carbonic dichloride, polymer with 4,4-(1-methylethylidene)bis[phenol], 4-(1-methyl-1-phenylethyl)phenyl ester	Supplier	111211-39-3	99.0	1.0	4554.0	mg																										
Substance	2	Carbon black	Supplier	1333-86-4	1.0	1.0	46.0	mg																										
Material	1	Screw				1.0	3319.99999989	mg																										
Substance	2	Carbon	Supplier	7440-44-0	0.28	1.0	9.296	mg																										
Substance	2	Phosphorus	Supplier	7723-14-0	0.03	1.0	0.996	mg																										
Substance	2	Iron	Supplier	7439-89-6	98.64	1.0	3274.848	mg																										
Substance	2	Manganese	Supplier	7439-96-5	1.0	1.0	33.2	mg																										
Substance	2	Sulfur	Supplier	7704-34-9	0.05	1.0	1.66	mg																										
Material	1	Terminal				1.0	2400.00000036	mg																										
Substance	2	Zinc	Supplier	7440-66-6	32.0	1.0	768.0	mg																										
Substance	2	Copper	Supplier	7440-50-8	68.0	1.0	1632.0	mg																										
Material	1	Plating 1				1.0	0.0010	mg																										
Substance	2	Sulfuric acid, nickel(2+) salt, hydrate (1:1:6)	Supplier	10101-97-0	100.0	1.0	0.0010	mg																										
Material	1	Plating				1.0	0.0010	mg																										
Substance	2	Tin	Supplier	7440-31-5	100.0	1.0	0.0010	mg																										