



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Cc Wu	Contact Title	Prod Compliance Engineer		
Company Unique ID	TE Connectivity	Response Date	2016-05-20	Contact Email	cc.wu@te.com				
Contact Phone Number	+86-21-33259321								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	2-1445098-3	Amount	0.4419917	Version	-	Identity			
Manufacturer Item Name	MICRO MNL HDR ASSY S/ROW AU LF	Weight Uom	g	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-0615	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	MICRO MNL HDR HSG SINGLE ROW				1.0	0.3066	g	
Material	2	PA4T-GF30-FR(40)				1.0	0.3066	g	
Substance	3	Carbon black	Supplier	1333-86-4	0.9	1.0	0.0027594	g	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	0.09198	g	
Substance	3	Polyamide 4T - ISO 1043-1 Term PA4T	Supplier	1043-1-PA4T	47.1	1.0	0.1444086	g	
Substance	3	Halogen-free organic phosphorus flame retardant - ISO 1043-4 code #FR(40)	Supplier	1043-4-FR40	12.0	1.0	0.036792	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	10.0	1.0	0.03066	g	
Sub-Item	1	Post Contact right angle lower				3.0	0.04513057	g	
Material	2	Brass				3.0	0.04394874	g	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	3.0	4.394874E-7	g	
Substance	3	Zinc	Supplier	7440-66-6	28.0225	3.0	0.01231554	g	
Substance	3	Manganese	Supplier	7439-96-5	0.05	3.0	2.197437E-5	g	
Substance	3	Antimony	Supplier	7440-36-0	0.01	3.0	4.394874E-6	g	
Substance	3	Iron	Supplier	7439-89-6	0.05	3.0	2.197437E-5	g	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	3.0	4.394874E-5	g	
Substance	3	Copper	Supplier	7440-50-8	71.5	3.0	0.03142335	g	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	3.0	4.394874E-7	g	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	3.0	4.394874E-6	g	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	3.0	2.197437E-7	g	
Substance	3	Nickel	Nickel	7440-02-0	0.2	3.0	8.789749E-5	g	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	3.0	2.197437E-6	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	3.0	2.197437E-5	g	
Material	2	Tin Plate				3.0	4.3088E-4	g	
Substance	3	Tin	Supplier	7440-31-5	99.73	3.0	4.2972E-4	g	

Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	3.0	8.61758E-7	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	3.0	3.016153E-7	g	
Material	2	Gold Plate				3.0	1.5035E-4	g	
Substance	3	Gold	Supplier	7440-57-5	99.7	3.0	1.499E-4	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	3.0	4.51056E-7	g	
Material	2	Nickel Plate				3.0	6.0059E-4	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	3.0	1.201184E-6	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	3.0	6.00592E-7	g	
Substance	3	Nickel	Nickel	7440-02-0	99.7	3.0	5.9879E-4	g	