



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	John R. Penica	Contact Title	Mgr. Global Product Compliance		
Company Unique ID	TE Connectivity	Response Date	2016-07-20	Contact Email	jrpenica@te.com				
Contact Phone Number	717-592-3266								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	8-1437657-8	Amount	26690.1	Version	-	Identity			
Manufacturer Item Name	8PCV-05-006=#8 TRIBARRIER	Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-1215	REACH Candidate Substances of Very High Concern ARE NOT Yet Reviewed								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Material	1	Tin_Plating				1.0	0.05	mg	
Substance	2	Tin	Supplier	7440-31-5	100.0	1.0	0.05	mg	
Material	1	Inulating body				1.0	11020.0	mg	
Substance	2	Antimony oxide (Sb2O3)	Supplier	1309-64-4	5.0	1.0	551.0	mg	
Substance	2	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	1.0	1.0	110.2	mg	
Substance	2	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	3306.0	mg	
Substance	2	1,4-Benzenedicarboxylic acid, polymer with 1,4-butanediol	Supplier	26062-94-2	55.0	1.0	6061.0	mg	
Substance	2	Carbonic dichloride, polymer with 4,4-(1-methylethylene)bis[2,6-dibromophenyl], bis(2,4,6-tribromophenyl) ester	Brominated Flame Retardants (other than PBBs or PBDEs)	71342-77-3	9.0	1.0	991.8	mg	
Material	1	Zinc_Plating				1.0	0.05	mg	
Substance	2	Chromium	Supplier	7440-47-3	1.0	1.0	5.0E-4	mg	
Substance	2	Zinc	Supplier	7440-66-6	99.0	1.0	0.0495	mg	
Material	1	Brass_Terminal				1.0	5140.0	mg	
Substance	2	Copper	Supplier	7440-50-8	68.0	1.0	3495.2	mg	
Substance	2	Zinc	Supplier	7440-66-6	32.0	1.0	1644.8	mg	
Material	1	Screw				1.0	10530.0	mg	
Substance	2	Carbon	Supplier	7440-44-0	0.19	1.0	20.007	mg	
Substance	2	Silicon	Supplier	7440-21-3	0.0070	1.0	0.7371	mg	
Substance	2	Aluminum	Supplier	7429-90-5	0.038	1.0	4.0014	mg	
Substance	2	Iron	Supplier	7439-89-6	98.89	1.0	10413.117	mg	
Substance	2	Sulfur	Supplier	7704-34-9	0.013	1.0	1.3689	mg	
Substance	2	Manganese	Supplier	7439-96-5	0.85	1.0	89.505	mg	
Substance	2	Phosphorus	Supplier	7723-14-0	0.012	1.0	1.2636	mg	