



<b>Form Type</b>	Distribute	<b>Version</b>	2.0	<b>Ref</b>	IPC 1752A	<b>Sectionals</b>	Material Info	<b>Subsectionals</b>	D, A
<b>Supplier Information</b>									
<b>Company Name</b>	TE Connectivity	<b>Request Document ID</b>		<b>Contact Name</b>	JOHN PENICA	<b>Contact Title</b>	Sr. Mgr. Global PEC_INDUSTRIAL		
<b>Company Unique ID</b>	TE Connectivity	<b>Response Date</b>	2016-06-06	<b>Contact Email</b>	jrpenica@tycoelectronics.com				
<b>Contact Phone Number</b>	717-592-3266								
<b>Legal Statement</b>									
<b>Supplier Acceptance</b>	true								
<b>Legal Statement</b>									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
<b>Product</b>									
<b>Manufacturer Item number</b>	1-215570-2	<b>Amount</b>	0.77136958	<b>Version</b>	-	<b>Identity</b>			
<b>Manufacturer Item Name</b>	MICRO-MATCH PBC.12P	<b>Weight Uom</b>	g	<b>Mfr Site</b>		<b>Authority</b>			
<b>Date</b>		<b>UOM</b>	Each						
<b>EUroHS-0508</b>	Product(s) meets EU RoHS requirement without any exemptions								
<b>ChinaRoHS-0508</b>	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
<b>EUREACH-0615</b>	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
<b>Product Disclosure</b>									
<b>Sub-Item/Material/Substance</b>	<b>Level</b>	<b>Name</b>	<b>Substance Category</b>	<b>Substance CAS</b>	<b>Substance Concentration</b>	<b>Quantity</b>	<b>Mass per Unit</b>	<b>UOM</b>	<b>Exemption</b>
Sub-Item	1	MICRO-MATCH P.B.HSG				1.0	0.27461	g	
Material	2	POLYESTER PBT				1.0	0.27461	g	
Substance	3	1,4-Benzenedicarb oxylie acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	54.0	1.0	0.1482894	g	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	19.0	1.0	0.0521759	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0506	4.0	1.0	0.0109844	g	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	4.0	1.0	0.0109844	g	
Substance	3	2-Propenoic acid, (2,3,4,5,6-pentabromoph enyl)methyl ester, homopolymer	Brominated Flame Retardants (other than PBBs or PBDEs)	59447-57-3	19.0	1.0	0.0521759	g	
Sub-Item	1	MICRO-MATCH M COVER				1.0	0.132	g	
Material	2	POLYESTER PBT				1.0	0.132	g	
Substance	3	1,4-Benzenedicarb oxylie acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	54.0	1.0	0.07128	g	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	19.0	1.0	0.02508	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0506	4.0	1.0	0.00528	g	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	4.0	1.0	0.00528	g	
Substance	3	2-Propenoic acid, (2,3,4,5,6-pentabromoph enyl)methyl ester, homopolymer	Brominated Flame Retardants (other than PBBs or PBDEs)	59447-57-3	19.0	1.0	0.02508	g	

Sub-Item	1	MICRO MATCH PB CONT				12.0	0.03039663	g	
Material	2	Nickel Plate				12.0	1.1413E-4	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	12.0	2.28264E-7	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	12.0	1.14132E-7	g	
Substance	3	Nickel	Nickel	7440-02-0	99.7	12.0	1.1379E-4	g	
Material	2	Tin Plate				12.0	1.825E-4	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	12.0	3.65E-7	g	
Substance	3	Tin	Supplier	7440-31-5	99.73	12.0	1.8201E-4	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	12.0	1.2775E-7	g	
Material	2	Phos Bronze				12.0	0.0301	g	
Substance	3	Copper	Supplier	7440-50-8	94.6985	12.0	0.02850425	g	
Substance	3	Manganese	Supplier	7439-96-5	0.02	12.0	6.02E-6	g	
Substance	3	Chromium	Supplier	7440-47-3	0.01	12.0	3.01E-6	g	
Substance	3	Tin	Supplier	7440-31-5	4.5	12.0	0.0013545	g	
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	12.0	1.505E-6	g	
Substance	3	Iron	Supplier	7439-89-6	0.1	12.0	3.01E-5	g	
Substance	3	Antimony	Supplier	7440-36-0	0.01	12.0	3.01E-6	g	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	12.0	3.01E-7	g	
Substance	3	Zinc	Supplier	7440-66-6	0.3	12.0	9.03E-5	g	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	12.0	3.01E-5	g	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	12.0	3.01E-5	g	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	12.0	1.505E-6	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	12.0	1.505E-5	g	
Substance	3	Nickel	Nickel	7440-02-0	0.1	12.0	3.01E-5	g	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	12.0	1.505E-7	g	