



<b>Form Type</b>	Distribute	<b>Version</b>	2.0	<b>Ref</b>	IPC 1752A	<b>Sectionals</b>	Material Info	<b>Subsectionals</b>	D, A
<b>Supplier Information</b>									
<b>Company Name</b>	TE Connectivity	<b>Request Document ID</b>		<b>Contact Name</b>	John R. Penica	<b>Contact Title</b>	Sr. Mgr. Global Product Environmental Compliance_ INDUSTRIAL		
<b>Company Unique ID</b>	TE Connectivity	<b>Response Date</b>	2016-08-03	<b>Contact Email</b>	jrpenica@te.com				
<b>Contact Phone Number</b>	717-592-3266								
<b>Legal Statement</b>									
<b>Supplier Acceptance</b>	true								
<b>Legal Statement</b>									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
<b>Product</b>									
<b>Manufacturer Item number</b>	2-34852-1	<b>Amount</b>	1180.185124	<b>Version</b>	-	<b>Identity</b>			
<b>Manufacturer Item Name</b>	TERMINAL,PG R 12-10 6	<b>Weight Uom</b>	mg	<b>Mfr Site</b>		<b>Authority</b>			
<b>Date</b>		<b>UOM</b>	Each						
<b>EUroHS-0508</b>	Product(s) meets EU RoHS requirement without any exemptions								
<b>ChinaRoHS-0508</b>	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
<b>EUREACH-1215</b>	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
<b>Product Disclosure</b>									
<b>Sub-Item/Material/Substance</b>	<b>Level</b>	<b>Name</b>	<b>Substance Category</b>	<b>Substance CAS</b>	<b>Substance Concentration</b>	<b>Quantity</b>	<b>Mass per Unit</b>	<b>UOM</b>	<b>Exemption</b>
Sub-Item	1	TERMINAL,BU DG R 12-10 6				1.0	1149.596324	mg	
Material	2	Copper				1.0	1143.0468	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.05	1.0	0.57152	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	0.01143047	mg	
Substance	3	Copper	Supplier	7440-50-8	99.7575	1.0	1140.27491	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.01143047	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	1.0	0.05715234	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.1143	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	0.22861	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	1.14305	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.57152	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.00571523	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	0.05715234	mg	
Material	2	Tin Plate				1.0	6.549524	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	1.0	6.53184	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.01309905	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	1.0	0.00458467	mg	
Sub-Item	1	TUBING EXTRUDED				1.0	30.5888	mg	
Material	2	PVC				1.0	30.435856	mg	
Substance	3	Ethene, chloro-	Supplier	75-01-4	4.0E-4	1.0	1.2174E-4	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	7.5	1.0	2.28269	mg	
Substance	3	Ethene, chloro-, homopolymer	Supplier	9002-86-2	87.9961	1.0	26.78237	mg	
Substance	3	8-Oxa-3,5-dithia-4-stannatetradecanoic acid, 10-ethyl-4,4-dimethyl-7-oxo-, 2-ethylhexyl ester	Supplier	57583-35-4	1.5	1.0	0.45654	mg	

Substance	3	Octadecanoic acid, calcium salt (2:1)	Supplier	1592-23-0	0.5	1.0	0.15218	mg	
Substance	3	Calcium hydroxide (Ca(OH)2)	Supplier	1305-62-0	0.0035	1.0	0.00106525	mg	
Substance	3	8-Oxa-3,5-dithia-4-stannatetradecanoic acid, 10-ethyl-4-[[[2-(2-ethylhexyl)oxy]-2-oxoethyl]thio]-4-methyl-7-oxo-, 2-ethylhexyl ester	Supplier	57583-34-3	0.5	1.0	0.15218	mg	
Substance	3	Limestone	Supplier	1317-65-3	2.0	1.0	0.60872	mg	
Material	2	COLORANT				1.0	0.152944	mg	
Substance	3	Octadecanoic acid, calcium salt (2:1)	Supplier	1592-23-0	1.0	1.0	0.00152944	mg	
Substance	3	Aluminum oxide (Al2O3)	Supplier	1344-28-1	0.1	1.0	1.5294E-4	mg	
Substance	3	Ethene, chloro-	Supplier	75-01-4	4.0E-4	1.0	1.0E-5	mg	
Substance	3	8-Oxa-3,5-dithia-4-stannatetradecanoic acid, 10-ethyl-4-[[[2-(2-ethylhexyl)oxy]-2-oxoethyl]thio]-4-methyl-7-oxo-, 2-ethylhexyl ester	Supplier	57583-34-3	0.9	1.0	0.0013765	mg	
Substance	3	Octadecanoic acid, zinc salt (2:1)	Supplier	557-05-1	0.2	1.0	3.0589E-4	mg	
Substance	3	8-Oxa-3,5-dithia-4-stannatetradecanoic acid, 10-ethyl-4,4-dimethyl-7-oxo-, 2-ethylhexyl ester	Supplier	57583-35-4	0.9	1.0	0.0013765	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	6.5	1.0	0.00994136	mg	
Substance	3	Ethene, chloro-, homopolymer	Supplier	9002-86-2	70.5996	1.0	0.10798	mg	
Substance	3	Aluminate (Al(OH)63-), (OC-6-11)-, magnesium carbonate hydroxide (2:6:1:4)	Supplier	11097-59-9	0.7	1.0	0.00107061	mg	
Substance	3	Ethene, homopolymer, oxidized	Supplier	68441-17-8	1.7	1.0	0.00260005	mg	
Substance	3	Zeolites	Supplier	1318-02-1	0.1	1.0	1.5294E-4	mg	
Substance	3	Titanium oxide (TiO2)	Supplier	13463-67-7	12.0	1.0	0.01835328	mg	
Substance	3	Silica	Supplier	7631-86-9	0.3	1.0	4.5883E-4	mg	
Substance	3	Benzenesulfonic acid, 4-[[[1-[[[2-(2-chlorophenyl)amino]carbonyl]-2-oxop...	Supplier	71832-85-4	5.0	1.0	0.0076472	mg	