



<b>Form Type</b>	Distribute	<b>Version</b>	2.0	<b>Ref</b>	IPC 1752A	<b>Sectionals</b>	Material Info	<b>Subsectionals</b>	D, A
<b>Supplier Information</b>									
<b>Company Name</b>	TE Connectivity	<b>Request Document ID</b>		<b>Contact Name</b>	John R. Penica	<b>Contact Title</b>	Engineer Product Compliance china		
<b>Company Unique ID</b>	TE Connectivity	<b>Response Date</b>	2016-07-08	<b>Contact Email</b>	cc.wu@te.com				
<b>Contact Phone Number</b>	86-2124071672								
<b>Legal Statement</b>									
<b>Supplier Acceptance</b>	true								
<b>Legal Statement</b>									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
<b>Product</b>									
<b>Manufacturer Item number</b>	3-1879214-3	<b>Amount</b>	0.542309	<b>Version</b>	-	<b>Identity</b>			
<b>Manufacturer Item Name</b>	CPF 0402 698R 0.1% 25PPM 1K RL	<b>Weight Uom</b>	mg	<b>Mfr Site</b>		<b>Authority</b>			
<b>Date</b>		<b>UOM</b>	Each						
<b>EUroHS-0508</b>	Product(s) meets EU RoHS requirement without any exemptions								
<b>ChinaRoHS-0508</b>	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
<b>EUREACH-0615</b>	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
<b>Product Disclosure</b>									
<b>Sub-Item/Material/Substance</b>	<b>Level</b>	<b>Name</b>	<b>Substance Category</b>	<b>Substance CAS</b>	<b>Substance Concentration</b>	<b>Quantity</b>	<b>Mass per Unit</b>	<b>UOM</b>	<b>Exemption</b>
Material	1	Tin Plating				1.0	0.00341655	mg	
Substance	2	Tin	Supplier	7440-31-5	100.0	1.0	0.00341655	mg	
Material	1	Upside Electrode				1.0	0.00623113	mg	
Substance	2	Ethanol, 2-(2-butoxyethoxy)-	Supplier	112-34-5	20.0	1.0	0.00124623	mg	
Substance	2	Copper oxide (CuO)	Supplier	1317-38-0	10.0	1.0	6.2311E-4	mg	
Substance	2	Terpineol	Supplier	8000-41-7	15.0	1.0	9.3467E-4	mg	
Substance	2	Silver	Supplier	7440-22-4	55.0	1.0	0.00342712	mg	
Material	1	Substrate				1.0	0.51998928	mg	
Substance	2	Aluminum oxide (Al2O3)	Supplier	1344-28-1	96.0	1.0	0.49919	mg	
Substance	2	Quartz (SiO2)	Supplier	14808-60-7	3.0	1.0	0.01559968	mg	
Substance	2	Magnesium oxide (MgO)	Supplier	1309-48-4	1.0	1.0	0.00519989	mg	
Material	1	Backside Electrode				1.0	0.00623113	mg	
Substance	2	Ethanol, 2-(2-butoxyethoxy)-	Supplier	112-34-5	20.0	1.0	0.00124623	mg	
Substance	2	Copper oxide (CuO)	Supplier	1317-38-0	10.0	1.0	6.2311E-4	mg	
Substance	2	Terpineol	Supplier	8000-41-7	15.0	1.0	9.3467E-4	mg	
Substance	2	Silver	Supplier	7440-22-4	55.0	1.0	0.00342712	mg	
Material	1	Resistor Layer				1.0	4.034779E-6	mg	
Substance	2	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	100.0	1.0	1.0E-5	mg	
Material	1	Edge Electrode				1.0	5.097705E-6	mg	
Substance	2	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	100.0	1.0	1.0E-5	mg	
Material	1	Nickel Plating				1.0	0.00144797	mg	
Substance	2	Nickel	Nickel	7440-02-0	100.0	1.0	0.00144797	mg	
Material	1	Overcoat				1.0	0.00498382	mg	
Substance	2	Ethanol, 2-(2-butoxyethoxy)-	Supplier	112-34-5	12.0	1.0	5.9806E-4	mg	
Substance	2	Carbon black	Supplier	1333-86-4	3.0	1.0	1.4951E-4	mg	
Substance	2	Resin acids and Rosin acids	Supplier	73138-82-6	35.0	1.0	0.00174434	mg	
Substance	2	Acetamide	Supplier	60-35-5	20.0	1.0	9.9676E-4	mg	

Substance	2	Talc (Mg <sub>3</sub> H <sub>2</sub> (SiO <sub>3</sub> ) <sub>4</sub> )	Supplier	14807-96-6	10.0	1.0	4.9838E-4	mg	
Substance	2	Silica, vitreous	Supplier	60676-86-0	20.0	1.0	9.9676E-4	mg	