



<b>Form Type</b>	Distribute	<b>Version</b>	2.0	<b>Ref</b>	IPC 1752A	<b>Sectionals</b>	Material Info	<b>Subsectionals</b>	D, A
<b>Supplier Information</b>									
<b>Company Name</b>	TE Connectivity	<b>Request Document ID</b>		<b>Contact Name</b>	Benfer, David W	<b>Contact Title</b>	Staff Mfg & Process Dvl Engineer, Eng Proc Opt/LEANPD		
<b>Company Unique ID</b>	TE Connectivity	<b>Response Date</b>	2017-01-27	<b>Contact Email</b>	dave.benfer@te.com				
<b>Contact Phone Number</b>	+1-717-986-3725								
<b>Legal Statement</b>									
<b>Supplier Acceptance</b>	true								
<b>Legal Statement</b>									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
<b>Product</b>									
<b>Manufacturer Item number</b>	1-87224-4	<b>Amount</b>	974.33	<b>Version</b>	-	<b>Identity</b>			
<b>Manufacturer Item Name</b>	14 MODII HDR SRST UNSHRD .100	<b>Weight Uom</b>	mg	<b>Mfr Site</b>		<b>Authority</b>			
<b>Date</b>		<b>UOM</b>	Each						
<b>EUroHS-0508</b>	Product(s) meets EU RoHS requirement without any exemptions								
<b>ChinaRoHS-0508</b>	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
<b>EUREACH-1215</b>	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
<b>Product Disclosure</b>									
<b>Sub-Item/Material/Substance</b>	<b>Level</b>	<b>Name</b>	<b>Substance Category</b>	<b>Substance CAS</b>	<b>Substance Concentration</b>	<b>Quantity</b>	<b>Mass per Unit</b>	<b>UOM</b>	<b>Exemption</b>
Sub-Item	1	MODII POST PLTD 15 AU				14.0	55.14	mg	
Material	2	Phos Bronze				14.0	54.392	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6985	14.0	51.50841	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	14.0	0.0108784	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	14.0	0.0054392	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	14.0	2.44764	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	14.0	0.0027196	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	14.0	0.054392	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	14.0	0.0054392	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	14.0	5.4392E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	14.0	0.16318	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	14.0	0.054392	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	14.0	0.054392	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	14.0	0.0027196	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	14.0	0.027196	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	14.0	0.054392	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	14.0	2.7196E-4	mg	
Material	2	Gold Plate				14.0	0.017	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.1	14.0	1.7E-5	mg	
Substance	3	Gold	Supplier	7440-57-5	99.9	14.0	0.016983	mg	
Material	2	Nickel Plate				14.0	0.596	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	14.0	0.001192	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	14.0	5.96E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	14.0	0.59421	mg	
Material	2	Gold Plate				14.0	0.135	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	14.0	0.13459	mg	

Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	14.0	4.05E-4	mg	
Sub-Item	1	Nylon Compound				1.0	202.37	mg	
Material	2	PA66-GF25				1.0	202.37	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	23.95	1.0	48.46761	mg	
Substance	3	Poly[imino(1-oxo-1,6-hexanediy)]	Supplier	25038-54-4	0.945	1.0	1.9124	mg	
Substance	3	Siloxanes and Silicones, di-Me	Supplier	63148-62-9	0.0020	1.0	0.0040474	mg	
Substance	3	1,4:7,10-Dimethanodibenzocyclooctene, 1,2,3,4,7,8,9,10,13,13,14,14-dodecachloro-1,4,4a,5,6,6a,7,10,10a,11,12,12a-dodecahydro-	Supplier	13560-89-9	14.17	1.0	28.67583	mg	
Substance	3	Hexanedioic acid, polymer with hexahydro-2H-azepin-2-one and 1,6-hexanediamine	Supplier	24993-04-2	51.993	1.0	105.21823	mg	
Substance	3	1,2-Benzenedicarboxylic acid, 1,2-diundecyl ester, branched and linear	Supplier	85507-79-5	1.43	1.0	2.89389	mg	
Substance	3	Carbon black	Supplier	1333-86-4	0.49	1.0	0.99161	mg	
Substance	3	Boric acid, zinc salt	Supplier	1332-07-6	2.1	1.0	4.24977	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	4.81	1.0	9.734	mg	
Substance	3	Aluminum, hydroxybis(octadecanoato-kappa-O)-	Supplier	300-92-5	0.1	1.0	0.20237	mg	
Substance	3	Copper iodide (CuI)	Supplier	7681-65-4	0.01	1.0	0.020237	mg	