

PART INFORMATION	
Mfg Item Number	MRF1K50HR5
Mfg Item Name	NI-1230
SUPPLIER	
Company Name	Freescale Semiconductor Inc
Company Unique ID	14-141-7928
Response Date	2016-08-25
Response Document ID	0040K10565D006A1.0
Contact Name	Freescale Semiconductor Inc
Contact Title	Product Technical Support
Contact Phone	1-800-521-6274
Contact Email	support@freescale.com
Authorized Representative	Daniel Binyon
Representative Title	EPP Customer Response
Representative Phone	512-895-3406
Representative Email	eppanlst@freescale.com
URL for Additional Information	www.freescale.com
DECLARATION	
EU RoHS	Yes
Pb Free	Yes
HalogenFree	Yes
Plating Indicator	e4
EU RoHS Exemption(s)	
MANUFACTURING	
Mfg Item Number	MRF1K50HR5
Mfg Item Name	NI-1230
Version	ALL
Weight	13.155200
UoM	g
Unit Volume	EACH
J-STD-020 MSL Rating	
Peak Processing Temperature	260 C
Max Time at Peak Temperature	40 seconds
Number of Processing Cycles	3

RoHS	
RoHS Directive	2011/65/EU
RoHS Definition	RoHS Definition: Quantity limit of 0.1% by mass (1000 PPM) of homogeneous material for: Lead (Pb), Mercury, Hexavalent Chromium, Polybrominated Biphenyls (PBB), Polybrominated Diphenyl Ethers (PBDE) and quantity limit of 0.01% by mass (100 PPM) of homogeneous material of Cadmium
RoHS Legal Definition	Please indicate whether any homogeneous material (as defined by the RoHS Directive, EU 2011/65/EU and implemented by the laws of the European Union member states) of the part(s) identified on this form contains lead, mercury, cadmium, hexavalent chromium, polybrominated biphenyls and/or polybrominated diphenyl ethers (each a RoHS restricted substance) in excess of the applicable quantity limit identified below. If a homogeneous material within the part(s) contains a RoHS restricted substance in excess of an applicable quantity limit, please indicate below which, if any, RoHS exemption you believe may apply. If the part is an assembly with lower level components, the declaration shall encompass all such components. Supplier certifies that it gathered the information it provides in this form using appropriate methods to ensure its accuracy and that such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products with European Union member state laws that implement the RoHS Directive. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part(s), and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part(s), the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Suppliers liability and the Companys remedies for issues that arise regarding information the Supplier provides in this form. In the absence of such written agreement, the warranty rights and/or remedies of Suppliers Standard Terms and Conditions of Sale applicable to such part(s) shall apply.
RoHS Declaration	1 - Item(s) do not contain RoHS restricted substances per the definition above
Supplier Acceptance	Accepted
Signature	Daniel Binyon
Exemption List Version	2012/51/EU
List of Freescale Accepted Exemptions	6(a) : Lead as an alloying element in steel for machining purposes and in galvanized steel containing up to 0.35% lead by weight 6(b) : Lead as an alloying element in aluminium containing up to 0.4% lead by weight 6(c) : Copper alloy containing up to 4% lead by weight 7(a) : Lead in high melting temperature type solders (i.e. lead-based alloys containing 85% by weight or more lead) 7(b) : Lead in solders for servers, storage and storage array systems, network infrastructure equipment for switching, signaling, transmission, and network management for telecommunications 7(c)-I : Electrical and electronic components containing lead in a glass or ceramic other than dielectric ceramic in capacitors, e.g. piezoelectronic devices, or in a glass or ceramic matrix compound 7(c)-II : Lead in dielectric ceramic in capacitors for a rated voltage of 125 V AC or 250 V DC or higher 7(c)-III : Lead in dielectric ceramic in capacitors for a rated voltage of less than 125 V AC or 250 V DC 7(c)-IV : Lead in PZT based dielectric ceramic materials for capacitors being part of integrated circuits or discrete semiconductors 15 : Lead in solders to complete a viable electrical connection between semiconductor die and carrier within integrated circuit flip chip packages

MATERIAL COMPOSITION

Homogeneous Material	Weight	SubstanceClass	Substance	CAS	Exemption	SubstanceWeight	UoM	SubPart PPM	SubPart%		ARTICLEPPM	ARTICLE%
Cap/Cover	1.7943						g					
Cap/Cover		Metals	Aluminum Oxides (Al2O3)	1344-28-1		1.70352636	g	949410	94.941		129494	12.9494
Cap/Cover		Solvents, additives, and other materials	Calcium monoxide	1305-78-8		0.00353477	g	1970	0.197		268	0.0268
Cap/Cover		Plastics/polymers	Proprietary Material-Other Epoxy resins	-		0.02715494	g	15134	1.5134		2064	0.2064
Cap/Cover		Metals	Magnesium-oxide	1309-48-4		0.01767206	g	9849	0.9849		1343	0.1343
Cap/Cover		Glass	Silica, crystalline - quartz (SiO2)	14808-60-7		0.04241187	g	23637	2.3637		3223	0.3223
Bonding Wire, Aluminum	0.0022						g					
Bonding Wire, Aluminum		Metals	Aluminum, metal	7429-90-5		0.0022	g	1000000	100		167	0.0167
Header Assembly	11.34						g					
Header Assembly		Metals	Aluminum Oxides (Al2O3)	1344-28-1		0.41043996	g	36194	3.6194		31199	3.1199
Header Assembly		Metals	Copper, metal	7440-50-8		4.8831174	g	430610	43.061		371192	37.1192
Header Assembly		Metals	Gold, metal	7440-57-5		0.0756378	g	6670	0.667		5749	0.5749
Header Assembly		Metals	Iron, metal	7439-89-6		0.45736488	g	40332	4.0332		34766	3.4766
Header Assembly		Metals	Molybdenum, metal	7439-98-7		5.09195484	g	449026	44.9026		387077	38.7077
Header Assembly		Nickel (external applications only)	Nickel	7440-02-0		0.23522562	g	20743	2.0743		17880	1.788
Header Assembly		Metals	Tungsten, metal	7440-33-7		0.1862595	g	16425	1.6425		14158	1.4158
Silicon Semiconductor Die	0.0187						g					
Silicon Semiconductor Die		Metals	Gold, metal	7440-57-5		0.00019074	g	10200	1.02		14	0.0014
Silicon Semiconductor Die		Solvents, additives, and other materials	Other miscellaneous substances (less than 5%).	-		0.00037019	g	19796	1.9796		28	0.0028
Silicon Semiconductor Die		Glass	Silicon, doped	-		0.01813907	g	970004	97.0004		1378	0.1378

LINKS	
MCD LINK	
NXP website	http://www.nxp.com
GENERAL ENVIRONMENTAL COMPLIANCE LINKS	
RoHS signed letter	http://www.nxp.com/files/corporate/doc/support_info/NXP-ROHS-DECLARATION.pdf
China RoHS	http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization/china-rohs:ENV_CHINA_ROHS_STRATEGY
REACH signed letter	http://www.nxp.com/files/corporate/doc/support_info/NXP-REACH-STATEMENT.pdf
ELV signed letter	http://www.nxp.com/files/corporate/doc/support_info/NXP-ELV-STATEMENT.pdf
Conflict Minerals statement	http://www.nxp.com/files/corporate/doc/support_info/NXP-STATEMENT-CONFLICT-MINERALS.pdf
NXP ENVIRONMENTAL INFORMATION	
Environmental Compliance website	http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization:ABUENVPRFPRDX
FAQ	http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization/eco-product-faqs:ENVIRON_FAQ
Technical Service Request	http://www.nxp.com/support/sales-and-support:SUPPORTHOME
LINKS TO BLANK IPC1752 FORMS	
Blank IPC1752 v1.1 Form	http://www.NXP.com/files/abstract/corporate/ehs_epp/IPC-1752-2_v1.1_MCD_Template.pdf

IPC1752 XML LINKS

http://www.freescale.com/mcds/MRF1K50HR5_IPC1752_v11.xml

http://www.freescale.com/mcds/MRF1K50HR5_IPC1752A.xml