



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A																									
Supplier Information																																		
Company Name	TE Connectivity	Request Document ID		Contact Name	Wu, Cc	Contact Title	Engineer Product Compliance china																											
Company Unique ID	TE Connectivity	Response Date	2016-09-01	Contact Email	cc.wu@te.com																													
Contact Phone Number		86-2124071672																																
Legal Statement																																		
Supplier Acceptance	true																																	
Legal Statement																																		
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.																																		
Product																																		
Manufacturer Item number	41274-1	Amount	969.893	Version	-	Identity																												
Manufacturer Item Name	FASTON 250 REC 18-14 AWG TPBR	Weight Uom	mg	Mfr Site		Authority																												
Date		UOM	Each																															
EUROHS-0508	Product(s) meets EU RoHS requirement without any exemptions																																	
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products																																	
EUREACH-1215	REACH Candidate Substances of Very High Concern ARE NOT Yet Reviewed																																	
Product Disclosure																																		
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption																									
Material	1	Brass				1.0	966.07	mg																										
Substance	2	Chromium	Supplier	7440-47-3	0.0010	1.0	0.0096607	mg																										
Substance	2	Zinc	Supplier	7440-66-6	28.0225	1.0	270.71697	mg																										
Substance	2	Manganese	Supplier	7439-96-5	0.05	1.0	0.48303	mg																										
Substance	2	Antimony	Supplier	7440-36-0	0.01	1.0	0.096607	mg																										
Substance	2	Iron	Supplier	7439-89-6	0.05	1.0	0.48303	mg																										
Substance	2	Cobalt	Supplier	7440-48-4	0.1	1.0	0.96607	mg																										
Substance	2	Copper	Supplier	7440-50-8	71.5	1.0	690.74005	mg																										
Substance	2	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.0096607	mg																										
Substance	2	Arsenic	Supplier	7440-38-2	0.01	1.0	0.096607	mg																										
Substance	2	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.00483035	mg																										
Substance	2	Nickel	Nickel	7440-02-0	0.2	1.0	1.93214	mg																										
Substance	2	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	0.0483035	mg																										
Substance	2	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.48303	mg																										
Material	1	Tin Plate				1.0	3.823	mg																										
Substance	2	Tin	Supplier	7440-31-5	99.73	1.0	3.81268	mg																										
Substance	2	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.007646	mg																										
Substance	2	Lead	Lead/Lead Compounds	7439-92-1	0.07	1.0	0.0026761	mg																										