



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Dong, Rebecca	Contact Title	Prod Compliance Engineer		
Company Unique ID	TE Connectivity	Response Date	2017-01-23	Contact Email	Rebecca_dong@te.com				
Contact Phone Number	86-2133259330								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	5175472-8	Amount	5840.0	Version	-	Identity			
Manufacturer Item Name	CHAMP 050 B/B PLUG H W/LEG 68P	Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-1215	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	CHAMP 050 PLUG HSG 68P H				1.0	3060.0	mg	
Material	2	PA66-GF20FR				1.0	3060.0	mg	
Substance	3	2,5-Furandione, polymers with hydrogenated butadiene-styrene polymer, block, graft	Supplier	113569-15-6	2.0	1.0	61.2	mg	
Substance	3	Poly(oxy-1,2-ethanediyl), .alpha.-hydro-.omega.-hydroxy-	Supplier	25322-68-3	0.1	1.0	3.06	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	10.0	1.0	306.0	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	20.0	1.0	612.0	mg	
Substance	3	Benzene, ethenyl-, homopolymer, brominated	Supplier	88497-56-7	25.0	1.0	765.0	mg	
Substance	3	Carbon black	Supplier	1333-86-4	1.5	1.0	45.9	mg	
Substance	3	Poly[imino(1,6-dioxo-1,6-hexanediyl)imino-1,6-hexanediyl]	Supplier	32131-17-2	36.9	1.0	1129.14	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	3.0	1.0	91.8	mg	
Substance	3	Benzenepropamide, N,N-1,6-hexanediylbis[3,5-bis(1,1-dimethylethyl)-4-hydroxy-	Supplier	23128-74-7	0.5	1.0	15.3	mg	
Substance	3	Octadecanoic acid, calcium salt (2:1)	Supplier	1592-23-0	1.0	1.0	30.6	mg	
Sub-Item	1	CHAMP 050 B-T-B PLUG CONT H AU				34.0	25.0	mg	

Material	2	Tin Plate				34.0	0.4	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	34.0	8.0E-4	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	34.0	0.39892	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	34.0	2.8E-4	mg	
Material	2	Gold Plate				34.0	0.02	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	34.0	0.01994	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	34.0	6.0E-5	mg	
Material	2	Phos Bronze				34.0	24.28	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6985	34.0	22.9928	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	34.0	0.004856	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	34.0	0.002428	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	34.0	1.0926	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	34.0	0.001214	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	34.0	0.02428	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	34.0	0.002428	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	34.0	2.428E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	34.0	0.07284	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	34.0	0.02428	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	34.0	0.02428	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	34.0	0.001214	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	34.0	0.01214	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	34.0	0.02428	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	34.0	1.214E-4	mg	
Material	2	Nickel Plate				34.0	0.3	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	34.0	6.0E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	34.0	3.0E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	34.0	0.2991	mg	
Sub-Item	1	RETENTION LEG				2.0	95.0	mg	
Material	2	Tin Plate				2.0	0.5925	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	2.0	0.001185	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	2.0	0.5909	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	2.0	4.1475E-4	mg	
Material	2	Brass				2.0	93.4745	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	2.0	9.3474E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	28.0225	2.0	26.19389	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.05	2.0	0.04673725	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	2.0	0.00934745	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	2.0	0.04673725	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	2.0	0.0934745	mg	
Substance	3	Copper	Supplier	7440-50-8	71.5	2.0	66.83427	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	2.0	9.3474E-4	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	2.0	0.00934745	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	2.0	4.6737E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.2	2.0	0.18695	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	2.0	0.00467373	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	2.0	0.04673725	mg	
Material	2	Nickel Plate				2.0	0.933	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	2.0	0.001866	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	2.0	9.33E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	2.0	0.9302	mg	

Sub-Item	1	CHAMP 050 TINE PLATE 68P				1.0	890.0	mg	
Material	2	PBT-I-GF30- FR(17)				1.0	890.0	mg	
Substance	3	Dolomite (CaMg(CO3)2)	Supplier	16389-88-1	0.5	1.0	4.45	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	35.0	1.0	311.5	mg	
Substance	3	Benzenepropa noic acid, 3,5- bis(1,1- dimethylethyl)- 4-hydroxy-, 1,1-[2,2-bis[[3- [3,5-bis(1,1- dimethylethyl)- 4- hydroxyphenyl] -1- oxopropoxy]me thyl]-1,3- propanediyl] ester	Supplier	6683-19-8	0.2	1.0	1.78	mg	
Substance	3	Furan, tetrahydro-	Supplier	109-99-9	0.2	1.0	1.78	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2- 1212	3.0	1.0	26.7	mg	
Substance	3	Talc (Mg3H2(SiO3) 4)	Supplier	14807-96-6	2.0	1.0	17.8	mg	
Substance	3	Ethene, 1,1,2,2- tetrafluoro-, homopolymer	Supplier	9002-84-0	1.0	1.0	8.9	mg	
Substance	3	Chlorite-group minerals	Supplier	1318-59-8	0.5	1.0	4.45	mg	
Substance	3	Carbon black	Supplier	1333-86-4	1.0	1.0	8.9	mg	
Substance	3	1,4- Benzenedicarb oxylic acid, 1,4- dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	36.6	1.0	325.74	mg	
Substance	3	Phosphoric acid, zinc salt (2:3)	Supplier	7779-90-0	0.5	1.0	4.45	mg	
Substance	3	Aromatic Brominated flame retardant with Antimony - ISO 1043-4 code #FR(17)	Supplier	1043-4-FR17	18.0	1.0	160.2	mg	
Substance	3	Quartz (SiO2)	Supplier	14808-60-7	0.5	1.0	4.45	mg	
Substance	3	2- Propenenitrile, polymer with ethenylbenzen e	Supplier	9003-54-7	1.0	1.0	8.9	mg	
Sub-Item	1	CHAMP 050 B- T-B PLUG CONT H AU				34.0	25.0	mg	
Material	2	Tin Plate				34.0	0.4	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2- 1212	0.2	34.0	8.0E-4	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	34.0	0.39892	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	34.0	2.8E-4	mg	
Material	2	Gold Plate				34.0	0.02	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	34.0	0.01994	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2- 1212	0.3	34.0	6.0E-5	mg	
Material	2	Phos Bronze				34.0	24.28	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6985	34.0	22.9928	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	34.0	0.004856	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	34.0	0.002428	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	34.0	1.0926	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	34.0	0.001214	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	34.0	0.02428	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	34.0	0.002428	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	34.0	2.428E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	34.0	0.07284	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	34.0	0.02428	mg	

Substance	3	Cobalt	Supplier	7440-48-4	0.1	34.0	0.02428	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	34.0	0.001214	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	34.0	0.01214	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	34.0	0.02428	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	34.0	1.214E-4	mg	
Material	2	Nickel Plate				34.0	0.3	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	34.0	6.0E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	34.0	3.0E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	34.0	0.2991	mg	