



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Benfer, David W	Contact Title	Staff Mfg & Process Dvl Engineer, Eng Proc Opt/LEANPD		
Company Unique ID	TE Connectivity	Response Date	2017-01-24	Contact Email	dave.benfer@te.com				
Contact Phone Number	+1-717-986-3725								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	5558872-1	Amount	2088.514642	Version	-	Identity			
Manufacturer Item Name	MJ,TE,4P,W/O PNL STOPS	Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-1215	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	TERMINAL,TO P ENTRY,MOD JK				1.0	38.132356	mg	
Material	2	Nickel Plate				1.0	0.272452	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	2.7245E-4	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	5.449E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	0.27163	mg	
Material	2	Gold Plate				1.0	0.0116143	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	1.0	3.48429E-5	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	1.0	0.01157946	mg	
Material	2	Phos Bronze				1.0	37.67	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.03767	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.003767	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.2	1.0	0.07534	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	1.0	0.0018835	mg	
Substance	3	Copper	Supplier	7440-50-8	90.0485	1.0	33.92127	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	0.007534	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.35	1.0	0.13185	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	3.767E-4	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	1.0	0.03767	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	1.0	0.003767	mg	
Substance	3	Tin	Supplier	7440-31-5	9.0	1.0	3.3903	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	1.0	0.03767	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	1.8835E-4	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	0.0018835	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.018835	mg	
Material	2	Tin Plate				1.0	0.17829	mg	

Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	3.5658E-4	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	1.0	0.17781	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	1.0	1.248E-4	mg	
Sub-Item	1	HSG, TOP ENTRY, 4POS, FLGLS				1.0	2050.382286	mg	
Material	2	PBT-GF20-FR(17)				1.0	2050.382286	mg	
Substance	3	Benzenepropanoic acid, 3,5-bis(1,1-dimethylethyl)-4-hydroxy-, 1,1-[2,2-bis[[3-[3,5-bis(1,1-dimethylethyl)-4-hydroxyphenyl]-1-oxopropoxy]methyl]-1,3-propanediyl] ester	Supplier	6683-19-8	0.2	1.0	4.10076	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	25.0	1.0	512.59557	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	5.0	1.0	102.51911	mg	
Substance	3	Ethene, 1,1,2,2-tetrafluoro-, homopolymer	Supplier	9002-84-0	0.5	1.0	10.25191	mg	
Substance	3	2-Propenenitrile, polymer with ethenylbenzene	Supplier	9003-54-7	0.5	1.0	10.25191	mg	
Substance	3	Phosphoric acid, zinc salt (2:1)	Supplier	13598-37-3	0.3	1.0	6.15115	mg	
Substance	3	Carbon black	Supplier	1333-86-4	1.5	1.0	30.75573	mg	
Substance	3	Aromatic Brominated flame retardant with Antimony - ISO 1043-4 code #FR(17)	Supplier	1043-4-FR17	17.0	1.0	348.56499	mg	
Substance	3	Furan, tetrahydro-	Supplier	109-99-9	0.2	1.0	4.10076	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	5.0	1.0	102.51911	mg	
Substance	3	Ethene, homopolymer	Supplier	9002-88-4	5.0	1.0	102.51911	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	39.796	1.0	815.97013	mg	
Substance	3	Arsenic oxide (As2O3)	Arsenic oxide (As2O3)	1327-53-3	0.0020	1.0	0.04100765	mg	
Substance	3	Lead oxide (lead monoxide)	Lead/Lead Compounds	1317-36-8	0.0020	1.0	0.04100765	mg	