


D


C

B

A



- 1
- TRUE POSITION TOLERANCE OF THE POST TIPS APPLIES WHEN THE HEADERS ARE HELD FLAT AGAINST THE PRINTED CIRCUIT BOARD.
- 2
- ASSEMBLY MAY BE BROKEN TO THE DESIRED NUMBER OF POSITIONS.
- 3
- .000100-.000200 MATTE TIN-LEAD OVER .000050 NICKEL.
- 4
- .000100-.000200 BRIGHT TIN OVER .000050 NICKEL.
- 5
- PRELIMINARY PART - NOT RELEASED FOR PRODUCTION.
- 6
- HOUSING MATERIAL: FLAME RETARDANT THERMOPLASTIC; COLOR-BLACK.
- 7
- OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



RECOMMENDED HOLE LAYOUT

REVISIONS					
P	LTR	DESCRIPTION		DATE	DWN APVD
	P5	REVISED	PER ECO-16-012733	01SEP2016	NK MM

7	OBSOLETE	4	1.684	1.600	16	34	4-103328-9
		4	1.284	1.200	12	26	4-103328-8
		4	.884	.800	8	18	4-103328-7
		4	.584	.500	5	12	4-103328-6
		5	3.984	3.900	39	80	4-103328-5
4		4	.984	.900	9	20	4-103328-4
		4	.684	.600	6	14	4-103328-3
		4	.284	.200	2	6	4-103328-2
		4	.084	---	---	2	4-103328-1
		3	3.984	3.900	39	80	4-103328-0
7	OBSOLETE	3	3.884	3.800	38	78	3-103328-9
7	OBSOLETE	3	3.784	3.700	37	76	3-103328-8
7	OBSOLETE	3	3.684	3.600	36	74	3-103328-7
7	OBSOLETE	3	3.584	3.500	35	72	3-103328-6
3		3	3.484	3.400	34	70	3-103328-5
		3	3.384	3.300	33	68	3-103328-4
		3	3.284	3.200	32	66	3-103328-3
		3	3.184	3.100	31	64	3-103328-2
		3	3.084	3.000	30	62	3-103328-1
7	OBSOLETE	3	2.984	2.900	29	60	3-103328-0
7	OBSOLETE	3	2.884	2.800	28	58	2-103328-9
7	OBSOLETE	3	2.784	2.700	27	56	2-103328-8
7	OBSOLETE	3	2.684	2.600	26	54	2-103328-7
7	OBSOLETE	3	2.584	2.500	25	52	2-103328-6
3		3	2.484	2.400	24	50	2-103328-5
		3	2.384	2.300	23	48	2-103328-4
		3	2.284	2.200	22	46	2-103328-3
		3	2.184	2.100	21	44	2-103328-2
		3	2.084	2.000	20	42	2-103328-1
3		3	1.984	1.900	19	40	2-103328-0
		3	1.884	1.800	18	38	1-103328-9
		3	1.784	1.700	17	36	1-103328-8
		3	1.684	1.600	16	34	1-103328-7
		3	1.584	1.500	15	32	1-103328-6
7	OBSOLETE	3	1.484	1.400	14	30	1-103328-5
		3	1.384	1.300	13	28	1-103328-4
		3	1.284	1.200	12	26	1-103328-3
		3	1.184	1.100	11	24	1-103328-2
		3	1.084	1.000	10	22	1-103328-1
3		3	.984	.900	9	20	1-103328-0
		3	.884	.800	8	18	103328-9
		3	.784	.700	7	16	103328-8
		3	.684	.600	6	14	103328-7
		3	.584	.500	5	12	103328-6
3		3	.484	.400	4	10	103328-5
		3	.384	.300	3	8	103328-4
		3	.284	.200	2	6	103328-3
		3	.184	.100	1	4	103328-2
		3	.084	---	---	2	103328-1

7 SUPERSEDED BY 6-146254-1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHES

MATERIAL
POST: COPPER ALLOY

6

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± .005
4 PLC ± -
ANGLES ± -

FINISH
SEE TABLE

DWN
J.MARTINELLI
CHK
JOHN KNITTLE
APVD
B.FLINCHBAUGH

10/15/92
23NOV92
23NOV92

NAME
ASSEMBLY, HEADER, BREAKAWAY, MOD II,
DOUBLE ROW, .100 X .100 C/L, VERTICAL,
WITH .025 SQUARE POSTS

SIZE
A1

CAGE CODE
00779

DRAWING NO
103328

RESTRICTED TO
-

CUSTOMER DRAWING

SCALE
4:1

SHEET
1

OF
1

REV
P5

TE Connectivity

TE