



<b>Form Type</b>	Distribute	<b>Version</b>	2.0	<b>Ref</b>	IPC 1752A	<b>Sectionals</b>	Material Info	<b>Subsectionals</b>	D, A
<b>Supplier Information</b>									
<b>Company Name</b>	TE Connectivity	<b>Request Document ID</b>		<b>Contact Name</b>	Wu, Cc	<b>Contact Title</b>	Prod Compliance Engineer, China CIS Compliance		
<b>Company Unique ID</b>	TE Connectivity	<b>Response Date</b>	2017-01-27	<b>Contact Email</b>	cc.wu@te.com				
<b>Contact Phone Number</b>	+86-21-33259321								
<b>Legal Statement</b>									
<b>Supplier Acceptance</b>	true								
<b>Legal Statement</b>									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
<b>Product</b>									
<b>Manufacturer Item number</b>	1-1123723-2	<b>Amount</b>	550.000902	<b>Version</b>	-	<b>Identity</b>			
<b>Manufacturer Item Name</b>	3.96 EP HDR ASSY 2P(NATURAL)	<b>Weight Uom</b>	mg	<b>Mfr Site</b>		<b>Authority</b>			
<b>Date</b>		<b>UOM</b>	Each						
<b>EUroHS-0508</b>	Product(s) meets EU RoHS requirement without any exemptions								
<b>ChinaRoHS-0508</b>	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
<b>EUREACH-1215</b>	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
<b>Product Disclosure</b>									
<b>Sub-Item/Material/Substance</b>	<b>Level</b>	<b>Name</b>	<b>Substance Category</b>	<b>Substance CAS</b>	<b>Substance Concentration</b>	<b>Quantity</b>	<b>Mass per Unit</b>	<b>UOM</b>	<b>Exemption</b>
Sub-Item	1	3.96 EP HDR HSG 2P(NATURAL)				1.0	250.0	mg	
Material	2	PBT-GF30				1.0	250.0	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	75.0	mg	
Substance	3	1,4-Benzenedicarboxylic acid, polymer with 1,4-butanediol	Supplier	26062-94-2	54.5	1.0	136.25	mg	
Substance	3	Phenol, 4,4-(1-methylethylidene)bis[2,6-dibromo-, polymer with 2,2-[(1-methylethylidene)bis[(2,6-dibromo-4,1-phenylene)oxy methylene]]bis[oxirane]	Supplier	68928-70-1	12.0	1.0	30.0	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	3.5	1.0	8.75	mg	
Sub-Item	1	POST CONTACT FOR EP HDR ASSY(T				2.0	150.000451	mg	
Material	2	Nickel Plate				2.0	0.728077	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	2.0	0.00145615	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	2.0	7.2808E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	2.0	0.72589	mg	
Material	2	Brass				2.0	148.813	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.2	2.0	0.29763	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	2.0	0.0148813	mg	
Substance	3	Zinc	Supplier	7440-66-6	35.5226	2.0	52.86225	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	2.0	0.14881	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	2.0	0.00148813	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	2.0	0.0744065	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.05	2.0	0.0744065	mg	

Substance	3	Copper	Supplier	7440-50-8	64.0	2.0	95.24032	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	2.0	0.00148813	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0099	2.0	0.01473249	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	2.0	0.0744065	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	2.0	7.4407E-4	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	2.0	0.00744065	mg	
Material	2	Tin Plate				2.0	0.459374	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	2.0	0.45813	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	2.0	9.1875E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	2.0	3.2156E-4	mg	