



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A																	
Supplier Information																										
Company Name	TE Connectivity	Request Document ID		Contact Name	Wu, Cc	Contact Title	Prod Compliance Engineer, China CIS Compliance																			
Company Unique ID	TE Connectivity	Response Date	2017-01-27	Contact Email	cc.wu@te.com																					
Contact Phone Number	+86-21-33259321																									
Legal Statement																										
Supplier Acceptance	true																									
Legal Statement																										
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.																										
Product																										
Manufacturer Item number	1-1123723-6	Amount	1730.002706	Version	-	Identity																				
Manufacturer Item Name	3.96 EP HDR ASSY 6P(NATURAL)	Weight Uom	mg	Mfr Site		Authority																				
Date		UOM	Each																							
EURoHS-0508	Product(s) meets EU RoHS requirement without any exemptions																									
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products																									
EUREACH-1215	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH																									
Product Disclosure																										
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption																	
Sub-Item	1	POST CONTACT FOR EP HDR ASSY(T				6.0	150.000451	mg																		
Material	2	Tin Plate				6.0	0.459374	mg																		
Substance	3	Tin	Supplier	7440-31-5	99.73	6.0	0.45813	mg																		
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	6.0	9.1875E-4	mg																		
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	6.0	3.2156E-4	mg																		
Material	2	Nickel Plate				6.0	0.728077	mg																		
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	6.0	0.00145615	mg																		
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	6.0	7.2808E-4	mg																		
Substance	3	Nickel	Nickel	7440-02-0	99.7	6.0	0.72589	mg																		
Material	2	Brass				6.0	148.813	mg																		
Substance	3	Nickel	Nickel	7440-02-0	0.2	6.0	0.29763	mg																		
Substance	3	Antimony	Supplier	7440-36-0	0.01	6.0	0.0148813	mg																		
Substance	3	Zinc	Supplier	7440-66-6	35.5226	6.0	52.86225	mg																		
Substance	3	Cobalt	Supplier	7440-48-4	0.1	6.0	0.14881	mg																		
Substance	3	Chromium	Supplier	7440-47-3	0.0010	6.0	0.00148813	mg																		
Substance	3	Iron	Supplier	7439-89-6	0.05	6.0	0.0744065	mg																		
Substance	3	Manganese	Supplier	7439-96-5	0.05	6.0	0.0744065	mg																		
Substance	3	Copper	Supplier	7440-50-8	64.0	6.0	95.24032	mg																		
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	6.0	0.00148813	mg																		
Substance	3	Arsenic	Supplier	7440-38-2	0.0099	6.0	0.01473249	mg																		
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	6.0	0.0744065	mg																		
Substance	3	Mercury	Mercury/Mercu ry Compounds	7439-97-6	5.0E-4	6.0	7.4407E-4	mg																		
Substance	3	Cadmium	Cadmium/Cad mium Compounds	7440-43-9	0.0050	6.0	0.00744065	mg																		
Sub-Item	1	3.96 EP HDR HSG 6P(NATURAL)				1.0	830.0	mg																		

Material	2	PBT-GF30				1.0	830.0	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	249.0	mg	
Substance	3	1,4-Benzenedicarboxylic acid, polymer with 1,4-butanediol	Supplier	26062-94-2	54.5	1.0	452.35	mg	
Substance	3	Phenol, 4,4-(1-methylethylidene)bis[2,6-dibromo-, polymer with 2,2-[(1-methylethylidene)bis[(2,6-dibromo-4,1-phenylene)oxy methylene]]bis[oxirane]	Supplier	68928-70-1	12.0	1.0	99.6	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	3.5	1.0	29.05	mg	