



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	John R. Penica	Contact Title	Sr Mgr Environmental Engineering, Ind Central Eng		
Company Unique ID	TE Connectivity	Response Date	2016-08-03	Contact Email	jrpenica@te.com				
Contact Phone Number	717-592-3266								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	1-1734742-6	Amount	260.0	Version	-	Identity			
Manufacturer Item Name	.5 FPC VT ZIF Type-A 16 CONT	Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-1215	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Material	1	CONTACT-Gold Plating				1.0	1.1685	mg	
Substance	2	Gold	Supplier	7440-57-5	99.7	1.0	1.16499	mg	
Substance	2	Cobalt	Supplier	7440-48-4	0.3	1.0	0.0035055	mg	
Material	1	CONTACT				1.0	88.5025	mg	
Substance	2	Phosphorus	Supplier	7723-14-0	0.25	1.0	0.22126	mg	
Substance	2	Copper	Supplier	7440-50-8	93.5	1.0	82.74984	mg	
Substance	2	Zinc	Supplier	7440-66-6	0.2	1.0	0.177	mg	
Substance	2	Iron	Supplier	7439-89-6	0.1	1.0	0.0885025	mg	
Substance	2	Tin	Supplier	7440-31-5	5.941	1.0	5.25793	mg	
Substance	2	Lead	Lead/Lead Compounds	7439-92-1	0.0090	1.0	0.00796522	mg	
Material	1	ACTUATUR				1.0	50.0	mg	
Substance	2	Glass, oxide, chemicals	Supplier	65997-17-3	6.241	1.0	3.1205	mg	
Substance	2	Poly(thio-1,4-phenylene)	Supplier	25212-74-2	93.759	1.0	46.8795	mg	
Material	1	TAB				1.0	18.5725	mg	
Substance	2	Zinc	Supplier	7440-66-6	32.94	1.0	6.11778	mg	
Substance	2	Copper	Supplier	7440-50-8	67.0	1.0	12.44357	mg	
Substance	2	Iron	Supplier	7439-89-6	0.05	1.0	0.00928625	mg	
Substance	2	Lead	Lead/Lead Compounds	7439-92-1	0.01	1.0	0.00185725	mg	
Material	1	TABS-Nickel Plating				1.0	0.391	mg	
Substance	2	Nickel	Nickel	7440-02-0	100.0	1.0	0.391	mg	
Material	1	HOUSING				1.0	100.0	mg	
Substance	2	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	30.0	mg	
Substance	2	Propanoic acid, 3-[(aminoiminom ethyl)thio]-	Supplier	5398-29-8	5.0	1.0	5.0	mg	
Substance	2	Benzene, ethenyl-, homopolymer, brominated	Supplier	88497-56-7	20.0	1.0	20.0	mg	
Substance	2	1,4-Benzenedicarb oxylic acid, polymer with 2-methyl-1,8-octanediamine and 1,9-nonanediamine	Supplier	169284-22-4	45.0	1.0	45.0	mg	

Material	1	CONTACT-Nickel Plating				1.0	0.779	mg	
Substance	2	Nickel	Nickel	7440-02-0	100.0	1.0	0.779	mg	
Material	1	TABS-Tin Plating				1.0	0.5865	mg	
Substance	2	Tin	Supplier	7440-31-5	100.0	1.0	0.5865	mg	