



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Benfer, David W	Contact Title	Prod Compliance Engineer for DND		
Company Unique ID	TE Connectivity	Response Date	2017-01-24	Contact Email	dave.benfer@te.com				
Contact Phone Number	717-986-3725								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	1-1734592-2	Amount	148.03184	Version	-	Identity			
Manufacturer Item Name	FPC CONN. 0.5MM PITCH B/C, 12P	Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-1215	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Material	1	CONTACT-GOLD PLATING				1.0	0.00224	mg	
Substance	2	Gold	Supplier	7440-57-5	99.7	1.0	0.00223328	mg	
Substance	2	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	1.0	1.0E-5	mg	
Material	1	CONTACT				1.0	56.0	mg	
Substance	2	Copper	Supplier	7440-50-8	94.15	1.0	52.724	mg	
Substance	2	Phosphorus	Supplier	7723-14-0	0.2	1.0	0.112	mg	
Substance	2	Tin	Supplier	7440-31-5	5.55	1.0	3.108	mg	
Substance	2	Nickel	Nickel	7440-02-0	0.1	1.0	0.056	mg	
Material	1	HOLD DOWN				1.0	7.0	mg	
Substance	2	Tin	Supplier	7440-31-5	5.35	1.0	0.3745	mg	
Substance	2	Copper	Supplier	7440-50-8	94.45	1.0	6.6115	mg	
Substance	2	Phosphorus	Supplier	7723-14-0	0.2	1.0	0.014	mg	
Material	1	ACTUATOR				1.0	34.0	mg	
Substance	2	Antimony oxide (Sb2O3)	Supplier	1309-64-4	2.0	1.0	0.68	mg	
Substance	2	Glass, oxide, chemicals	Supplier	65997-17-3	45.0	1.0	15.3	mg	
Substance	2	Fatty acids, C18-unsatd., dimers, polymers with ethylenediamine, hexamethylene diamine and propionic acid	Supplier	67989-30-4	53.0	1.0	18.02	mg	
Material	1	HOUSING				1.0	51.0	mg	
Substance	2	Glass, oxide, chemicals	Supplier	65997-17-3	33.0	1.0	16.83	mg	

Substance	2	1,4-Benzenedicarboxylic acid, polymer with [1,1-biphenyl]-4,4-diol, 4-hydroxybenzoic acid, 6-hydroxy-2-naphthalenecarboxylic acid and N-(4-hydroxyphenyl)acetamide	Supplier	147310-94-9	67.0	1.0	34.17	mg	
Material	1	CONTACT/HOLD DOWN - NICKEL PLATING				1.0	0.0031	mg	
Substance	2	Nickel	Nickel	7440-02-0	99.9	1.0	0.0030969	mg	
Substance	2	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	1.0E-5	mg	
Material	1	HOLD DOWN - TinPlating				1.0	0.0265	mg	
Substance	2	Tin	Supplier	7440-31-5	99.9001	1.0	0.02647353	mg	
Substance	2	Lead	Lead/Lead Compounds	7439-92-1	0.0999	1.0	2.64735E-5	mg	