



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Penica, John R	Contact Title	Sr Mgr Engineering, IND Central Eng		
Company Unique ID	TE Connectivity	Response Date	2017-01-16	Contact Email	jrpenica@te.com				
Contact Phone Number	+1-717-592-3266								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	1-5435802-5	Amount	1048.0182	Version	-	Identity			
Manufacturer Item Name	RIGHT ANGLE DIP SW 4 P SEALED	Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-1215	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	CAM, SIDE ACT DIP SW				4.0	22.47	mg	
Material	2	PBT				4.0	22.47	mg	
Substance	3	Benzenepropanoic acid, 3,5-bis(1,1-dimethylethyl)-4-hydroxy-, 1,1-[2,2-bis[[3-[3,5-bis(1,1-dimethylethyl)-4-hydroxyphenyl]-1-oxopropoxy]methyl]-1,3-propanediyl] ester	Supplier	6683-19-8	0.2	4.0	0.04494	mg	
Substance	3	Ethene, homopolymer	Supplier	9002-88-4	5.0	4.0	1.1235	mg	
Substance	3	Ethene, 1,1,2,2-tetrafluoro-, homopolymer	Supplier	9002-84-0	0.1	4.0	0.02247	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	8.0	4.0	1.7976	mg	
Substance	3	7-Oxabicyclo[4.1.0]heptane-3-carboxylic acid, 7-oxabicyclo[4.1.0]hept-3-ylmethyl ester	Supplier	2386-87-0	0.1	4.0	0.02247	mg	
Substance	3	Phosphoric acid, zinc salt (2:3)	Supplier	7779-90-0	0.5	4.0	0.11235	mg	
Substance	3	2-Propenenitrile, polymer with ethenylbenzene	Supplier	9003-54-7	0.1	4.0	0.02247	mg	
Substance	3	Furan, tetrahydro-	Supplier	109-99-9	0.5	4.0	0.11235	mg	

Substance	3	Carbonic dichloride, polymer with 4,4-(1-methylethylidene)bis[2,6-dibromophenol] and 4,4-(1-methylethylidene)bis[phenol], 4-(1-methyl-1-phenylethyl)phenyl ester	Supplier	156042-31-8	30.0	4.0	6.741	mg	
Substance	3	Carbonic dichloride, polymer with 4,4-(1-methylethylidene)bis[phenol], 4-(1-methyl-1-phenylethyl)phenyl ester	Supplier	111211-39-3	5.0	4.0	1.1235	mg	
Substance	3	Acetic acid ethenyl ester, polymer with ethene	Supplier	24937-78-8	2.0	4.0	0.4494	mg	
Substance	3	Phosphorous acid, decyl diphenyl ester	Supplier	3287-06-7	0.1	4.0	0.02247	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	48.4	4.0	10.87548	mg	
Sub-Item	1	CORE TYPE C MOLDED 4 POS				1.0	242.47	mg	
Material	2	PBT-I-GF30-FR(17)				1.0	242.47	mg	
Substance	3	Dolomite (CaMg(CO ₃) ₂)	Supplier	16389-88-1	0.5	1.0	1.21235	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	35.0	1.0	84.8645	mg	
Substance	3	Benzenepropanoic acid, 3,5-bis(1,1-dimethylethyl)-4-hydroxy-, 1,1-[2,2-bis[[3-[3,5-bis(1,1-dimethylethyl)-4-hydroxyphenyl]-1-oxopropoxy]methyl]-1,3-propanediyl] ester	Supplier	6683-19-8	0.2	1.0	0.48494	mg	
Substance	3	Furan, tetrahydro-	Supplier	109-99-9	0.2	1.0	0.48494	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	3.0	1.0	7.2741	mg	
Substance	3	Talc (Mg ₃ H ₂ (SiO ₃) ₄)	Supplier	14807-96-6	2.0	1.0	4.8494	mg	
Substance	3	Ethene, 1,1,2,2-tetrafluoro-, homopolymer	Supplier	9002-84-0	1.0	1.0	2.4247	mg	
Substance	3	Chlorite-group minerals	Supplier	1318-59-8	0.5	1.0	1.21235	mg	
Substance	3	Carbon black	Supplier	1333-86-4	1.0	1.0	2.4247	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	36.6	1.0	88.74402	mg	
Substance	3	Phosphoric acid, zinc salt (2:3)	Supplier	7779-90-0	0.5	1.0	1.21235	mg	
Substance	3	Aromatic Brominated flame retardant with Antimony - ISO 1043-4 code #FR(17)	Supplier	1043-4-FR17	18.0	1.0	43.6446	mg	
Substance	3	Quartz (SiO ₂)	Supplier	14808-60-7	0.5	1.0	1.21235	mg	
Substance	3	2-Propenenitrile, polymer with ethenylbenzene	Supplier	9003-54-7	1.0	1.0	2.4247	mg	

Sub-Item	1	LOWER CONTACT FORMED				5.0	13.0082	mg	
Material	2	Nickel Plate				5.0	0.381	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	5.0	7.62E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	5.0	3.81E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	5.0	0.37986	mg	
Material	2	Gold Plate				5.0	0.0032	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	5.0	0.0031904	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	5.0	1.0E-5	mg	
Material	2	Beryllium Copper				5.0	12.5	mg	
Substance	3	Copper	Supplier	7440-50-8	96.9485	5.0	12.11856	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	5.0	0.0025	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	5.0	0.00125	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.6	5.0	0.075	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	5.0	0.00125	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	5.0	1.25E-4	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	5.0	0.0125	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	5.0	0.00125	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	5.0	0.0125	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	5.0	6.25E-5	mg	
Substance	3	Nickel	Nickel	7440-02-0	2.2	5.0	0.275	mg	
Material	2	Tin Plate				5.0	0.124	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	5.0	2.48E-4	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	5.0	0.12367	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	5.0	8.68E-5	mg	
Sub-Item	1	UPPER SPRING CONTACT FORMED				5.0	13.04788	mg	
Material	2	Nickel Plate				5.0	0.38	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	5.0	7.6E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	5.0	3.8E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	5.0	0.37886	mg	
Material	2	Gold Plate				5.0	0.00688	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	5.0	0.00685936	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	5.0	2.064E-5	mg	
Material	2	Beryllium Copper				5.0	12.537	mg	
Substance	3	Copper	Supplier	7440-50-8	96.9485	5.0	12.15443	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	5.0	0.0025074	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	5.0	0.0012537	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.6	5.0	0.075222	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	5.0	0.0012537	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	5.0	1.2537E-4	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	5.0	0.012537	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	5.0	0.0012537	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	5.0	0.012537	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	5.0	6.2685E-5	mg	
Substance	3	Nickel	Nickel	7440-02-0	2.2	5.0	0.27581	mg	
Material	2	Tin Plate				5.0	0.124	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	5.0	2.48E-4	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	5.0	0.12367	mg	

Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	5.0	8.68E-5	mg	
Sub-Item	1	CASE, SIDE ACT DIP SW 4 POS				1.0	384.9	mg	
Material	2	PBT-I-GF30-FR(17)				1.0	384.9	mg	
Substance	3	Dolomite (CaMg(CO3)2)	Supplier	16389-88-1	0.5	1.0	1.9245	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	35.0	1.0	134.715	mg	
Substance	3	Benzenepropionic acid, 3,5-bis(1,1-dimethylethyl)-4-hydroxy-, 1,1-[2,2-bis[[3-[3,5-bis(1,1-dimethylethyl)-4-hydroxyphenyl]-1-oxopropoxy]methyl]-1,3-propanediyl] ester	Supplier	6683-19-8	0.2	1.0	0.7698	mg	
Substance	3	Furan, tetrahydro-	Supplier	109-99-9	0.2	1.0	0.7698	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	3.0	1.0	11.547	mg	
Substance	3	Talc (Mg3H2(SiO3)4)	Supplier	14807-96-6	2.0	1.0	7.698	mg	
Substance	3	Ethene, 1,1,2,2-tetrafluoro-, homopolymer	Supplier	9002-84-0	1.0	1.0	3.849	mg	
Substance	3	Chlorite-group minerals	Supplier	1318-59-8	0.5	1.0	1.9245	mg	
Substance	3	Carbon black	Supplier	1333-86-4	1.0	1.0	3.849	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	36.6	1.0	140.8734	mg	
Substance	3	Phosphoric acid, zinc salt (2:3)	Supplier	7779-90-0	0.5	1.0	1.9245	mg	
Substance	3	Aromatic Brominated flame retardant with Antimony - ISO 1043-4 code #FR(17)	Supplier	1043-4-FR17	18.0	1.0	69.282	mg	
Substance	3	Quartz (SiO2)	Supplier	14808-60-7	0.5	1.0	1.9245	mg	
Substance	3	2-Propenenitrile, polymer with ethenylbenzene	Supplier	9003-54-7	1.0	1.0	3.849	mg	
Sub-Item	1	Adhesive and Sealants				1.0	200.4878	mg	
Material	2	Plastic Coating - Sealent				1.0	200.4878	mg	
Substance	3	1,2-Benzenedicarboxylic acid, di-C9-11-branched alkyl esters, C10-rich	Phthalates (DINP, DIDP, DNOP)	68515-49-1	20.0	1.0	40.09756	mg	
Substance	3	Castor-oil	Supplier	8001-79-4	20.0	1.0	40.09756	mg	
Substance	3	CELLULOSE, ACETATE BUTYRATE	Supplier	9004-36-8	50.0	1.0	100.2439	mg	
Substance	3	Soybean oil, epoxidized	Supplier	8013-07-8	10.0	1.0	20.04878	mg	