



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	John R Penica	Contact Title	Sr Mgr Environmental Engineering		
Company Unique ID	TE Connectivity	Response Date	2016-11-29	Contact Email	jrpenica@te.com				
Contact Phone Number	+1-717-592-3266								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	1-1825058-9	Amount	1.0460683	Version	-	Identity			
Manufacturer Item Name	ADE08S04=DIP SWTCH,EXT,SM T-GW	Weight Uom	g	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-1215	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Material	1	Cover				1.0	0.287	g	
Substance	2	Benzene, 1,4-dichloro-, polymer with sodium sulfide (Na2S)	Supplier	26125-40-6	70.0	1.0	0.2009	g	
Substance	2	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	0.0861	g	
Material	1	Nickel Plating(Fixed Contact)				1.0	6.9E-4	g	
Substance	2	Nickel	Nickel	7440-02-0	100.0	1.0	6.9E-4	g	
Material	1	Moving Contact				1.0	0.0030	g	
Substance	2	Cobalt	Supplier	7440-48-4	16.67	1.0	5.001E-4	g	
Substance	2	Beryllium	Supplier	7440-41-7	20.0	1.0	6.0E-4	g	
Substance	2	Copper	Supplier	7440-50-8	63.33	1.0	0.0018999	g	
Material	1	Base				1.0	0.71	g	
Substance	2	Glass, oxide, chemicals	Supplier	65997-17-3	40.0	1.0	0.284	g	
Substance	2	Benzene, 1,4-dichloro-, polymer with sodium sulfide (Na2S)	Supplier	26125-40-6	60.0	1.0	0.426	g	
Material	1	Actuator				1.0	0.013	g	
Substance	2	Antimonate (SbO31-), sodium (1:1)	Supplier	15432-85-6	24.62	1.0	0.0032006	g	
Substance	2	Glass, oxide, chemicals	Supplier	65997-17-3	14.62	1.0	0.0019006	g	
Substance	2	Benzene, ethenyl-, homopolymer, brominated	Supplier	88497-56-7	23.46	1.0	0.0030498	g	
Substance	2	Polyamide Homologous Polymer Series - ISO 1043-1 Term PA6T/66	Supplier	1043-1-PA6T/66	37.3	1.0	0.004849	g	
Material	1	Fixed Contact				1.0	0.0323	g	
Substance	2	Zinc	Supplier	7440-66-6	0.0619	1.0	1.99937E-5	g	
Substance	2	Copper	Supplier	7440-50-8	98.2054	1.0	0.03172034	g	

Substance	2	Antimony	Supplier	7440-36-0	0.0619	1.0	1.99937E-5	g	
Substance	2	Bismuth	Supplier	7440-69-9	0.0619	1.0	1.99937E-5	g	
Substance	2	Iron	Supplier	7439-89-6	1.547	1.0	4.9968E-4	g	
Substance	2	Lead	Lead/Lead Compounds	7439-92-1	0.0619	1.0	1.99937E-5	g	
Material	1	Gold Plating(Fixed Contact)				1.0	1.4E-5	g	
Substance	2	Gold	Supplier	7440-57-5	100.0	1.0	1.4E-5	g	
Material	1	Nickel plating(Moving Contact)				1.0	6.3E-5	g	
Substance	2	Nickel	Nickel	7440-02-0	100.0	1.0	6.3E-5	g	
Material	1	Gold plating(Moving Contact)				1.0	1.3E-6	g	
Substance	2	Gold	Supplier	7440-57-5	100.0	1.0	1.3E-6	g	