

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

-,-

© COPYRIGHT - By -





ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	APVD
			D	END STAND OFF WIDTH INCREASED	07JAN2016	KJK PS

NOTES:

- TO DETERMINE DIMENSIONS TAKE $2 \times N = \text{NR. OF POS.}$.
FOR EXAMPLE: $2 \times 10 \text{ POS.: } N \times 2,54 = 25,4 \text{ mm.}$
FOR ORDERNR. USE BASIC NR. + NR. OF POS.
FOR EXAMPLE: $2 \times 2 \text{ POS.} = 215 \text{ 308-2 (SHORTEST VERSION)}$
 $2 \times 36 \text{ POS.} = 3-215 \text{ 308-6 (LONGEST VERSION)}$
- HOUSING MATERIAL: GREEN GLASS FILLED PBT,
UL 94V-0
CONTACT MATERIAL: PHOSPHOR BRONZE.
- PLATING: $2.5 - 4.0 \mu\text{m}$ TIN OVER $0.5 \mu\text{m}$ NICKEL
- MATES WITH 0,63 SQUARE/ROUND MODU POSTS.
- CONTACT-POINT.
- RECOMMENDED PC-BOARD-THICKNESS: 1.6 mm
- PC-BOARD RETENTION FEATURE.
- HV100 CONNECTOR PACKED IN ANTI-STATIC BLISTER TRAY.

POS. PER ROW 'N'	L	PART NUMBER	
-	-	-	-
2	5.08	215308-2	OBSOLETE
3	7.62	-3	OBSOLETE
4	10.16	-4	
5	12.70	-5	
6	15.24	-6	OBSOLETE
7	17.78	-7	
8	20.32	-8	
9	22.86	-9	
10	25.40	1-	-0 OBSOLETE
11	27.94	1-	-1
12	30.48	1-	-2
13	33.02	1-	-3 OBSOLETE
14	35.56	1-	-4 OBSOLETE
15	38.10	1-	-5
16	40.64	1-	-6
17	43.18	1-	-7 OBSOLETE
18	45.72	1-	-8
19	48.26	1-	-9
20	50.80	2-	-0
21	53.34	2-	-1 OBSOLETE
22	55.88	2-	-2
23	58.42	2-	-3
24	60.96	2-	-4
25	63.50	2-	-5
26	66.04	2-	-6 OBSOLETE
27	68.58	2-	-7 OBSOLETE
28	71.12	2-	-8
29	73.66	2-	-9 OBSOLETE
30	76.20	3-	-0
31	78.74	3-	-1 OBSOLETE
32	81.28	3-	-2
33	83.82	3-	-3 OBSOLETE
34	86.36	3-	-4 OBSOLETE
35	88.90	3-	-5
36	91.44	3- 215308	-6



P.C.-BOARD HOLE-PATTERN

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN A.HO 24.02.89	 TE Connectivity			
		CHK M.SCHAARSCHMIDT 24.02.89				
		APVD G.FELDMEIER	NAME			
		PRODUCT SPEC 108-19056	HV 100 VERTICAL CONNECTOR DUAL ROW, 7,0mm HEIGHT, TOP ENTRY, TIN			
		APPLICATION SPEC	SIZE		CAGE CODE	DRAWING NO
		WEIGHT	A3		00779	C-215308
CUSTOMER DRAWING		SCALE	5:1		SHEET	1 OF 1
		REV	D			