



<b>Form Type</b>	Distribute	<b>Version</b>	2.0	<b>Ref</b>	IPC 1752A	<b>Sectionals</b>	Material Info	<b>Subsectionals</b>	D, A
<b>Supplier Information</b>									
<b>Company Name</b>	TE Connectivity	<b>Request Document ID</b>		<b>Contact Name</b>	Benfer, David W	<b>Contact Title</b>	Prod Compliance Engineer, Eng Proc Opt/LEANPD		
<b>Company Unique ID</b>	TE Connectivity	<b>Response Date</b>	2016-12-16	<b>Contact Email</b>	dave.benfer@te.com				
<b>Contact Phone Number</b>	717-986-3725								
<b>Legal Statement</b>									
<b>Supplier Acceptance</b>	true								
<b>Legal Statement</b>									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
<b>Product</b>									
<b>Manufacturer Item number</b>	1981568-1	<b>Amount</b>	232.0	<b>Version</b>	-	<b>Identity</b>			
<b>Manufacturer Item Name</b>	REC TYPE B ASSY (Au) MICRO USB	<b>Weight Uom</b>	mg	<b>Mfr Site</b>		<b>Authority</b>			
<b>Date</b>		<b>UOM</b>	Each						
<b>EURoHS-0508</b>	Product(s) meets EU RoHS requirement without any exemptions								
<b>ChinaRoHS-0508</b>	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
<b>EUREACH-1215</b>	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
<b>Product Disclosure</b>									
<b>Sub-Item/Material/Substance</b>	<b>Level</b>	<b>Name</b>	<b>Substance Category</b>	<b>Substance CAS</b>	<b>Substance Concentration</b>	<b>Quantity</b>	<b>Mass per Unit</b>	<b>UOM</b>	<b>Exemption</b>
Sub-Item	1	REC METAL SHELL TYPE B MICRO USB				1.0	190.0	mg	
Material	2	Stainless Steel				1.0	185.212	mg	
Substance	3	Chromium	Supplier	7440-47-3	18.0	1.0	33.33816	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.5	1.0	0.92606	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.045	1.0	0.0833454	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.0185212	mg	
Substance	3	Carbon	Supplier	7440-44-0	0.15	1.0	0.27782	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.01	1.0	0.0185212	mg	
Substance	3	Silicon	Supplier	7440-21-3	1.5	1.0	2.77818	mg	
Substance	3	Manganese	Supplier	7439-96-5	2.0	1.0	3.70424	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.03	1.0	0.0555636	mg	
Substance	3	Sulfur	Supplier	7704-34-9	0.03	1.0	0.0555636	mg	
Substance	3	Iron	Supplier	7439-89-6	68.6147	1.0	127.08266	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	1.0	0.18503	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0099	1.0	0.01833599	mg	
Substance	3	Nickel	Nickel	7440-02-0	9.0	1.0	16.66908	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	9.2606E-4	mg	
Material	2	Tin Plate				1.0	1.86	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.00372	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	1.0	1.85498	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	1.0	0.001302	mg	
Material	2	Nickel Plate				1.0	2.928	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.005856	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.002928	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	2.91922	mg	

Sub-Item	1	REC INSERT MOLD (Au&BLACK) MICRO USB				1.0	42.0	mg	
Material	2	LCP-(GF+MD)40				1.0	29.0	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	2.0	1.0	0.58	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	26.5	1.0	7.685	mg	
Substance	3	Talc (Mg3H2(SiO3)4)	Supplier	14807-96-6	12.7	1.0	3.683	mg	
Substance	3	Carbon black	Supplier	1333-86-4	1.0	1.0	0.29	mg	
Substance	3	1,3-Benzenedicarboxylic acid, polymer with 1,4-benzenedicarboxylic acid, [1,1-biphenyl]-4,4-diol and 4-hydroxybenzoic acid	Supplier	60088-52-0	57.8	1.0	16.762	mg	
Material	2	Phos Bronze				1.0	12.12	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6985	1.0	11.47746	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	0.002424	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	1.0	0.001212	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	1.0	0.5454	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	1.0	6.06E-4	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	1.0	0.01212	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.001212	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	1.212E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	1.0	0.03636	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	1.0	0.01212	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.01212	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	6.06E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.00606	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	1.0	0.01212	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	6.06E-5	mg	
Material	2	Gold Plate				1.0	0.25	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	1.0	0.24925	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	1.0	7.5E-4	mg	
Material	2	Nickel Plate				1.0	0.63	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	6.3E-4	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.00126	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	0.62811	mg	