



<b>Form Type</b>	Distribute	<b>Version</b>	2.0	<b>Ref</b>	IPC 1752A	<b>Sectionals</b>	Material Info	<b>Subsectionals</b>	D, A
<b>Supplier Information</b>									
<b>Company Name</b>	TE Connectivity	<b>Request Document ID</b>		<b>Contact Name</b>	Cc Wu	<b>Contact Title</b>	Product Compliance Engineer		
<b>Company Unique ID</b>	TE Connectivity	<b>Response Date</b>	2016-03-21	<b>Contact Email</b>	cc.wu@te.com				
<b>Contact Phone Number</b>	+86-21-33259321								
<b>Legal Statement</b>									
<b>Supplier Acceptance</b>	true								
<b>Legal Statement</b>									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
<b>Product</b>									
<b>Manufacturer Item number</b>	1-282002-8	<b>Amount</b>	2374.1	<b>Version</b>	-	<b>Identity</b>			
<b>Manufacturer Item Name</b>	MONO-SHAPE MK I TAB CONN ASSY	<b>Weight Uom</b>	mg	<b>Mfr Site</b>		<b>Authority</b>			
<b>Date</b>		<b>UOM</b>	Each						
<b>EUroHS-0508</b>	Product(s) meets EU RoHS requirement without any exemptions								
<b>ChinaRoHS-0508</b>	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
<b>EUREACH-0615</b>	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
<b>Product Disclosure</b>									
<b>Sub-Item/Material/Substance</b>	<b>Level</b>	<b>Name</b>	<b>Substance Category</b>	<b>Substance CAS</b>	<b>Substance Concentration</b>	<b>Quantity</b>	<b>Mass per Unit</b>	<b>UOM</b>	<b>Exemption</b>
Sub-Item	1	5MM PITCH IDC TAB CONTACT				2.0	520.5	mg	
Material	2	Tin Plate				2.0	3.5	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	2.0	3.49055	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	2.0	0.0070	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	2.0	0.00245	mg	
Material	2	Brass				2.0	517.0	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	2.0	0.00517	mg	
Substance	3	Zinc	Supplier	7440-66-6	28.0225	2.0	144.87633	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.05	2.0	0.2585	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	2.0	0.0517	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	2.0	0.2585	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	2.0	0.517	mg	
Substance	3	Copper	Supplier	7440-50-8	71.5	2.0	369.655	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	2.0	0.00517	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	2.0	0.0517	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	2.0	0.002585	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.2	2.0	1.034	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	2.0	0.02585	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	2.0	0.2585	mg	
Sub-Item	1	AMP MONO-SHAPE 2 P.TAB HOUSING				1.0	1333.1	mg	
Material	2	PA66-GF20-FR(16+72)				1.0	1333.1	mg	
Substance	3	Boric acid, zinc salt	Supplier	1332-07-6	8.0	1.0	106.648	mg	
Substance	3	Poly[imino(1,6-dioxo-1,6-hexanediy)]imino-1,6-hexanediy]	Supplier	32131-17-2	45.0	1.0	599.895	mg	
Substance	3	Benzene, ethenyl-, homopolymer, brominated	Supplier	88497-56-7	20.0	1.0	266.62	mg	

Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	5.0	1.0	66.655	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	22.0	1.0	293.282	mg	