



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A																									
Supplier Information																																		
Company Name	TE Connectivity	Request Document ID		Contact Name	Wu, Cc	Contact Title	Prod Compliance Engineer, China CIS Compliance																											
Company Unique ID	TE Connectivity	Response Date	2017-01-27	Contact Email	cc.wu@te.com																													
Contact Phone Number		+86-21-33259321																																
Legal Statement																																		
Supplier Acceptance	true																																	
Legal Statement																																		
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.																																		
Product																																		
Manufacturer Item number	1-770166-1	Amount	809.686	Version	-	Identity																												
Manufacturer Item Name	02P MINI UMNL ASSY VO SNAU LF	Weight Uom	mg	Mfr Site		Authority																												
Date		UOM	Each																															
EUROHS-0508	Product(s) meets EU RoHS requirement without any exemptions																																	
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products																																	
EUREACH-1215	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH																																	
Product Disclosure																																		
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption																									
Sub-Item	1	MINI UMNL BAND PIN SNAU LF				2.0	109.843	mg																										
Material	2	Nickel Plate				2.0	0.647	mg																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	2.0	0.001294	mg																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	2.0	6.47E-4	mg																										
Substance	3	Nickel	Nickel	7440-02-0	99.7	2.0	0.64506	mg																										
Material	2	Gold Plate				2.0	0.273	mg																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	1.0	2.0	0.00273	mg																										
Substance	3	Gold	Supplier	7440-57-5	99.0	2.0	0.27027	mg																										
Material	2	Tin Plate				2.0	0.923	mg																										
Substance	3	Tin	Supplier	7440-31-5	99.73	2.0	0.92051	mg																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	2.0	0.001846	mg																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	2.0	6.461E-4	mg																										
Material	2	Brass Wire				2.0	108.0	mg																										
Substance	3	Copper	Supplier	7440-50-8	71.5	2.0	77.22	mg																										
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	2.0	0.00108	mg																										
Substance	3	Zinc	Supplier	7440-66-6	28.0226	2.0	30.26441	mg																										
Substance	3	Manganese	Supplier	7439-96-5	0.05	2.0	0.054	mg																										
Substance	3	Chromium	Supplier	7440-47-3	0.0010	2.0	0.00108	mg																										
Substance	3	Iron	Supplier	7439-89-6	0.05	2.0	0.054	mg																										
Substance	3	Cobalt	Supplier	7440-48-4	0.1	2.0	0.108	mg																										
Substance	3	Arsenic	Supplier	7440-38-2	0.0099	2.0	0.010692	mg																										
Substance	3	Antimony	Supplier	7440-36-0	0.01	2.0	0.0108	mg																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	2.0	0.054	mg																										
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	2.0	0.0054	mg																										

Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	2.0	5.4E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.2	2.0	0.216	mg	
Sub-Item	1	02P MINI-UMNL HDR HSG V0 WHT				1.0	590.0	mg	
Material	2	PA				1.0	590.0	mg	
Substance	3	Water	Supplier	7732-18-5	0.3262	1.0	1.92458	mg	
Substance	3	2H-Azepin-2-one, hexahydro-	Supplier	105-60-2	0.4637	1.0	2.73583	mg	
Substance	3	Siloxanes and Silicones, di-Me	Supplier	63148-62-9	3.0E-4	1.0	0.00177	mg	
Substance	3	Poly[imino(1,6-dioxo-1,6-hexanediyl)imino-1,6-hexanediyl]	Supplier	32131-17-2	0.9451	1.0	5.57609	mg	
Substance	3	Benzenepropionamide, N,N-1,6-hexanediylbis[3,5-bis(1,1-dimethylethyl)-4-hydroxy-	Supplier	23128-74-7	0.4004	1.0	2.36236	mg	
Substance	3	1,2-Ethanediamine	Supplier	107-15-3	0.0033	1.0	0.01947	mg	
Substance	3	Phosphoric acid, sodium salt, hydrate (1:2:12)	Supplier	10039-32-4	0.025	1.0	0.1475	mg	
Substance	3	Octadecanoic acid, calcium salt (2:1)	Supplier	1592-23-0	0.2012	1.0	1.18708	mg	
Substance	3	Octadecanamide, N,N-1,2-ethanediylbis-	Supplier	110-30-5	0.1901	1.0	1.12159	mg	
Substance	3	1,3,5-Triazine-2,4,6-(1H,3H,5H)-trione, compd. with 1,3,5-triazine-2,4,6-triamine (1:1)	Supplier	37640-57-6	9.0717	1.0	53.52303	mg	
Substance	3	Hexanedioic acid, polymer with hexahydro-2H-azepin-2-one and 1,6-hexanediamine	Supplier	24993-04-2	88.373	1.0	521.4007	mg	