



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Benfer, David W	Contact Title	Prod Compliance Engineer		
Company Unique ID	TE Connectivity	Response Date	2015-06-22	Contact Email	dave.benfer@te.com				
Contact Phone Number	717-986-3725								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	2-5174341-5	Amount	16495.7380606	Version	-	Identity			
Manufacturer Item Name	68P S-MINI-MITE CAP HDR R-LEG	Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-1214	REACH Candidate Substances of Very High Concern ARE NOT Yet Reviewed								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	68P TIN PLATE AMPLIMITE 050				1.0	525.0	mg	
Material	2	PBT-GF30 FR(17)				1.0	525.0	mg	
Substance	3	Aromatic Brominated flame retardant with Antimony - ISO 1043-4 code #FR(17)	Supplier	1043-4-FR17	15.0	1.0	78.75	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	7.0	1.0	36.75	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	1.0	1.0	5.25	mg	
Substance	3	1,4-Benzenedicarb oxylie acid, polymer with 1,4-butanediol	Supplier	26062-94-2	59.0	1.0	309.75	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	17.0	1.0	89.25	mg	
Substance	3	Carbon black	Supplier	1333-86-4	1.0	1.0	5.25	mg	
Sub-Item	1	S-AMPLIMITE 050 CAP ASSY 68P				1.0	780.0	mg	
Material	2	PBT-GF30				1.0	780.0	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	234.0	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	7.0	1.0	54.6	mg	
Substance	3	Carbon black	Supplier	1333-86-4	0.5	1.0	3.9	mg	
Substance	3	Poly(butylene terephthalate) - ISO 1043-1 Term PBT	Supplier	1043-1-PBT	42.0	1.0	327.6	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	5.5	1.0	42.9	mg	
Substance	3	Aromatic Brominated flame retardant with Antimony - ISO 1043-4 code #FR(17)	Supplier	1043-4-FR17	15.0	1.0	117.0	mg	

Sub-Item	1	AMPLIMITE 050 POST CONT(0.76) LEAD FREE				34.0	40.2003509	mg	
Material	2	Gold Plate				34.0	0.0260799	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	34.0	0.02600166	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2- 0909	0.3	34.0	7.82397E-5	mg	
Material	2	Nickel Plate				34.0	1.418	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2- 1212	0.2	34.0	0.002836	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	34.0	0.001418	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	34.0	1.41375	mg	
Material	2	Phos Bronze				34.0	38.6003	mg	
Substance	3	Mercury	Mercury/Mercu ry Compounds	7439-97-6	5.0E-4	34.0	1.93E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	34.0	0.0386003	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.015	34.0	0.00579005	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	34.0	0.00386003	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	34.0	0.00772006	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	34.0	3.86E-4	mg	
Substance	3	Iron	Supplier	7439-89-6	0.12	34.0	0.04632036	mg	
Substance	3	Copper	Supplier	7440-50-8	97.2735	34.0	37.54786	mg	
Substance	3	Tin	Supplier	7440-31-5	2.2	34.0	0.84921	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	34.0	0.0386003	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.04	34.0	0.01544012	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	34.0	0.00386003	mg	
Substance	3	Cadmium	Cadmium/Cad mium Compounds	7440-43-9	0.01	34.0	0.00386003	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	34.0	0.0386003	mg	
Material	2	Tin Plate				34.0	0.155971	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	34.0	1.5581E-4	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	34.0	0.15582	mg	
Sub-Item	1	RETENTION LEG S-MINI MITE				2.0	6408.895971	mg	
Material	2	Brass				2.0	6407.7	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	2.0	0.064077	mg	
Substance	3	Zinc	Supplier	7440-66-6	28.0225	2.0	1795.59773	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.05	2.0	3.20385	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	2.0	0.64077	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	2.0	3.20385	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	2.0	6.4077	mg	
Substance	3	Copper	Supplier	7440-50-8	71.5	2.0	4581.5055	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	2.0	0.064077	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	2.0	0.64077	mg	
Substance	3	Mercury	Mercury/Mercu ry Compounds	7439-97-6	5.0E-4	2.0	0.0320385	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.2	2.0	12.8154	mg	
Substance	3	Cadmium	Cadmium/Cad mium Compounds	7440-43-9	0.0050	2.0	0.32039	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	2.0	3.20385	mg	
Material	2	Nickel Plate				2.0	1.04	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2- 1212	0.2	2.0	0.00208	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	2.0	0.00104	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	2.0	1.03688	mg	
Material	2	Tin Plate				2.0	0.155971	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	2.0	1.5581E-4	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	2.0	0.15582	mg	
Sub-Item	1	AMPLIMITE 050 POST CONT(0.76) LEAD FREE				34.0	29.592182	mg	
Material	2	Gold Plate				34.0	0.0260799	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	34.0	0.02600166	mg	

Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	34.0	7.82397E-5	mg	
Material	2	Nickel Plate				34.0	1.04	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	34.0	0.00208	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	34.0	0.00104	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	34.0	1.03688	mg	
Material	2	Phos Bronze				34.0	28.5246	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	34.0	1.4262E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	34.0	0.0285246	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.015	34.0	0.00427869	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	34.0	0.00285246	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	34.0	0.00570492	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	34.0	2.8525E-4	mg	
Substance	3	Iron	Supplier	7439-89-6	0.12	34.0	0.03422952	mg	
Substance	3	Copper	Supplier	7440-50-8	97.2735	34.0	27.74688	mg	
Substance	3	Tin	Supplier	7440-31-5	2.2	34.0	0.62754	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	34.0	0.0285246	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.04	34.0	0.01140984	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	34.0	0.00285246	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	34.0	0.00285246	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	34.0	0.0285246	mg	
Material	2	Tin Plate				34.0	0.0015021	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	34.0	1.0E-5	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	34.0	0.0015006	mg	