



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A																									
Supplier Information																																		
Company Name	TE Connectivity	Request Document ID		Contact Name	Benfer, David W	Contact Title	Prod Compliance Engineer																											
Company Unique ID	TE Connectivity	Response Date	2016-05-13	Contact Email	dave.benfer@te.com																													
Contact Phone Number		717-986-3725																																
Legal Statement																																		
Supplier Acceptance	true																																	
Legal Statement																																		
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.																																		
Product																																		
Manufacturer Item number	292161-4	Amount	189.428	Version	-	Identity																												
Manufacturer Item Name	CT P/HDR ASSY V 4P W/KINK NAT	Weight Uom	mg	Mfr Site		Authority																												
Date		UOM	Each																															
EUROHS-0508	Product(s) meets EU RoHS requirement without any exemptions																																	
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products																																	
EUREACH-0615	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH																																	
Product Disclosure																																		
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption																									
Sub-Item	1	0.6DIA POST				4.0	22.357	mg																										
Material	2	Tin Plate				4.0	0.259	mg																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	4.0	1.813E-4	mg																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	4.0	5.18E-4	mg																										
Substance	3	Tin	Supplier	7440-31-5	99.73	4.0	0.2583	mg																										
Material	2	Brass				4.0	21.782	mg																										
Substance	3	Mercury	Mercury/Mercu ry Compounds	7439-97-6	5.0E-4	4.0	1.0891E-4	mg																										
Substance	3	Nickel	Nickel	7440-02-0	0.2	4.0	0.043564	mg																										
Substance	3	Antimony	Supplier	7440-36-0	0.01	4.0	0.0021782	mg																										
Substance	3	Copper	Supplier	7440-50-8	68.5	4.0	14.92067	mg																										
Substance	3	Zinc	Supplier	7440-66-6	31.0026	4.0	6.75299	mg																										
Substance	3	Cobalt	Supplier	7440-48-4	0.1	4.0	0.021782	mg																										
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	4.0	2.1782E-4	mg																										
Substance	3	Arsenic	Supplier	7440-38-2	0.0099	4.0	0.00215642	mg																										
Substance	3	Iron	Supplier	7439-89-6	0.07	4.0	0.0152474	mg																										
Substance	3	Chromium	Supplier	7440-47-3	0.0010	4.0	2.1782E-4	mg																										
Substance	3	Manganese	Supplier	7439-96-5	0.05	4.0	0.010891	mg																										
Substance	3	Cadmium	Cadmium/Cad mium Compounds	7440-43-9	0.0050	4.0	0.0010891	mg																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	4.0	0.010891	mg																										
Material	2	Nickel Plate				4.0	0.316	mg																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	4.0	6.32E-4	mg																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	4.0	3.16E-4	mg																										
Substance	3	Nickel	Nickel	7440-02-0	99.7	4.0	0.31505	mg																										
Sub-Item	1	CT CONN MT HDR HSG V 4P				1.0	100.0	mg																										
Material	2	PA66				1.0	100.0	mg																										
Substance	3	Phosphoric acid, trimethyl ester	Supplier	512-56-1	0.05	1.0	0.05	mg																										

Substance	3	Nitrogen compounds - ISO 1043-4 code #FR(30)	Supplier	1043-4-FR30	9.0	1.0	9.0	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	3.0	1.0	3.0	mg	
Substance	3	Poly[imino(1,6-dioxo-1,6-hexanediyl)imino-1,6-hexanediyl]	Supplier	32131-17-2	87.95	1.0	87.95	mg	