



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Penica, John R	Contact Title	Sr Mgr Engineering, IND Central Eng		
Company Unique ID	TE Connectivity	Response Date	2017-01-09	Contact Email	jrpenica@te.com				
Contact Phone Number	+1-717-592-3266								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	103321-3	Amount	810.0000036	Version	-	Identity			
Manufacturer Item Name	03 MODIII HDR SRST B/A .100CL	Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EURoHS-0508	Product(s) does not meet EU RoHS requirements and is not under exemptions								
ChinaRoHS-0508	Product(s) is NOT eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-1215	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	40 B/A SRST HSG 50/50 BLEND				1.0	681.0	mg	
Material	2	PBT-GF30-FR(17)				1.0	681.0	mg	
Substance	3	Carbon black	Supplier	1333-86-4	0.5	1.0	3.405	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.7	1.0	4.767	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	33.0	1.0	224.73	mg	
Substance	3	1,4-Benzenedicarb oxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	46.0	1.0	313.26	mg	
Substance	3	Ethene, 1,1,2,2-tetrafluoro-, homopolymer	Supplier	9002-84-0	0.6	1.0	4.086	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	7.0	1.0	47.67	mg	
Substance	3	Benzenepropa noic acid, 3,5-bis(1,1-dimethylethyl)-4-hydroxy-, 1,1-[2,2-bis[[3-[3,5-bis(1,1-dimethylethyl)-4-hydroxyphenyl]-1-oxopropoxy]methyl]-1,3-propanediyl] ester	Supplier	6683-19-8	0.2	1.0	1.362	mg	
Substance	3	2-Propenoic acid, (2,3,4,5,6-pentabromophenyl)methyl ester, homopolymer	Brominated Flame Retardants (other than PBBs or PBDEs)	59447-57-3	12.0	1.0	81.72	mg	
Sub-Item	1	STARLESS BAND W/POST SN				3.0	43.0000012	mg	

Material	2	Tin-Lead Plate				3.0	0.9502366	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	13.0	3.0	0.12353	mg	
Substance	3	Tin	Supplier	7440-31-5	86.5	3.0	0.82195	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.5	3.0	0.00475118	mg	
Material	2	Nickel Plate				3.0	0.5570176	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	3.0	0.00111403	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	3.0	5.5702E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	3.0	0.55535	mg	
Material	2	Phos Bronze				3.0	41.492747	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	3.0	4.1493E-4	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.015	3.0	0.00622391	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	3.0	0.00829855	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.35	3.0	0.14522	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	3.0	0.00414928	mg	
Substance	3	Tin	Supplier	7440-31-5	5.8	3.0	2.40658	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	3.0	0.04149275	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	3.0	0.12448	mg	
Substance	3	Copper	Supplier	7440-50-8	93.1335	3.0	38.64365	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	3.0	0.00414928	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	3.0	0.04149275	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	3.0	0.04149275	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	3.0	0.00414928	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	3.0	2.0746E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	3.0	0.02074637	mg	