



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Rebecca Dong	Contact Title	Compliance Engineer		
Company Unique ID	TE Connectivity	Response Date	2017-01-12	Contact Email	Rebecca_dong@te.com				
Contact Phone Number	86(21)33259330								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	292253-3	Amount	0.184	Version	-	Identity			
Manufacturer Item Name	CT CONN MT HDR ASSY H 3P NAT	Weight Uom	g	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-1215	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	CT CONN MT HDR HSG H 3P				1.0	0.1	g	
Material	2	PA66				1.0	0.1	g	
Substance	3	Phosphoric acid, trimethyl ester	Supplier	512-56-1	0.05	1.0	5.0E-5	g	
Substance	3	Nitrogen compounds - ISO 1043-4 code #FR(30)	Supplier	1043-4-FR30	9.0	1.0	0.0090	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	3.0	1.0	0.0030	g	
Substance	3	Poly[imino(1,6-dioxo-1,6-hexanediyl)imino-1,6-hexanediyl]	Supplier	32131-17-2	87.95	1.0	0.08795	g	
Sub-Item	1	0.6DIA POST				3.0	0.028	g	
Material	2	Nickel Plate				3.0	9.0E-5	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	3.0	1.8E-7	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	3.0	9.0E-8	g	
Substance	3	Nickel	Nickel	7440-02-0	99.7	3.0	8.973E-5	g	
Material	2	Brass				3.0	0.02784	g	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	3.0	1.392E-7	g	
Substance	3	Nickel	Nickel	7440-02-0	0.2	3.0	5.568E-5	g	
Substance	3	Antimony	Supplier	7440-36-0	0.01	3.0	2.784E-6	g	
Substance	3	Copper	Supplier	7440-50-8	68.5	3.0	0.0190704	g	
Substance	3	Zinc	Supplier	7440-66-6	31.0026	3.0	0.00863112	g	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	3.0	2.784E-5	g	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	3.0	2.784E-7	g	
Substance	3	Arsenic	Supplier	7440-38-2	0.0099	3.0	2.75616E-6	g	
Substance	3	Iron	Supplier	7439-89-6	0.07	3.0	1.9488E-5	g	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	3.0	2.784E-7	g	
Substance	3	Manganese	Supplier	7439-96-5	0.05	3.0	1.392E-5	g	

Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	3.0	1.392E-6	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	3.0	1.392E-5	g	
Material	2	Tin Plate				3.0	7.0E-5	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	3.0	4.9E-8	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	3.0	1.4E-7	g	
Substance	3	Tin	Supplier	7440-31-5	99.73	3.0	6.9811E-5	g	