



<b>Form Type</b>	Distribute	<b>Version</b>	2.0	<b>Ref</b>	IPC 1752A	<b>Sectionals</b>	Material Info	<b>Subsectionals</b>	D, A
<b>Supplier Information</b>									
<b>Company Name</b>	TE Connectivity	<b>Request Document ID</b>		<b>Contact Name</b>	Benfer, David W	<b>Contact Title</b>	Staff Mfg & Process Dvl Engineer, Eng Proc Opt/LEANPD		
<b>Company Unique ID</b>	TE Connectivity	<b>Response Date</b>	2017-01-21	<b>Contact Email</b>	dave.benfer@te.com				
<b>Contact Phone Number</b>	+1-717-986-3725								
<b>Legal Statement</b>									
<b>Supplier Acceptance</b>	true								
<b>Legal Statement</b>									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
<b>Product</b>									
<b>Manufacturer Item number</b>	103361-4	<b>Amount</b>	1418.50325	<b>Version</b>	-	<b>Identity</b>			
<b>Manufacturer Item Name</b>	06 MODII HDR SRRRA SHRD .100CL	<b>Weight Uom</b>	mg	<b>Mfr Site</b>		<b>Authority</b>			
<b>Date</b>		<b>UOM</b>	Each						
<b>EURoHS-0508</b>	Product(s) does not meet EU RoHS requirements and is not under exemptions								
<b>ChinaRoHS-0508</b>	Product(s) is NOT eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
<b>EUREACH-1215</b>	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
<b>Product Disclosure</b>									
<b>Sub-Item/Material/Substance</b>	<b>Level</b>	<b>Name</b>	<b>Substance Category</b>	<b>Substance CAS</b>	<b>Substance Concentration</b>	<b>Quantity</b>	<b>Mass per Unit</b>	<b>UOM</b>	<b>Exemption</b>
Sub-Item	1	06 MODII HDR HSG SR SHRD				1.0	1112.0	mg	
Material	2	PA66-GF25				1.0	1112.0	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	3.5	1.0	38.92	mg	
Substance	3	Benzenamine, reaction products with aniline hydrochloride and nitrobenzene	Supplier	101357-15-7	4.0	1.0	44.48	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	25.0	1.0	278.0	mg	
Substance	3	Poly[imino(1,6-dioxo-1,6-hexanediy)imino-1,6-hexanediy]	Supplier	32131-17-2	61.5	1.0	683.88	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	6.0	1.0	66.72	mg	
Sub-Item	1	MOD II POST PLTD 30 DPLX				6.0	51.083875	mg	
Material	2	Brass				6.0	49.930929	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	6.0	4.9931E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	28.0225	6.0	13.99189	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.05	6.0	0.02496546	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	6.0	0.00499309	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	6.0	0.02496546	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	6.0	0.04993093	mg	
Substance	3	Copper	Supplier	7440-50-8	71.5	6.0	35.70061	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	6.0	4.9931E-4	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	6.0	0.00499309	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	6.0	2.4965E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.2	6.0	0.09986186	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	6.0	0.00249655	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	6.0	0.02496546	mg	

Material	2	Gold Plate				6.0	0.1677453	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	6.0	0.16724	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	6.0	5.0324E-4	mg	
Material	2	Nickel Plate				6.0	0.7136269	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	6.0	0.00142725	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	6.0	7.1363E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	6.0	0.71149	mg	
Material	2	Tin-Lead Plate				6.0	0.2715738	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	40.0	6.0	0.10863	mg	
Substance	3	Tin	Supplier	7440-31-5	60.0	6.0	0.16294	mg	