



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Cc Wu	Contact Title	Product Compliance Engineer		
Company Unique ID	TE Connectivity	Response Date	2016-06-23	Contact Email	cc.wu@te.com				
Contact Phone Number	86-2124071672								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	3-794630-4	Amount	676.8412	Version	-	Identity			
Manufacturer Item Name	04P MICRO MNL ASSY VRT HDR LF	Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-0615	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	MICROMNL LP CONT,VERTIC LE,SN				4.0	82.3403	mg	
Material	2	Brass				4.0	80.7	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	4.0	8.07E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	28.0225	4.0	22.61416	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.05	4.0	0.04035	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	4.0	0.00807	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	4.0	0.04035	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	4.0	0.0807	mg	
Substance	3	Copper	Supplier	7440-50-8	71.5	4.0	57.7005	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	4.0	8.07E-4	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	4.0	0.00807	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	4.0	4.035E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.2	4.0	0.1614	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	4.0	0.004035	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	4.0	0.04035	mg	
Material	2	Nickel Plate				4.0	0.5018	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	4.0	0.0010036	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	4.0	5.018E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	4.0	0.50029	mg	
Material	2	Tin Plate				4.0	1.1385	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	4.0	1.13543	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	4.0	0.002277	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	4.0	7.9695E-4	mg	
Sub-Item	1	4POS MICRO MNL HSG,BLACK				1.0	347.48	mg	
Material	2	PA4T-GF30-FR(40)				1.0	347.48	mg	
Substance	3	Carbon black	Supplier	1333-86-4	0.9	1.0	3.12732	mg	

Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	104.244	mg	
Substance	3	Polyamide 4T - ISO 1043-1 Term PA4T	Supplier	1043-1-PA4T	47.1	1.0	163.66308	mg	
Substance	3	Halogen-free organic phosphorus flame retardant - ISO 1043-4 code #FR(40)	Supplier	1043-4-FR40	12.0	1.0	41.6976	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	10.0	1.0	34.748	mg	