



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Benfer David W	Contact Title	Product Compliance Engineer for DND		
Company Unique ID	TE Connectivity	Response Date	2016-04-11	Contact Email	dave.benfer@te.com				
Contact Phone Number	717-986-3725								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	1473005-4	Amount	4596.6	Version	-	Identity			
Manufacturer Item Name	SEMI-HARD TRAY DDR2 SODIMM SOCKET 200P 5	Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-0615	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	DDR2 SODIMM SOCKET 200P 5.2H STD TYPE				1.0	4596.6	mg	
Material	2	Gold Plate				1.0	2.316	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	1.0	2.30905	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	1.0	0.006948	mg	
Material	2	Stainless Steel				1.0	604.0	mg	
Substance	3	Chromium	Supplier	7440-47-3	18.0	1.0	108.72	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.5	1.0	3.02	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.045	1.0	0.2718	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.0604	mg	
Substance	3	Carbon	Supplier	7440-44-0	0.15	1.0	0.906	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.01	1.0	0.0604	mg	
Substance	3	Silicon	Supplier	7440-21-3	1.5	1.0	9.06	mg	
Substance	3	Manganese	Supplier	7439-96-5	2.0	1.0	12.08	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.03	1.0	0.1812	mg	
Substance	3	Sulfur	Supplier	7704-34-9	0.03	1.0	0.1812	mg	
Substance	3	Iron	Supplier	7439-89-6	68.6147	1.0	414.43279	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	1.0	0.6034	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0099	1.0	0.059796	mg	
Substance	3	Nickel	Nickel	7440-02-0	9.0	1.0	54.36	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.00302	mg	
Material	2	Brass				1.0	96.11	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	9.611E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	28.0225	1.0	26.93242	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.05	1.0	0.048055	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.009611	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	1.0	0.048055	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.09611	mg	
Substance	3	Copper	Supplier	7440-50-8	71.5	1.0	68.71865	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	9.611E-4	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.009611	mg	

Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	4.8055E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.2	1.0	0.19222	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	0.0048055	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.048055	mg	
Material	2	Copper Alloy				1.0	1521.748	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	1.52175	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	0.30435	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.15217	mg	
Substance	3	Iron	Supplier	7439-89-6	0.2	1.0	3.0435	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	0.01521748	mg	
Substance	3	Tin	Supplier	7440-31-5	1.5	1.0	22.82622	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.15217	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	1.0	1.52175	mg	
Substance	3	Zinc	Supplier	7440-66-6	21.73	1.0	330.67584	mg	
Substance	3	Copper	Supplier	7440-50-8	76.0475	1.0	1157.25131	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.01521748	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.00760874	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	1.0	1.06522	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.2	1.0	3.0435	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.15217	mg	
Material	2	Tin Plate				1.0	1.766	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	1.0	0.0012362	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.003532	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	1.0	1.76123	mg	
Material	2	LCP-GF30				1.0	2232.6	mg	
Substance	3	Ethene, homopolymer	Supplier	9002-88-4	0.2	1.0	4.4652	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	3.0	1.0	66.978	mg	
Substance	3	Carbon black	Supplier	1333-86-4	2.0	1.0	44.652	mg	
Substance	3	2,6-Naphthalenedicarboxylic acid, polymer with 1,4-benzenedicarboxylic acid, 1,4-benzenediol, [1,1'-biphenyl]-4,4'-diol and 4-hydroxybenzoic acid	Supplier	126710-21-2	65.8	1.0	1469.0508	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	29.0	1.0	647.454	mg	
Material	2	Nickel Plate				1.0	138.06	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.27612	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.13806	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	137.64582	mg	