



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Rebecca Dong	Contact Title	Compliance Engineer		
Company Unique ID	TE Connectivity	Response Date	2016-04-26	Contact Email	Rebecca_dong@te.com				
Contact Phone Number	86(21)33259330								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	353293-4	Amount	0.2108	Version	-	Identity			
Manufacturer Item Name	MINI CT MT REC ASSY 4P GRAY	Weight Uom	g	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-0615	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	MT REC CONT FOR 1.5 MINI CT				4.0	0.02595	g	
Material	2	Phos Bronze				4.0	0.02495	g	
Substance	3	Copper	Supplier	7440-50-8	94.6985	4.0	0.02362728	g	
Substance	3	Manganese	Supplier	7439-96-5	0.02	4.0	4.99E-6	g	
Substance	3	Chromium	Supplier	7440-47-3	0.01	4.0	2.495E-6	g	
Substance	3	Tin	Supplier	7440-31-5	4.5	4.0	0.00112275	g	
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	4.0	1.2475E-6	g	
Substance	3	Antimony	Supplier	7440-36-0	0.01	4.0	2.495E-6	g	
Substance	3	Iron	Supplier	7439-89-6	0.1	4.0	2.495E-5	g	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	4.0	2.495E-7	g	
Substance	3	Zinc	Supplier	7440-66-6	0.3	4.0	7.485E-5	g	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	4.0	2.495E-5	g	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	4.0	2.495E-5	g	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	4.0	1.2475E-6	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	4.0	1.2475E-5	g	
Substance	3	Nickel	Nickel	7440-02-0	0.1	4.0	2.495E-5	g	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	4.0	1.2475E-7	g	
Material	2	Tin Plate				4.0	0.0010	g	
Substance	3	Zinc	Supplier	7440-66-6	0.35	4.0	3.5E-6	g	
Substance	3	Copper	Supplier	7440-50-8	1.5	4.0	1.5E-5	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	4.0	2.0E-6	g	
Substance	3	Tin	Supplier	7440-31-5	97.85	4.0	9.785E-4	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	4.0	1.0E-6	g	
Sub-Item	1	MINI CT MT REC HSG 4P GRAY				1.0	0.107	g	
Material	2	PA66-GF20-FR				1.0	0.107	g	
Substance	3	Phenol, 2,4(or 2,6)-dibromo-, homopolymer	Brominated Flame Retardants (other than PBBs or PBDEs)	69882-11-7	20.0	1.0	0.0214	g	

Substance	3	Poly[imino(1,6-dioxo-1,6-hexanediyl)imino-1,6-hexanediyl]	Supplier	32131-17-2	52.0	1.0	0.05564	g	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	20.0	1.0	0.0214	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	1.0	1.0	0.00107	g	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	7.0	1.0	0.00749	g	