



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Olson, Joseph R	Contact Title	Prod Sustaining Engineer		
Company Unique ID	TE Connectivity	Response Date	2015-07-24	Contact Email	jrolson@te.com				
Contact Phone Number	1-717-592-4423								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	5-104071-8	Amount	469.873565	Version	-	Identity			
Manufacturer Item Name	06 SYSTEM 50 HDR SRST SHRD SN	Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-1214	REACH Candidate Substances of Very High Concern ARE NOT Yet Reviewed								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	06 SYSTEM 50 HDR HSG SR LATCH				1.0	399.638645	mg	
Material	2	LIQUID CRYSTAL PLOYMER				1.0	399.638645	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	3.0	1.0	11.98916	mg	
Substance	3	Liquid Crystal Polymer - ISO 1043-1 Term LCP	Supplier	1043-1-LCP	67.0	1.0	267.75789	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	119.89159	mg	
Sub-Item	1	SYSTEM 50 POST PLTD SN				6.0	11.70582	mg	
Material	2	Tin Plate				6.0	0.0746	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	6.0	7.45254E-5	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	6.0	0.07452547	mg	
Material	2	Brass				6.0	11.23425	mg	
Substance	3	Tin	Supplier	7440-31-5	0.1	6.0	0.01123425	mg	
Substance	3	Copper	Supplier	7440-50-8	64.0	6.0	7.18992	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	6.0	0.00561712	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	6.0	1.1234E-4	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	6.0	0.00112342	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	6.0	0.01123425	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.1	6.0	0.01123425	mg	
Substance	3	Zinc	Supplier	7440-66-6	35.2085	6.0	3.95541	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	6.0	0.00112342	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	6.0	0.00112342	mg	
Substance	3	Aluminum	Supplier	7429-90-5	0.05	6.0	0.00561712	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.3	6.0	0.03370275	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	6.0	0.00112342	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	6.0	5.617125E-5	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	6.0	0.00561712	mg	
Material	2	Nickel Plate				6.0	0.219	mg	

Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	6.0	4.38E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	6.0	2.19E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	6.0	0.21834	mg	
Material	2	Gold Plate				6.0	0.1721	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	6.0	0.17158	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	6.0	5.163E-4	mg	
Material	2	Gold Plate				6.0	0.00587	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	6.0	1.761E-5	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	6.0	0.00585239	mg	