



| | | | | | | | | | |
|---|---|---|---------------------------|-----------------------------|--------------------------------|-----------------------------|--|----------------------|------------------|
| Form Type | Distribute | Version | 2.0 | Ref | IPC 1752A | Sectionals | Manufacturing Info/ Material Info | Subsectionals | D, A |
| Supplier Information | | | | | | | | | |
| Company Name | TE Connectivity | Request Document ID | | Contact Name | Chan, Nelson | Contact Title | Manager Sales, HKG SELL DIR-EMS | | |
| Company Unique ID | TE Connectivity | Response Date | 2015-10-28 | Contact Email | nelson.chan@te.com | | | | |
| Contact Phone Number | +852-2738-8751 | | | | | | | | |
| Legal Statement | | | | | | | | | |
| Supplier Acceptance | true | | | | | | | | |
| Legal Statement | | | | | | | | | |
| The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers. | | | | | | | | | |
| Product | | | | | | | | | |
| Manufacturer Item number | 1934222-1 | Amount | 11615.664 | Version | - | Identity | | | |
| Manufacturer Item Name | Tin Man Recpt Assy 4Pair8Column | Weight Uom | mg | Mfr Site | | Authority | | | |
| Date | | UOM | Each | | | | | | |
| EUROHS-0508 | Product(s) meets EU RoHS requirement without any exemptions | | | | | | | | |
| ChinaRoHS-0508 | Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products | | | | | | | | |
| EUREACH-1214 | REACH Candidate Substances of Very High Concern ARE NOT Yet Reviewed | | | | | | | | |
| Manufacturing Information | | | | | | | | | |
| J-STD-020 MSL Rating | | Max Total a Wave Time | | Ramp Rate | | Wave Additional Info | | | |
| Classification Temp | | Max Wave Solder Time | 0.0 | Ramp Down Rate | | Psi Rating Reflow | | | |
| Max Time Within 5 | | Psi Rating Wave | | Package Designator | | Size | 0.0 | | |
| Time Above 217 | | Reflow Additional Info | | Preheat Max Temp | | Terminal Base Alloy | Cu Alloy | | |
| Preheat Duration | | bulk Solder Termination | NAC | Nbr or Reflow Cycles | | Terminal Plating | Matte Tin (Sn) - reflowed over Nickel (Ni) barrier | | |
| Preheat Min Temp | | Nbr of Instances | 0 | Component Temp Spike | | Shape | NAC | | |
| Product Disclosure | | | | | | | | | |
| Sub-Item/Material/Substance | Level | Name | Substance Category | Substance CAS | Substance Concentration | Quantity | Mass per Unit | UOM | Exemption |
| Sub-Item | 1 | TinMan Receptacle 4 Pair Overmold Assy | | | | 4.0 | 2255.916 | mg | |
| Material | 2 | Tin Plate | | | | 4.0 | 0.7792 | mg | |
| Substance | 3 | Lead | Lead/Lead Compounds | 7439-92-1 | 0.0999 | 4.0 | 7.7842E-4 | mg | |
| Substance | 3 | Tin | Supplier | 7440-31-5 | 99.9001 | 4.0 | 0.77842 | mg | |
| Material | 2 | LCP-GF20 | | | | 4.0 | 1429.0 | mg | |
| Substance | 3 | Ethene, homopolymer | Supplier | 9002-88-4 | 0.15 | 4.0 | 2.1435 | mg | |
| Substance | 3 | Glass, oxide, chemicals | Supplier | 65997-17-3 | 20.0 | 4.0 | 285.8 | mg | |
| Substance | 3 | Contains No Reportable TE5081-2 Substances | Supplier | TE5081-2-1212 | 1.25 | 4.0 | 17.8625 | mg | |
| Substance | 3 | Chlorite-group minerals | Supplier | 1318-59-8 | 3.0 | 4.0 | 42.87 | mg | |
| Substance | 3 | 2,6-Naphthalenedi carboxylic acid, polymer with 1,4-benzenedicarb oxylic acid, 1,4-benzenediol and 4-hydroxybenzoi c acid | Supplier | 86013-04-9 | 57.2 | 4.0 | 817.388 | mg | |
| Substance | 3 | Talc (Mg3H2(SiO3) 4) | Supplier | 14807-96-6 | 16.6 | 4.0 | 237.214 | mg | |
| Substance | 3 | Carbon black | Supplier | 1333-86-4 | 1.25 | 4.0 | 17.8625 | mg | |

| | | | | | | | | | |
|-----------|---|--|---------------------------|---------------|---------|-----|-----------|----|--|
| Substance | 3 | Aluminum hydroxide (Al(OH)3) | Supplier | 21645-51-2 | 0.15 | 4.0 | 2.1435 | mg | |
| Substance | 3 | Magnesite (Mg(CO3)), calcined | Supplier | 83897-85-2 | 0.2 | 4.0 | 2.858 | mg | |
| Substance | 3 | Dolomite (CaMg(CO3)2) | Supplier | 16389-88-1 | 0.2 | 4.0 | 2.858 | mg | |
| Material | 2 | Nickel Plate | | | | 4.0 | 34.53 | mg | |
| Substance | 3 | Contains No Reportable TE5081-2 Substances | Supplier | TE5081-2-1212 | 0.2 | 4.0 | 0.06906 | mg | |
| Substance | 3 | Lead | Lead/Lead Compounds | 7439-92-1 | 0.1 | 4.0 | 0.03453 | mg | |
| Substance | 3 | Nickel | Nickel | 7440-02-0 | 99.7 | 4.0 | 34.42641 | mg | |
| Material | 2 | Gold Plate | | | | 4.0 | 0.4068 | mg | |
| Substance | 3 | Gold | Supplier | 7440-57-5 | 99.7 | 4.0 | 0.40558 | mg | |
| Substance | 3 | Contains No Reportable TE5081-2 Substances | Supplier | TE5081-2-0909 | 0.3 | 4.0 | 0.0012204 | mg | |
| Material | 2 | Phos Bronze | | | | 4.0 | 791.2 | mg | |
| Substance | 3 | Copper | Supplier | 7440-50-8 | 94.6985 | 4.0 | 749.25453 | mg | |
| Substance | 3 | Manganese | Supplier | 7439-96-5 | 0.02 | 4.0 | 0.15824 | mg | |
| Substance | 3 | Chromium | Supplier | 7440-47-3 | 0.01 | 4.0 | 0.07912 | mg | |
| Substance | 3 | Tin | Supplier | 7440-31-5 | 4.5 | 4.0 | 35.604 | mg | |
| Substance | 3 | Arsenic | Supplier | 7440-38-2 | 0.0050 | 4.0 | 0.03956 | mg | |
| Substance | 3 | Iron | Supplier | 7439-89-6 | 0.1 | 4.0 | 0.7912 | mg | |
| Substance | 3 | Antimony | Supplier | 7440-36-0 | 0.01 | 4.0 | 0.07912 | mg | |
| Substance | 3 | Beryllium | Supplier | 7440-41-7 | 0.0010 | 4.0 | 0.007912 | mg | |
| Substance | 3 | Zinc | Supplier | 7440-66-6 | 0.3 | 4.0 | 2.3736 | mg | |
| Substance | 3 | Phosphorus | Supplier | 7723-14-0 | 0.1 | 4.0 | 0.7912 | mg | |
| Substance | 3 | Cobalt | Supplier | 7440-48-4 | 0.1 | 4.0 | 0.7912 | mg | |
| Substance | 3 | Cadmium | Cadmium/Cadmium Compounds | 7440-43-9 | 0.0050 | 4.0 | 0.03956 | mg | |
| Substance | 3 | Lead | Lead/Lead Compounds | 7439-92-1 | 0.05 | 4.0 | 0.3956 | mg | |
| Substance | 3 | Nickel | Nickel | 7440-02-0 | 0.1 | 4.0 | 0.7912 | mg | |
| Substance | 3 | Mercury | Mercury/Mercury Compounds | 7439-97-6 | 5.0E-4 | 4.0 | 0.003956 | mg | |
| Sub-Item | 1 | ZP MAX HSG RCP 4P8C | | | | 1.0 | 2592.0 | mg | |
| Material | 2 | LCP-(MD+GF)30 | | | | 1.0 | 2592.0 | mg | |
| Substance | 3 | Contains No Reportable TE5081-2 Substances | Supplier | TE5081-2-1212 | 1.0 | 1.0 | 25.92 | mg | |
| Substance | 3 | Glass, oxide, chemicals | Supplier | 65997-17-3 | 10.0 | 1.0 | 259.2 | mg | |
| Substance | 3 | 1,4-Benzenedicarboxylic acid, polymer with [1,1-biphenyl]-4,4-diol, 4-hydroxybenzoic acid, 6-hydroxy-2-naphthalenecarboxylic acid and N-(4-hydroxyphenyl)acetamide | Supplier | 147310-94-9 | 66.0 | 1.0 | 1710.72 | mg | |
| Substance | 3 | Carbon black | Supplier | 1333-86-4 | 1.0 | 1.0 | 25.92 | mg | |
| Substance | 3 | Talc (Mg3H2(SiO3)4) | Supplier | 14807-96-6 | 22.0 | 1.0 | 570.24 | mg | |