



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Olson, Joseph R	Contact Title	Prod Sustaining Engineer		
Company Unique ID	TE Connectivity	Response Date	2015-07-24	Contact Email	jrolson@te.com				
Contact Phone Number	1-717-592-4423								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	5-104666-3	Amount	2399.1692096	Version	-	Identity			
Manufacturer Item Name	40 SYSTEM 50 HDR DRST SHRD SN	Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUROHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-1214	REACH Candidate Substances of Very High Concern ARE NOT Yet Reviewed								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	SYSTEM 50 POST PLTD 30 DPLX SN				40.0	23.51423024	mg	
Material	2	Tin Plate				40.0	0.0746	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	40.0	7.45254E-5	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	40.0	0.07452547	mg	
Material	2	Gold Plate				40.0	0.0602	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	40.0	0.0600194	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	40.0	1.806E-4	mg	
Material	2	Nickel Plate				40.0	0.137	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	40.0	2.74E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	40.0	1.37E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	40.0	0.13659	mg	
Material	2	Brass				40.0	23.24	mg	
Substance	3	Tin	Supplier	7440-31-5	0.1	40.0	0.02324	mg	
Substance	3	Copper	Supplier	7440-50-8	64.0	40.0	14.8736	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	40.0	0.01162	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	40.0	2.324E-4	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	40.0	0.002324	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	40.0	0.02324	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.1	40.0	0.02324	mg	
Substance	3	Zinc	Supplier	7440-66-6	35.2085	40.0	8.18246	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	40.0	0.002324	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	40.0	0.002324	mg	
Substance	3	Aluminum	Supplier	7429-90-5	0.05	40.0	0.01162	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.3	40.0	0.06972	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	40.0	0.002324	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	40.0	1.162E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	40.0	0.01162	mg	
Material	2	Gold Plate				40.0	0.00243024	mg	

Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	40.0	1.0E-5	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	40.0	0.00242295	mg	
Sub-Item	1	40 SYSTEM 50 HDR HSG DR LATCH				1.0	1458.6	mg	
Material	2	LIQUID CRYSTAL PLOYMER				1.0	1458.6	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	3.0	1.0	43.758	mg	
Substance	3	Liquid Crystal Polymer - ISO 1043-1 Term LCP	Supplier	1043-1-LCP	67.0	1.0	977.262	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	437.58	mg	