



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A																									
Supplier Information																																		
Company Name	TE Connectivity	Request Document ID		Contact Name	Benfer, David W	Contact Title	Prod Compliance Engineer																											
Company Unique ID	TE Connectivity	Response Date	2016-05-13	Contact Email	dave.benfer@te.com																													
Contact Phone Number		717-986-3725																																
Legal Statement																																		
Supplier Acceptance	true																																	
Legal Statement																																		
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.																																		
Product																																		
Manufacturer Item number	2-292208-4	Amount	1110.304	Version	-	Identity																												
Manufacturer Item Name	MINI CT D/R DIP 24P V NAT	Weight Uom	mg	Mfr Site		Authority																												
Date		UOM	Each																															
EUROHS-0508	Product(s) meets EU RoHS requirement without any exemptions																																	
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products																																	
EUREACH-0615	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH																																	
Product Disclosure																																		
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption																									
Sub-Item	1	AMP MINI D/R HDR HSG V24P GRAY				1.0	646.0	mg																										
Material	2	PA66-GF20-FR				1.0	646.0	mg																										
Substance	3	Phenol, 2,4(or 2,6)-dibromo-, homopolymer	Brominated Flame Retardants (other than PBBs or PBDEs)	69882-11-7	20.0	1.0	129.2	mg																										
Substance	3	Poly[imino(1,6-dioxo-1,6-hexanediyl)imino-1,6-hexanediyl]	Supplier	32131-17-2	52.0	1.0	335.92	mg																										
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	20.0	1.0	129.2	mg																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	1.0	1.0	6.46	mg																										
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	7.0	1.0	45.22	mg																										
Sub-Item	1	0.5SQ POST				12.0	20.976	mg																										
Material	2	Tin Plate				12.0	0.242	mg																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	12.0	4.84E-4	mg																										
Substance	3	Tin	Supplier	7440-31-5	99.73	12.0	0.24135	mg																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	12.0	1.694E-4	mg																										
Material	2	Brass				12.0	20.5	mg																										
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	12.0	1.025E-4	mg																										
Substance	3	Nickel	Nickel	7440-02-0	0.2	12.0	0.041	mg																										
Substance	3	Antimony	Supplier	7440-36-0	0.01	12.0	0.00205	mg																										
Substance	3	Copper	Supplier	7440-50-8	68.5	12.0	14.0425	mg																										
Substance	3	Zinc	Supplier	7440-66-6	31.0026	12.0	6.35553	mg																										
Substance	3	Cobalt	Supplier	7440-48-4	0.1	12.0	0.0205	mg																										
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	12.0	2.05E-4	mg																										
Substance	3	Arsenic	Supplier	7440-38-2	0.0099	12.0	0.0020295	mg																										
Substance	3	Iron	Supplier	7439-89-6	0.07	12.0	0.01435	mg																										
Substance	3	Chromium	Supplier	7440-47-3	0.0010	12.0	2.05E-4	mg																										
Substance	3	Manganese	Supplier	7439-96-5	0.05	12.0	0.01025	mg																										

Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	12.0	0.001025	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	12.0	0.01025	mg	
Material	2	Nickel Plate				12.0	0.234	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	12.0	4.68E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	12.0	2.34E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	12.0	0.2333	mg	
Sub-Item	1	0.5SQ POST				12.0	17.716	mg	
Material	2	Tin Plate				12.0	0.211	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	12.0	4.22E-4	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	12.0	0.21043	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	12.0	1.477E-4	mg	
Material	2	Brass				12.0	17.3	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	12.0	8.65E-5	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.2	12.0	0.0346	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	12.0	0.00173	mg	
Substance	3	Copper	Supplier	7440-50-8	68.5	12.0	11.8505	mg	
Substance	3	Zinc	Supplier	7440-66-6	31.0026	12.0	5.36345	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	12.0	0.0173	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	12.0	1.73E-4	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0099	12.0	0.0017127	mg	
Substance	3	Iron	Supplier	7439-89-6	0.07	12.0	0.01211	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	12.0	1.73E-4	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.05	12.0	0.00865	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	12.0	8.65E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	12.0	0.00865	mg	
Material	2	Nickel Plate				12.0	0.205	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	12.0	4.1E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	12.0	2.05E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	12.0	0.20438	mg	