



<b>Form Type</b>	Distribute	<b>Version</b>	2.0	<b>Ref</b>	IPC 1752A	<b>Sectionals</b>	Material Info	<b>Subsectionals</b>	D, A
<b>Supplier Information</b>									
<b>Company Name</b>	TE Connectivity	<b>Request Document ID</b>		<b>Contact Name</b>	Olson, Joseph R	<b>Contact Title</b>	Prod Sustaining Engineer		
<b>Company Unique ID</b>	TE Connectivity	<b>Response Date</b>	2015-07-24	<b>Contact Email</b>	jrolson@te.com				
<b>Contact Phone Number</b>	1-717-592-4423								
<b>Legal Statement</b>									
<b>Supplier Acceptance</b>	true								
<b>Legal Statement</b>									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
<b>Product</b>									
<b>Manufacturer Item number</b>	5-104666-4	<b>Amount</b>	2877.438912	<b>Version</b>	-	<b>Identity</b>			
<b>Manufacturer Item Name</b>	50 SYSTEM 50 HDR DRST SHRD SN	<b>Weight Uom</b>	mg	<b>Mfr Site</b>		<b>Authority</b>			
<b>Date</b>		<b>UOM</b>	Each						
<b>EUROHS-0508</b>	Product(s) meets EU RoHS requirement without any exemptions								
<b>ChinaRoHS-0508</b>	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
<b>EUREACH-1214</b>	REACH Candidate Substances of Very High Concern ARE NOT Yet Reviewed								
<b>Product Disclosure</b>									
<b>Sub-Item/Material/Substance</b>	<b>Level</b>	<b>Name</b>	<b>Substance Category</b>	<b>Substance CAS</b>	<b>Substance Concentration</b>	<b>Quantity</b>	<b>Mass per Unit</b>	<b>UOM</b>	<b>Exemption</b>
Sub-Item	1	SYSTEM 50 POST PLTD 30 DPLX SN				50.0	23.51423024	mg	
Material	2	Gold Plate				50.0	0.00243024	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	50.0	1.0E-5	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	50.0	0.00242295	mg	
Material	2	Brass				50.0	23.24	mg	
Substance	3	Tin	Supplier	7440-31-5	0.1	50.0	0.02324	mg	
Substance	3	Copper	Supplier	7440-50-8	64.0	50.0	14.8736	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	50.0	0.01162	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	50.0	2.324E-4	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	50.0	0.002324	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	50.0	0.02324	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.1	50.0	0.02324	mg	
Substance	3	Zinc	Supplier	7440-66-6	35.2085	50.0	8.18246	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	50.0	0.002324	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	50.0	0.002324	mg	
Substance	3	Aluminum	Supplier	7429-90-5	0.05	50.0	0.01162	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.3	50.0	0.06972	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	50.0	0.002324	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	50.0	1.162E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	50.0	0.01162	mg	
Material	2	Nickel Plate				50.0	0.137	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	50.0	2.74E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	50.0	1.37E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	50.0	0.13659	mg	
Material	2	Tin Plate				50.0	0.0746	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	50.0	7.45254E-5	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	50.0	0.07452547	mg	
Material	2	Gold Plate				50.0	0.0602	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	50.0	0.0600194	mg	

Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	50.0	1.806E-4	mg	
Sub-Item	1	50 SYSTEM 50 HDR HSG DR LATCH				1.0	1701.7274	mg	
Material	2	LIQUID CRYSTAL PLOYMER				1.0	1701.7274	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	3.0	1.0	51.05182	mg	
Substance	3	Liquid Crystal Polymer - ISO 1043-1 Term LCP	Supplier	1043-1-LCP	67.0	1.0	1140.15736	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	510.51822	mg	