



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	David Benfer	Contact Title	Product Compliance Engineer		
Company Unique ID	TE Connectivity	Response Date	2015-04-09	Contact Email	dave.benfer@te.com				
Contact Phone Number	717-986-3725								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	5-5179010-6	Amount	3506.00504458	Version	-	Identity			
Manufacturer Item Name	0.8FH,R13H.5,140,08/Sn,TU	Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-1213	REACH Candidate Substances of Very High Concern ARE NOT Yet Reviewed								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	0.8 FH REC HSG 140P H13 BL=0.5				1.0	2440.0	mg	
Material	2	LCP-GF30				1.0	2440.0	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	732.0	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.4	1.0	9.76	mg	
Substance	3	1,4-Benzenedicarboxylic acid, polymer with [1,1-biphenyl]-4,4-diol, 4-hydroxybenzoic acid, 6-hydroxy-2-naphthalenecarboxylic acid and N-(4-hydroxyphenyl)acetamide	Supplier	147310-94-9	69.6	1.0	1698.24	mg	
Sub-Item	1	FH 0.8 9H, 13H REC CONT AUFLASH-MATTE TIN				140.0	7.61432175	mg	
Material	2	Gold Plate				140.0	0.00309875	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	140.0	0.00308945	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	140.0	1.0E-5	mg	
Material	2	Tin Plate				140.0	0.113223	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	140.0	1.1311E-4	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	140.0	0.11311	mg	
Material	2	Nickel Plate				140.0	0.498	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	140.0	9.96E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	140.0	4.98E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	140.0	0.49651	mg	
Material	2	Beryllium Copper				140.0	7.0	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	140.0	7.0E-5	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	140.0	0.0014	mg	

Substance	3	Iron	Supplier	7439-89-6	0.2	140.0	0.014	mg	
Substance	3	Aluminum	Supplier	7429-90-5	0.2	140.0	0.014	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.5	140.0	0.035	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.6	140.0	0.042	mg	
Substance	3	Copper	Supplier	7440-50-8	98.1535	140.0	6.87074	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	140.0	7.0E-4	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	140.0	7.0E-4	mg	
Substance	3	Silicon	Supplier	7440-21-3	0.2	140.0	0.014	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	140.0	3.5E-4	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	140.0	3.5E-5	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	140.0	0.0035	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.05	140.0	0.0035	mg	