



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A																									
Supplier Information																																		
Company Name	TE Connectivity	Request Document ID		Contact Name	Benfer, David W	Contact Title	Prod Compliance Engineer																											
Company Unique ID	TE Connectivity	Response Date	2015-12-28	Contact Email	dave.benfer@te.com																													
Contact Phone Number		717-986-3725																																
Legal Statement																																		
Supplier Acceptance	true																																	
Legal Statement																																		
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.																																		
Product																																		
Manufacturer Item number	5205207-1	Amount	6830.7187	Version	-	Identity																												
Manufacturer Item Name	HD RECPT ASSY SIZE 3	Weight Uom	mg	Mfr Site		Authority																												
Date		UOM	Each																															
EUROHS-0508	Product(s) meets EU RoHS requirement without any exemptions																																	
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products																																	
EUREACH-1214	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH																																	
Product Disclosure																																		
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption																									
Sub-Item	1	25 RCPT REAR INSERT				1.0	1740.0	mg																										
Material	2	PA66-GF25				1.0	1740.0	mg																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	3.5	1.0	60.9	mg																										
Substance	3	Benzenamine, reaction products with aniline hydrochloride and nitrobenzene	Supplier	101357-15-7	4.0	1.0	69.6	mg																										
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	25.0	1.0	435.0	mg																										
Substance	3	Poly[imino(1,6-dioxo-1,6-hexanediy)]imino-1,6-hexanediy]	Supplier	32131-17-2	61.5	1.0	1070.1	mg																										
Substance	3	Phosphorus	Supplier	7723-14-0	6.0	1.0	104.4	mg																										
Sub-Item	1	25 RCPT FRONT INSERT				1.0	2784.0	mg																										
Material	2	PBT-I-GF30-FR(17)				1.0	2784.0	mg																										
Substance	3	Dolomite (CaMg(CO3)2)	Supplier	16389-88-1	0.5	1.0	13.92	mg																										
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	35.0	1.0	974.4	mg																										
Substance	3	Benzenepropionic acid, 3,5-bis(1,1-dimethylethyl)-4-hydroxy-, 1,1-[2,2-bis[[3-[3,5-bis(1,1-dimethylethyl)-4-hydroxyphenyl]-1-oxopropoxy]methyl]-1,3-propanediyl] ester	Supplier	6683-19-8	0.2	1.0	5.568	mg																										
Substance	3	Furan, tetrahydro-	Supplier	109-99-9	0.2	1.0	5.568	mg																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	3.0	1.0	83.52	mg																										

Substance	3	Talc (Mg3H2(SiO3)4)	Supplier	14807-96-6	2.0	1.0	55.68	mg	
Substance	3	Ethene, 1,1,2,2-tetrafluoro-, homopolymer	Supplier	9002-84-0	1.0	1.0	27.84	mg	
Substance	3	Chlorite-group minerals	Supplier	1318-59-8	0.5	1.0	13.92	mg	
Substance	3	Carbon black	Supplier	1333-86-4	1.0	1.0	27.84	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	36.6	1.0	1018.944	mg	
Substance	3	Phosphoric acid, zinc salt (2:3)	Supplier	7779-90-0	0.5	1.0	13.92	mg	
Substance	3	Aromatic Brominated flame retardant with Antimony - ISO 1043-4 code #FR(17)	Supplier	1043-4-FR17	18.0	1.0	501.12	mg	
Substance	3	Quartz (SiO2)	Supplier	14808-60-7	0.5	1.0	13.92	mg	
Substance	3	2-Propenenitrile, polymer with ethenylbenzene	Supplier	9003-54-7	1.0	1.0	27.84	mg	
Sub-Item	1	SHELL FRT RCPT SZ 3 AMPLIMITE ZN				1.0	231.0564	mg	
Material	2	Zinc Plate				1.0	101.793	mg	
Substance	3	Zinc	Supplier	7440-66-6	100.0	1.0	101.793	mg	
Material	2	Tri Chrome Film				1.0	0.2634	mg	
Substance	3	Silicate(2-), hexafluoro-hydrogen (1:2)	Supplier	16961-83-4	30.0	1.0	0.07902	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	10.0	1.0	0.02634	mg	
Substance	3	Chromium chloride (CrCl3), hydrate (1:6)	Supplier	10060-12-5	60.0	1.0	0.15804	mg	
Material	2	Carbon Steel				1.0	129.0	mg	
Substance	3	Aluminum	Supplier	7429-90-5	0.08	1.0	0.1032	mg	
Substance	3	Sulfur	Supplier	7704-34-9	0.02	1.0	0.0258	mg	
Substance	3	Carbon	Supplier	7440-44-0	0.02	1.0	0.0258	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.0129	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.02	1.0	0.0258	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.15	1.0	0.1935	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.129	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.0129	mg	
Substance	3	Molybdenum	Supplier	7439-98-7	0.75	1.0	0.9675	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.4	1.0	0.516	mg	
Substance	3	Silicon	Supplier	7440-21-3	0.1	1.0	0.129	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.00129	mg	
Substance	3	Iron	Supplier	7439-89-6	98.1785	1.0	126.65026	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.05	1.0	0.0645	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.0129	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	6.45E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.129	mg	
Sub-Item	1	SHELL REAR SZ 3 AMPLIMITE ZN				1.0	2075.6623	mg	
Material	2	Carbon Steel				1.0	2000.0	mg	
Substance	3	Carbon	Supplier	7440-44-0	0.05	1.0	1.0	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.2	mg	
Substance	3	Sulfur	Supplier	7704-34-9	0.02	1.0	0.4	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.15	1.0	3.0	mg	
Substance	3	Silicon	Supplier	7440-21-3	0.1	1.0	2.0	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.02	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.2	mg	

Substance	3	Iron	Supplier	7439-89-6	97.9335	1.0	1958.67	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	2.0	mg	
Substance	3	Molybdenum	Supplier	7439-98-7	0.75	1.0	15.0	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.035	1.0	0.7	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.6	1.0	12.0	mg	
Substance	3	Aluminum	Supplier	7429-90-5	0.08	1.0	1.6	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.01	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	2.0	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.05	1.0	1.0	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.2	mg	
Material	2	Zinc Plate				1.0	75.467	mg	
Substance	3	Zinc	Supplier	7440-66-6	100.0	1.0	75.467	mg	
Material	2	Tri Chrome Film				1.0	0.1953	mg	
Substance	3	Silicate(2-), hexafluoro-, hydrogen (1:2)	Supplier	16961-83-4	30.0	1.0	0.05859	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	10.0	1.0	0.01953	mg	
Substance	3	Chromium chloride (CrCl3), hydrate (1:6)	Supplier	10060-12-5	60.0	1.0	0.11718	mg	