



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Manufacturing Info/ Material Info	Subsectionals	D, A																	
<b>Supplier Information</b>																										
Company Name	TE Connectivity	Request Document ID		Contact Name	CC WU	Contact Title	Product Compliance Engineer																			
Company Unique ID	TE Connectivity	Response Date	2016-12-11	Contact Email	cc.wu@tycoelectronics.com																					
Contact Phone Number	021-33259321																									
<b>Legal Statement</b>																										
Supplier Acceptance	true																									
<b>Legal Statement</b>																										
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.																										
<b>Product</b>																										
Manufacturer Item number	206429-1	Amount	9.2258	Version	-	Identity																				
Manufacturer Item Name	CPC PLUG ASSEMBLY SIZE 11-4	Weight Uom	g	Mfr Site		Authority																				
Date		UOM	Each																							
EUROHS-0508	Product(s) meets EU RoHS requirement without any exemptions																									
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products																									
EUREACH-1215	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH																									
<b>Manufacturing Information</b>																										
J-STD-020 MSL Rating		Max Total a Wave Time		Ramp Rate		Wave Additional Info																				
Classification Temp		Max Wave Solder Time	0.0	Ramp Down Rate		Psl Rating Reflow																				
Max Time Within 5		Psl Rating Wave		Package Designator		Size	0.0																			
Time Above 217		Reflow Additional Info		Preheat Max Temp		Terminal Base Alloy	Not Applicable																			
Preheat Duration		bulk Solder Termination	Not Applicable	Nbr or Reflow Cycles		Terminal Plating	Not Applicable																			
Preheat Min Temp		Nbr of Instances	0	Component Temp Spike		Shape	Not Applicable																			
<b>Product Disclosure</b>																										
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption																	
Sub-Item	1	PLUG FOR PIN CONT, SZ 11-4 CPC				1.0	5.0545	g																		
Material	2	PA66-GF25				1.0	5.0545	g																		
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	3.5	1.0	0.1769075	g																		
Substance	3	Benzenamine, reaction products with aniline hydrochloride and nitrobenzene	Supplier	101357-15-7	4.0	1.0	0.20218	g																		
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	25.0	1.0	1.263625	g																		
Substance	3	Poly[imino(1,6-dioxo-1,6-hexanediyl)imino-1,6-hexanediyl]	Supplier	32131-17-2	61.5	1.0	3.1085175	g																		
Substance	3	Phosphorus	Supplier	7723-14-0	6.0	1.0	0.30327	g																		
Sub-Item	1	COUPLING RING,SZ 11,CPC				1.0	4.1713	g																		
Material	2	PA66-GF25-FR(52)				1.0	4.1713	g																		

Substance	3	Poly[imino(1,6-dioxo-1,6-hexanediyl)imino-1,6-hexanediyl]	Supplier	32131-17-2	65.5	1.0	2.7322015	g	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	25.0	1.0	1.042825	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	2.0	1.0	0.083426	g	
Substance	3	Carbon black	Supplier	1333-86-4	1.0	1.0	0.041713	g	
Substance	3	Inorganic Red Phosphorus flame retardant - ISO 1043-4 code #FR(52)	Supplier	1043-4-FR52	6.5	1.0	0.2711345	g	