



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Benfer, David W	Contact Title	Prod Compliance Engineer for DND		
Company Unique ID	TE Connectivity	Response Date	2015-12-07	Contact Email	dave.benfer@te.com				
Contact Phone Number	717-986-3725								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	536052-5	Amount	9302.743456	Version	-	Identity			
Manufacturer Item Name	064 EURO TYPE B PIN ASSY	Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) does not meet EU RoHS requirements and is not under exemptions								
ChinaRoHS-0508	Product(s) is NOT eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-1214	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	064 EURO B R/A PIN HSG				1.0	5455.5	mg	
Material	2	PBT-I-GF30FR(17)				1.0	5455.5	mg	
Substance	3	Phosphoric acid, zinc salt (2:3)	Supplier	7779-90-0	0.5	1.0	27.2775	mg	
Substance	3	Benzenepropionic acid, 3,5-bis(1,1-dimethylethyl)-4-hydroxy-, 1,1-[2,2-bis[[3-[3,5-bis(1,1-dimethylethyl)-4-hydroxyphenyl]-1-oxopropoxy]methyl]-1,3-propanediyl] ester	Supplier	6683-19-8	0.1	1.0	5.4555	mg	
Substance	3	Aluminum oxide (Al2O3)	Supplier	1344-28-1	0.1	1.0	5.4555	mg	
Substance	3	Copper oxide (CuO)	Supplier	1317-38-0	0.1	1.0	5.4555	mg	
Substance	3	Ethene, 1,1,2,2-tetrafluoro-, homopolymer	Supplier	9002-84-0	1.0	1.0	54.555	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	45.895	1.0	2503.80173	mg	
Substance	3	Zinc oxide (ZnO)	Supplier	1314-13-2	0.1	1.0	5.4555	mg	
Substance	3	2-Propenenitrile, polymer with ethenylbenzene	Supplier	9003-54-7	1.0	1.0	54.555	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	4.0	1.0	218.22	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	2.0	1.0	109.11	mg	
Substance	3	Carbon black	Supplier	1333-86-4	0.01	1.0	0.54555	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	1636.65	mg	

Substance	3	Furan, tetrahydro-	Supplier	109-99-9	0.18	1.0	9.8199	mg	
Substance	3	Zinc sulfide (ZnS)	Supplier	1314-98-3	2.0	1.0	109.11	mg	
Substance	3	Aromatic Brominated flame retardant with Antimony - ISO 1043-4 code #FR(17)	Supplier	1043-4-FR17	10.0	1.0	545.55	mg	
Substance	3	Talc (Mg3H2(SiO3)4)	Supplier	14807-96-6	3.0	1.0	163.665	mg	
Substance	3	1H-Isoidole-1,3(2H)-dione, 4,5,6,7-tetrachloro-2-[2-(4,5,6,7-tetrachloro-2,3-dihydro-1,3-dioxo-1H-inden-2-yl)-8-quinolinyl]-	Supplier	30125-47-4	0.01	1.0	0.54555	mg	
Substance	3	Methane, dichloro-	Supplier	75-09-2	0.0050	1.0	0.27278	mg	
Sub-Item	1	ENH EURO PIN A 30AU				32.0	49.91	mg	
Material	2	Nickel Plate				32.0	0.59	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	32.0	0.00118	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	32.0	5.9E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	32.0	0.58823	mg	
Material	2	Tin-Lead Plate				32.0	0.28	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	7.0	32.0	0.0196	mg	
Substance	3	Tin	Supplier	7440-31-5	92.3	32.0	0.25844	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.7	32.0	0.00196	mg	
Material	2	Brass				32.0	49.01	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	32.0	4.901E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	28.0225	32.0	13.73383	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.05	32.0	0.024505	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	32.0	0.004901	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	32.0	0.024505	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	32.0	0.04901	mg	
Substance	3	Copper	Supplier	7440-50-8	71.5	32.0	35.04215	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	32.0	4.901E-4	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	32.0	0.004901	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	32.0	2.4505E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.2	32.0	0.09802	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	32.0	0.0024505	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	32.0	0.024505	mg	
Material	2	Gold Plate				32.0	0.03	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	32.0	0.02991	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	32.0	9.0E-5	mg	
Sub-Item	1	ENH EURO PIN B 30AU				32.0	70.316358	mg	
Material	2	Nickel Plate				32.0	0.82285	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	32.0	0.0016457	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	32.0	8.2285E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	32.0	0.82038	mg	
Material	2	Tin-Lead Plate				32.0	0.475118	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	7.0	32.0	0.03325826	mg	
Substance	3	Tin	Supplier	7440-31-5	92.3	32.0	0.43853	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.7	32.0	0.00332583	mg	
Material	2	Brass				32.0	68.99	mg	

Substance	3	Chromium	Supplier	7440-47-3	0.0010	32.0	6.899E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	28.0225	32.0	19.33272	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.05	32.0	0.034495	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	32.0	0.006899	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	32.0	0.034495	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	32.0	0.06899	mg	
Substance	3	Copper	Supplier	7440-50-8	71.5	32.0	49.32785	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	32.0	6.899E-4	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	32.0	0.006899	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	32.0	3.4495E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.2	32.0	0.13798	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	32.0	0.0034495	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	32.0	0.034495	mg	
Material	2	Gold Plate				32.0	0.02839	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	32.0	0.02830483	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	32.0	8.517E-5	mg	