



<b>Form Type</b>	Distribute	<b>Version</b>	2.0	<b>Ref</b>	IPC 1752A	<b>Sectionals</b>	Manufacturing Info/ Material Info	<b>Subsectionals</b>	D, A
<b>Supplier Information</b>									
<b>Company Name</b>	TE Connectivity	<b>Request Document ID</b>		<b>Contact Name</b>	Revak, David M	<b>Contact Title</b>	Mgr Prod Sustaining Engineering		
<b>Company Unique ID</b>	TE Connectivity	<b>Response Date</b>	2015-07-15	<b>Contact Email</b>	david.revak@te.com				
<b>Contact Phone Number</b>	+1-336-664-1906								
<b>Legal Statement</b>									
<b>Supplier Acceptance</b>	true								
<b>Legal Statement</b>									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
<b>Product</b>									
<b>Manufacturer Item number</b>	282080-1	<b>Amount</b>	2.78948845	<b>Version</b>	-	<b>Identity</b>			
<b>Manufacturer Item Name</b>	AMP SUPERSEAL 1.5 SERIES 2P PL	<b>Weight Uom</b>	g	<b>Mfr Site</b>		<b>Authority</b>			
<b>Date</b>		<b>UOM</b>	Each						
<b>EUROHS-0508</b>	Product(s) meets EU RoHS requirement without any exemptions								
<b>ChinaRoHS-0508</b>	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
<b>EUREACH-1214</b>	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
<b>Manufacturing Information</b>									
<b>J-STD-020 MSL Rating</b>		<b>Max Total a Wave Time</b>		<b>Ramp Rate</b>		<b>Wave Additional Info</b>			
<b>Classification Temp</b>		<b>Max Wave Solder Time</b>	0.0	<b>Ramp Down Rate</b>		<b>Psi Rating Reflow</b>			
<b>Max Time Within 5</b>		<b>Psi Rating Wave</b>		<b>Package Designator</b>		<b>Size</b>	0.0		
<b>Time Above 217</b>		<b>Reflow Additional Info</b>		<b>Preheat Max Temp</b>		<b>Terminal Base Alloy</b>	NAC		
<b>Preheat Duration</b>		<b>bulk Solder Termination</b>	NAC	<b>Nbr or Reflow Cycles</b>		<b>Terminal Plating</b>	NAC		
<b>Preheat Min Temp</b>		<b>Nbr of Instances</b>	0	<b>Component Temp Spike</b>		<b>Shape</b>	NAC		
<b>Product Disclosure</b>									
<b>Sub-Item/Material/Substance</b>	<b>Level</b>	<b>Name</b>	<b>Substance Category</b>	<b>Substance CAS</b>	<b>Substance Concentration</b>	<b>Quantity</b>	<b>Mass per Unit</b>	<b>UOM</b>	<b>Exemption</b>
Sub-Item	1	PLUG HOUSING				1.0	1.9865	g	
Material	2	POLYAMIDE 66				1.0	1.9865	g	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	20.0	1.0	0.3973	g	
Substance	3	Zinc	Supplier	7440-66-6	15.0	1.0	0.297975	g	
Substance	3	Copper	Supplier	7440-50-8	1.0	1.0	0.019865	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	2.0	1.0	0.03973	g	
Substance	3	Poly[[imino(1,6-dioxo-1,6-hexanediy)]imino-1,6-hexanediy]]	Supplier	32131-17-2	60.0	1.0	1.1919	g	
Substance	3	Carbon black	Supplier	1333-86-4	1.0	1.0	0.019865	g	
Substance	3	Aluminum	Supplier	7429-90-5	1.0	1.0	0.019865	g	
Sub-Item	1	RUBBER SEAL				1.0	0.56098	g	
Material	2	Elastomer Compound				1.0	0.275	g	
Substance	3	Siloxanes and Silicones, di-Me, vinyl group-terminated	Supplier	68083-19-2	61.4	1.0	0.16885	g	
Substance	3	Siloxanes and Silicones, Me hydrogen	Supplier	63148-57-2	2.9	1.0	0.007975	g	

Substance	3	Silanamine, 1-ethenyl-N-(ethenyldimethylsilyl)-1,1-dimethyl-	Supplier	7691-02-3	0.4	1.0	0.0011	g	
Substance	3	Cyclohexanol, 1-ethynyl-	Supplier	78-27-3	0.1	1.0	2.75E-4	g	
Substance	3	Siloxanes and Silicones, di-Me, di-Ph	Supplier	68083-14-7	3.4	1.0	0.00935	g	
Substance	3	Silanamine, 1,1,1-trimethyl-N-(trimethylsilyl)-, hydrolysis products with silica	Supplier	68909-20-6	31.8	1.0	0.08745	g	
Material	2	Polyester Compound				1.0	0.275	g	
Substance	3	Silanamine, 1-ethenyl-N-(ethenyldimethylsilyl)-1,1-dimethyl-	Supplier	7691-02-3	0.4	1.0	0.0011	g	
Substance	3	Siloxanes and Silicones, di-Me, vinyl group-terminated	Supplier	68083-19-2	63.8	1.0	0.17545	g	
Substance	3	Siloxanes and Silicones, di-Me, Me vinyl, vinyl group-terminated	Supplier	68083-18-1	1.8	1.0	0.00495	g	
Substance	3	Platinate(2-), hexachloro-, hydrogen (1:2), (OC-6-11)-, reaction products with 2,4,6,8-tetraethenyl-2,4,6,8-tetramethylcyclotetrasiloxane	Supplier	68585-32-0	0.1	1.0	2.75E-4	g	
Substance	3	Siloxanes and Silicones, di-Me, di-Ph	Supplier	68083-14-7	3.2	1.0	0.0088	g	
Substance	3	Silanamine, 1,1,1-trimethyl-N-(trimethylsilyl)-, hydrolysis products with silica	Supplier	68909-20-6	30.7	1.0	0.084425	g	
Material	2	COLORANT				1.0	0.01098	g	
Substance	3	Bismuth vanadium oxide (BiVO4)	Supplier	14059-33-7	19.0	1.0	0.0020862	g	
Substance	3	Silica	Supplier	7631-86-9	1.0	1.0	1.098E-4	g	
Substance	3	Siloxanes and Silicones, di-Me, vinyl group-terminated	Supplier	68083-19-2	80.0	1.0	0.008784	g	
Sub-Item	1	SECONDARY LOCK				1.0	0.24200845	g	
Material	2	POLYAMIDE 66				1.0	0.24200845	g	
Substance	3	Aluminum	Supplier	7429-90-5	1.0	1.0	0.00242008	g	
Substance	3	Poly[[imino(1,6-dioxo-1,6-hexanediy)]imino-1,6-hexanediy]	Supplier	32131-17-2	67.0	1.0	0.16214566	g	
Substance	3	Zinc	Supplier	7440-66-6	15.0	1.0	0.03630127	g	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	15.0	1.0	0.03630127	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	2.0	1.0	0.00484017	g	