



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Benfer, David W	Contact Title	Prod Compliance Engineer		
Company Unique ID	TE Connectivity	Response Date	2016-05-13	Contact Email	dave.benfer@te.com				
Contact Phone Number	717-986-3725								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	5406299-1	Amount	6540.875484	Version	-	Identity			
Manufacturer Item Name	MJ ASSY,S/P,8POS,SH,RVPGT,CAT 5	Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUROHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-0615	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	SHLD SNG PORTMJRVS PNL GD TB LF				1.0	2165.935484	mg	
Material	2	Brass				1.0	2122.0	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	0.02122	mg	
Substance	3	Zinc	Supplier	7440-66-6	28.0225	1.0	594.63745	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.05	1.0	1.061	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.2122	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	1.0	1.061	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	2.122	mg	
Substance	3	Copper	Supplier	7440-50-8	71.5	1.0	1517.23	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.02122	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.2122	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.01061	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.2	1.0	4.244	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	0.1061	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	1.061	mg	
Material	2	Nickel Plate				1.0	22.621506	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.02262151	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.04524301	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	22.55364	mg	
Material	2	Tin Plate				1.0	21.313978	mg	
Substance	3	Tin	Supplier	7440-31-5	97.85	1.0	20.85573	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.04262796	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.35	1.0	0.07459892	mg	
Substance	3	Copper	Supplier	7440-50-8	1.5	1.0	0.31971	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.02131398	mg	
Sub-Item	1	MJ ASSY,S/P,8POS,UNSHLD C				1.0	3853.14	mg	

Material	2	PA6T/66-GF30FR(16+72)				1.0	2057.0	mg	
Substance	3	Benzene, ethenyl-, homopolymer, brominated	Supplier	88497-56-7	25.0	1.0	514.25	mg	
Substance	3	Boric acid, zinc salt	Supplier	1332-07-6	5.0	1.0	102.85	mg	
Substance	3	Carbon black	Supplier	1333-86-4	3.0	1.0	61.71	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.5	1.0	10.285	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	35.0	1.0	719.95	mg	
Substance	3	Polyamide Homologous Polymer Series - ISO 1043-1 Term PA6T/66	Supplier	1043-1-PA6T/66	31.5	1.0	647.955	mg	
Material	2	Gold Plate				1.0	0.42	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	1.0	0.00126	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	1.0	0.41874	mg	
Material	2	Nickel Plate				1.0	6.58	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.00658	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.01316	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	6.56026	mg	
Material	2	PBT-GF30				1.0	1337.8	mg	
Substance	3	1,4-Benzenedicarboxylic acid, polymer with 1,4-butanediol	Supplier	26062-94-2	54.4	1.0	727.7632	mg	
Substance	3	Phenol, 4,4-(1-methylethylene)bis[2,6-dibromo-, polymer with 2,2-[(1-methylethylene)bis[(2,6-dibromo-4,1-phenylene)oxy methylene]]bis[oxirane]	Supplier	68928-70-1	12.0	1.0	160.536	mg	
Substance	3	12H-Phthaloperin-12-one, 8,9,10,11-tetrachloro-	Supplier	20749-68-2	0.1	1.0	1.3378	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	3.5	1.0	46.823	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	401.34	mg	
Material	2	Tin Plate				1.0	3.34	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.00668	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	1.0	3.33098	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	1.0	0.002338	mg	
Material	2	Phos Bronze				1.0	448.0	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.448	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.0448	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.2	1.0	0.896	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	1.0	0.0224	mg	
Substance	3	Copper	Supplier	7440-50-8	90.0485	1.0	403.41728	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	0.0896	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.35	1.0	1.568	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.00448	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	1.0	0.448	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	1.0	0.0448	mg	
Substance	3	Tin	Supplier	7440-31-5	9.0	1.0	40.32	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	1.0	0.448	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.00224	mg	

Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	0.0224	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.224	mg	
Sub-Item	1	SHLD REAR R/A 8POS LF,NI PLTD				1.0	521.8	mg	
Material	2	Brass				1.0	509.4	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	0.005094	mg	
Substance	3	Zinc	Supplier	7440-66-6	28.0225	1.0	142.74662	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.05	1.0	0.2547	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.05094	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	1.0	0.2547	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.5094	mg	
Substance	3	Copper	Supplier	7440-50-8	71.5	1.0	364.221	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.005094	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.05094	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.002547	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.2	1.0	1.0188	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	0.02547	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.2547	mg	
Material	2	Nickel Plate				1.0	12.4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.0124	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.0248	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	12.3628	mg	