



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Benfer, David W	Contact Title	Mgr. Global Product CoProd Compliance Engineerpliance		
Company Unique ID	TE Connectivity	Response Date	2016-05-10	Contact Email	dave.benfer@te.com				
Contact Phone Number	717-986-3725								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	292230-6	Amount	333.338	Version	-	Identity			
Manufacturer Item Name	1.5 MINI CT SGL V SMT W/BOSS 6	Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-0615	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	1.5 CT SGL V SMT ASSY W/BOSS				1.0	333.338	mg	
Material	2	PPA-GF30				1.0	239.0	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	71.7	mg	
Substance	3	Benzene, ethenyl-, homopolymer, brominated	Supplier	88497-56-7	20.0	1.0	47.8	mg	
Substance	3	Antimonate (SbO31-), sodium (1:1)	Supplier	15432-85-6	4.0	1.0	9.56	mg	
Substance	3	1,4-Benzenedicarboxylic acid, polymer with 1,6-hexanediamine and hexanedioic acid	Supplier	25776-72-1	46.0	1.0	109.94	mg	
Material	2	Tin Plate				1.0	0.837	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.001674	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	1.0	0.83474	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	1.0	5.859E-4	mg	
Material	2	Brass				1.0	92.67	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.2	1.0	0.18534	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.009267	mg	
Substance	3	Zinc	Supplier	7440-66-6	35.5226	1.0	32.91879	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.09267	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	9.267E-4	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	1.0	0.046335	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.05	1.0	0.046335	mg	
Substance	3	Copper	Supplier	7440-50-8	64.0	1.0	59.3088	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	9.267E-4	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0099	1.0	0.00917433	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.046335	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	4.6335E-4	mg	

Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	0.0046335	mg	
Material	2	Nickel Plate				1.0	0.831	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.001662	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	8.31E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	0.82851	mg	