



<b>Form Type</b>	Distribute	<b>Version</b>	2.0	<b>Ref</b>	IPC 1752A	<b>Sectionals</b>	Material Info	<b>Subsectionals</b>	D, A
<b>Supplier Information</b>									
<b>Company Name</b>	TE Connectivity	<b>Request Document ID</b>		<b>Contact Name</b>	Benfer, David W	<b>Contact Title</b>	Prod Compliance Engineer		
<b>Company Unique ID</b>	TE Connectivity	<b>Response Date</b>	2017-01-10	<b>Contact Email</b>	dave.benfer@te.com				
<b>Contact Phone Number</b>	717-986-3725								
<b>Legal Statement</b>									
<b>Supplier Acceptance</b>	true								
<b>Legal Statement</b>									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
<b>Product</b>									
<b>Manufacturer Item number</b>	5555980-1	<b>Amount</b>	2976.870077	<b>Version</b>	-	<b>Identity</b>			
<b>Manufacturer Item Name</b>	MJ,R/A,4P/4C,T RAY PACK	<b>Weight Uom</b>	mg	<b>Mfr Site</b>		<b>Authority</b>			
<b>Date</b>		<b>UOM</b>	Each						
<b>EUroHS-0508</b>	Product(s) meets EU RoHS requirement without any exemptions								
<b>ChinaRoHS-0508</b>	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
<b>EUREACH-1215</b>	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
<b>Product Disclosure</b>									
<b>Sub-Item/Material/Substance</b>	<b>Level</b>	<b>Name</b>	<b>Substance Category</b>	<b>Substance CAS</b>	<b>Substance Concentration</b>	<b>Quantity</b>	<b>Mass per Unit</b>	<b>UOM</b>	<b>Exemption</b>
Sub-Item	1	HSG,R/A,4PO S,MOD JK				1.0	2729.8	mg	
Material	2	PBT-GF20-FR(17)				1.0	2729.8	mg	
Substance	3	Benzenepropanoic acid, 3,5-bis(1,1-dimethylethyl)-4-hydroxy-, 1,1-[2,2-bis[[3-[3,5-bis(1,1-dimethylethyl)-4-hydroxyphenyl]-1-oxopropoxy]methyl]-1,3-propanediyl] ester	Supplier	6683-19-8	0.2	1.0	5.4596	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	25.0	1.0	682.45	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	5.0	1.0	136.49	mg	
Substance	3	Ethene, 1,1,2,2-tetrafluoro-, homopolymer	Supplier	9002-84-0	0.5	1.0	13.649	mg	
Substance	3	2-Propenenitrile, polymer with ethenylbenzene	Supplier	9003-54-7	0.5	1.0	13.649	mg	
Substance	3	Phosphoric acid, zinc salt (2:1)	Supplier	13598-37-3	0.3	1.0	8.1894	mg	
Substance	3	Carbon black	Supplier	1333-86-4	1.5	1.0	40.947	mg	
Substance	3	Aromatic Brominated flame retardant with Antimony - ISO 1043-4 code #FR(17)	Supplier	1043-4-FR17	17.0	1.0	464.066	mg	
Substance	3	Furan, tetrahydro-	Supplier	109-99-9	0.2	1.0	5.4596	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	5.0	1.0	136.49	mg	

Substance	3	Ethene, homopolymer	Supplier	9002-88-4	5.0	1.0	136.49	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	39.796	1.0	1086.35121	mg	
Substance	3	Arsenic oxide (As2O3)	Arsenic oxide (As2O3)	1327-53-3	0.0020	1.0	0.054596	mg	
Substance	3	Lead oxide (lead monoxide)	Lead/Lead Compounds	1317-36-8	0.0020	1.0	0.054596	mg	
Sub-Item	1	TERM,R/A,4 POSN,MOD JK,PLATED				1.0	247.070077	mg	
Material	2	Phos Bronze				1.0	244.4	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.2444	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.02444	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.2	1.0	0.4888	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	1.0	0.01222	mg	
Substance	3	Copper	Supplier	7440-50-8	90.0485	1.0	220.07853	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	0.04888	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.35	1.0	0.8554	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.002444	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	1.0	0.2444	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	1.0	0.02444	mg	
Substance	3	Tin	Supplier	7440-31-5	9.0	1.0	21.996	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	1.0	0.2444	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.001222	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	0.01222	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.1222	mg	
Material	2	Gold Plate				1.0	1.755055	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	1.0	0.00526517	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	1.0	1.74979	mg	
Material	2	Nickel Plate				1.0	0.892571	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	8.9257E-4	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.00178514	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	0.88989	mg	
Material	2	Tin Plate				1.0	0.022451	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	4.4902E-5	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	1.0	0.02239038	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	1.0	1.57157E-5	mg	